

USB-C to USB-B Cable (M/M) - USB 3.2, Gen 1 (5 Gbps), Thunderbolt 3 Compatible, 3 ft. (0.91 m)

MODEL NUMBER: **U422-003**



Connect a Type-B device, such as a printer, a scanner or an external hard drive, to the USB Type-C™ (USB-C) port on your smartphone, tablet, Ultrabook or computer.

Description

The U422-003 USB 3.2 Gen 1 Cable connects the USB Type-C (USB-C) port on your smartphone, tablet, Ultrabook or computer to a device with a USB Type-B port, such as a printer, a scanner or an external hard drive. The 3-ft. (0.91 m) cable supports data transfer speeds up to 5 Gbps. Unlike traditional USB cables that can be attached only one way, the reversible USB Type-C male connector plugs into a USB port in either direction for fast, fumble-free connection every time. Superior foil shielding provides reliable, error-free data communication. Nickel-plated molded end connectors and gold-plated copper contacts ensure superior conductivity and long life. Slim form supports evolving design trends toward smaller devices.

Features

Supports USB 3.2 Gen 1 Data transfer speeds up to 5 Gbps—10 times faster than USB 2.0 Uses USB Type-B male connector

USB Type-C (USB-C) Male Connector Fumble-free reversible plug ensures fast, easy connection every time Powerful enough for smartphones, tablets, computers and other larger platforms Premium Construction Gold-plated copper contacts and nickel-plated molded ends provide a lifetime of heavy use and superior conductivity Superior foil shielding offers reliable, error-free data communication Slim, sleek design tailored for emerging design trends toward smaller devices

Highlights

- Connects a USB Type-C (USB-C) device to any USB Type-B device
- Supports USB 3.2 Gen 1 data transfer speeds up to 5 Gbps
- Features reversible USB Type-C male plug on one end
- Works with USB 3.2 Gen 1 devices

System Requirements

- A device with a USB Type-C (USB-C) port
- A device with a USB Type-B port

Package Includes

- U422-003 USB 3.2 Gen 1 (5 Gbps) Cable, USB Type-C (USB-C) to USB Type-B M/M, 3-ft. (0.91 m)

Specifications

OVERVIEW	
UPC Code	037332189264
Technology	Thunderbolt; USB 3.x
Cable Type	Passive
CONNECTIONS	



Powering Business Worldwide

TRIPP LITE
SERIES

Side A - Connector 1	USB C (MALE)
Side B - Connector 1	USB B (MALE)
Connector Plating	Nickel
Contact Plating	Gold
Connector Style	Straight
PHYSICAL	
Material of Construction	PVC
Cable Jacket Color	Black
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	4.5MM
Cable Length (ft.)	3
Cable Length (m)	0.91
Cable Length (in.)	36
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.13
Shipping Weight (kg)	0.06
ENVIRONMENTAL	
Operating Temperature Range	14° to 140°F (-10° to 60°C)
Storage Temperature Range	-4° to 185°F (-20° to 85°C)
Relative Humidity	10% to 85% RH, Non-Condensing
FEATURES & SPECIFICATIONS	
USB Specification	USB 3.2 Gen 1 (up to 5 Gbps)
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[U422-003](#)