

› Electromechanical Counters

Hour Counter

CHMDR

- › 6-digits hour meter
- › Capacity 100 000 hrs (99 999.9 hrs)
- › Operation indicator
- › DIN Rail Mount 35 mm
- › Screw Washer
- › IP20 for terminals, IP40 for enclosure
- › Highly resistant to shocks and impacts
- › Excellent visibility due to the large digit size



CHMDR

Product selection			
Type	Operating frequency (Hz)	Rated Voltage	Part Number
CHMDR	-	10 → 80 V~	99793810N

General characteristics	
Counting capacity	99999.9
Reset to zero	Not included
Read accuracy (h)	1/10
Height digits (mm)	3.6
Colour of hour numbers	White on a black background
Colour of decimal digits	Black on a white background
Accuracy / Tolerance	± 0.02 % over entire range
Counting input mode	Addition
Operation indicator	Running Indicator 1 digit in 36 s
Degree of protection	IP20 for terminals, IP40 for enclosure
Mounting position	DIN Rail/Base
Size (mm)	35 mm
Temperature limits use (°C)	-5 → +55
Temperature limits stored (°C)	-20 → +70
Humidity	95 % (non-condensing)
Connections / Termination	Screw Washer
Consumption	1 VA
Vibration resistance	60Hz to 150 Hz ,2g
Test voltage for AC models	500 V
Weight (g)	70
Certifications	CE, UKCA, RoHS compliant
Approvals	-

You have a project? Contact us on www.crouzet.com

Description:

Crouzet Hour Meters, accurate and durable solutions for time measurement needs


Crouzet's hour meters are reliable electromechanical devices designed for measuring and recording time in industrial applications.

Crouzet's hour meters accurately track the duration of operation, providing essential information for maintenance scheduling and equipment monitoring.

For more information about: please visit www.crouzet.com

Dimensions (mm)

Panel Mounted

**Warning:**

The product information contained in this catalogue is given purely as information and does not constitute a representation, warranty or any form of contractual commitment. Crouzet and its subsidiaries reserve the right to modify their products without notice. It is imperative that we should be consulted over any particular use or application of our products and it is the responsibility of the buyer to establish, particularly through all the appropriate tests, that the product is suitable for the use or application. Under no circumstances will our warranty apply, nor shall we be held responsible for any application (such as any modification, addition, deletion, use in conjunction with other electrical or electronic components, circuits or assemblies, or any other unsuitable material or substance) which has not been expressly agreed by us prior to the sale of our products.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Crouzet:](#)

[99793810N](#)