

DisplayPort 1.2 to DVI Compact Adapter Video Converter (M/F)

MODEL NUMBER: **P134-000-DVI-V2**



Highlights

- Connect a DVI monitor to a computer with a DisplayPort output
- DisplayPort v1.2 to DVI Adapter Converter (DisplayPort-Male to DVI-I Female)
- Plug-and-play convenience; no drivers or software needed
- This product is a passive adapter and requires that the connected computer has a DP++ (DisplayPort ++) dual-mode mode

Package Includes

- DisplayPort 1.2 to DVI Compact Adapter Converter (DP-Male to DVI-I Female)

Description

The P134-000-DVI-V2 DisplayPort v1.2 to DVI Adapter Converter allows you to connect a computer with a DisplayPort connection to a DVI monitor. DisplayPort v1.2 doubles the previous version bandwidth of 8.64 Gbps to 17.28 Gbps in High Bit Rate (HBR2) mode, which allows increased resolutions, higher refresh rates and greater color depth. Fully molded one-piece design ensures longer life. The P134-000-DVI-V2 is a passive adapter and requires that the connected computer has a DP++ (DisplayPort ++) dual-mode port, which allows HDMI and DVI signals to be passed through. Check the documentation for your DisplayPort source for compatibility.

Features

- Connect a DVI monitor to a computer with a DisplayPort output
- DisplayPort v1.2 to DVI Adapter Converter (DisplayPort-Male to DVI-I Female)
- Supports DVI single-link computer video resolutions up to 1920 x 1080 (1080p)
- 17.28 Gbps bandwidth
- Fully molded one piece design
- Plug and Play; no drivers or software required
- Requires that the connected computer has a DP++ (DisplayPort ++) port, which allows HDMI and DVI signals to be passed through; check the documentation for your DisplayPort source for compatibility.

Specifications

OVERVIEW	
UPC Code	037332187550
Product Type	Video Adapter
Technology	DVI; DisplayPort
CONNECTIONS	

Side A - Connector 1	DISPLAYPORT (MALE)
Side B - Connector 1	DVI-I (FEMALE)
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / in.)	5.90 x 3.90 x 0.50
Shipping Dimensions (hwd / cm)	14.99 x 9.91 x 1.27
Shipping Weight (lbs.)	0.06
Shipping Weight (kg)	0.03
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[P134-000-DVI-V2](#)