

## DisplayPort to VGA Active Adapter Video Converter, Black (M/F), 1 ft. (0.31 m)

MODEL NUMBER: P134-001-VGA



DP to VGA converter connects a VGA monitor to the DisplayPort output on your laptop, PC or Chromebook.

### Features

**DP to VGA Converter Connects a DisplayPort Source to Your Existing VGA Display** This DisplayPort to VGA active adapter connects a VGA monitor, projector or television to the DisplayPort output on your PC, Chromebook or other compatible computer or tablet. It features a male DP connector and a female HD15 connector, allowing you to continue using your existing VGA display and VGA cable to transmit video signals without the expense of a new DP display.

**Transmits Outstanding 1080p Video for High-Definition Presentations** Ideal for classrooms, lecture halls and anywhere else you may give a presentation, this DisplayPort to VGA converter supports computer video resolutions up to 1920 x 1200, including 1080p, and high-definition resolutions up to 1080p. The active adapter converts both Single-Mode and Dual-Mode (DP++) DisplayPort output. It's recommended for use with graphics cards, such as AMD Eyefinity, that do not output DP++ signals.

**Ready to Use Right Out of the Package** The plug-and-play adapter requires no software, drivers or external power, works with both Windows and Mac operating systems, and is compatible with laptops, tablets and other devices equipped with a female DisplayPort. With its small size, the P134-001-VGA is recommended for stowing in your laptop bag and carrying to school, the office or the latest trade show.

**3-Year Warranty** The P134-001-VGA is backed by a 3-year warranty, ensuring reliability and performance.

## Specifications

OVERVIEW	
UPC Code	037332212870
Product Type	Video Adapter
Technology	VGA/SVGA; DisplayPort

### Highlights

- Continue using your current VGA display without the expense of a new DP monitor
- Delivers high-definition picture quality at resolutions up to 1920 x 1200, including 1080p
- Compact unit fits easily into briefcase or laptop bag for instant use anywhere
- Plug-and-play operation with no software required for easy, immediate installation
- Ideal for video presentations and watching movies in HD on a VGA display

### Applications

- Display 1080p video on an existing VGA monitor without the expense of buying a new DisplayPort monitor
- Extend your laptop's display to a secondary VGA monitor
- Give a video presentation in a classroom, conference room or trade show booth

### System Requirements

- Source device with DisplayPort output
- Display device with VGA input
- Not for use with MST hubs. For compatibility with MST hubs, use a DisplayPort 1.2-compliant adapter, such as P134-06N-VGA-V2.

### Package Includes

- P134-001-VGA DisplayPort to VGA Active Adapter – M/F, 1920 x 1200 (1080p), Black, 1 ft.



Powering Business Worldwide

TRIPP LITE  
SERIES

CONNECTIONS	
Side A - Connector 1	DISPLAYPORT (MALE)
Side B - Connector 1	HD15 (FEMALE)
PHYSICAL	
Color	Black
Cable Length (ft.)	1
Cable Length (m)	0.30
Cable Length (in.)	12
Cable Length (cm)	31
Shipping Weight (lbs.)	0.09
Shipping Weight (kg)	0.04
ENVIRONMENTAL	
Operating Temperature Range	32° to 113°F (0° to 45°C)
Storage Temperature Range	14° to 158°F (-10° to 70°C)
Operating Humidity Range	10% TO 85% RH, Non-Condensing
Storage Humidity Range	5% TO 90% RH, Non-Condensing
STANDARDS & COMPLIANCE	
Product Compliance	CE (Europe); FCC (USA); REACH; RoHS; UKCA; WEEE
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[P134-001-VGA](#)