

## Bracket Accessory - enables Vertical PDU Installation with Rear-Facing Outlets

MODEL NUMBER: PDUMVROTATEBRKT



### Highlights

- Set of brackets enables vertical PDU placement with outlets facing the rear in button-mount equipped racks
- Rear facing outlets enhance airflow and equipment cabling access
- Toolless mounting supported

### Description

PDUMVROTATEBRKT enables toolless installation of select PDUs in 0U vertical orientation with rear-facing outlets to facilitate better rack front-to-rear airflow and equipment access. Pair of brackets with installation buttons snap into the accessory mounting rails in equipped racks. Each bracket accepts a PDU button mount that snaps into place to securely hold a PDU as it distributes power to your rack enclosure.

Compatible with PDU1415, PDU1420T, PDU40TDUAL, PDUV15, PDUV20, PDUV30HV, PDUMV15, PDUMV20, PDUMV40, PDUMV30, PDUMV20HV, PDUMV30HV, PDUMV15NET, PDUMV20NET, PDUMV30NET, PDUMV20HVNET, PDUMV30HVNET and other PDUs referencing this accessory.

### Features

- Enables toolless installation of select PDUs in 0U / vertical orientation with rear-facing outlets to facilitate better rack front-to-rear airflow and equipment access
- Pair of brackets with installation buttons snap into the accessory mounting rails in equipped racks
- Each bracket accepts a PDU button mount that snaps into place to securely hold a PDU as it distributes power to your rack enclosure
- Compatible with PDU1415, PDU1420T, PDU40TDUAL, PDUV15, PDUV20, PDUV30HV, PDUMV15, PDUMV20, PDUMV40, PDUMV30, PDUMV20HV, PDUMV30HV, PDUMV15NET, PDUMV20NET, PDUMV30NET, PDUMV20HVNET, PDUMV30HVNET and other PDUs referencing this accessory

## Specifications

OVERVIEW	
UPC Code	037332147271
Accessory Type	Mounting Bracket
Accessory Class	PDU Accessories
PHYSICAL	
Shipping Dimensions (hwd / in.)	2.70 x 3.65 x 2.10



Powering Business Worldwide

TRIPP LITE  
SERIES

Shipping Dimensions (hwd / cm)	6.86 x 9.27 x 5.33
Shipping Weight (lbs.)	0.30
Shipping Weight (kg)	0.14
Unit Dimensions (hwd / in.)	2.613 x 2.322 x 1.654
<b>FEATURES &amp; SPECIFICATIONS</b>	
IP68 Rated	No
IP20 Rated	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS; EIA/ECA-310-E
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[PDUMVROTATEBRKT](#)