


# SmartRack Enclosure Skirt Kit for Euro-Series Wide Server Rack, 800 mm Width

MODEL NUMBER: SRSKIRTEU



Server rack skirt kit blocks unwanted airflow beneath 800 mm wide rack enclosure cabinets to improve cooling efficiency.

## Features

**Improves Cooling Efficiency and Optimizes Airflow in Your Euro-Series Rack** This SmartRack® enclosure skirt kit blocks unwanted airflow under a rack enclosure cabinet. By segregating cold aisle from hot aisle, this easy-to-install brush strip helps you reduce operating costs, improve equipment performance and provide longer lifespans for rack-mounted networking components. It also prevents dust from infiltrating the rack's interior.

**Installation Is Simple and Hassle-Free** This server rack skirt kit is compatible with Euro-Series rack cabinets, including SRX42 and SRX47, which measure 800 millimeters in width. All necessary mounting equipment is included. Just install the brush strip at floor level across the front or rear of the cabinet to prevent an air stream from forming between hot and cold aisles.

## Specifications

OVERVIEW	
UPC Code	037332214386
Accessory Type	Enclosure Skirt Kit
Accessory Class	Cooling Accessories
COOLING	
Cooling Type	Passive
PHYSICAL	
Shipping Dimensions (hwd / in.)	0.59 x 32.28 x 2.75
Shipping Dimensions (hwd / cm)	1.50 x 81.99 x 6.98

## Highlights

- Improves cooling efficiency by segregating hot aisles from cold aisles
- Hassle-free brush strip also prevents dust from getting inside the rack
- Compatible with SRX42 and SRX47 800 mm wide racks
- Includes all necessary installation hardware, so you can mount immediately

## Applications

- Prevent unwanted airflow under your rack enclosure to segregate cold aisle from hot aisle

## System Requirements

- Compatible with Euro-Series wide rack enclosures, including SRX42 and SRX47

## Package Includes

- SRSKIRTEU SmartRack Enclosure Skirt Kit for Euro-Series Wide Server Rack
- Mounting hardware



Powering Business Worldwide



Shipping Weight (lbs.)	0.73
Shipping Weight (kg)	0.33
Unit Dimensions (hwd / in.)	0.393 x 31.490 x 2.500
Unit Dimensions (hwd / cm)	6.35 x 81.99 x 0.99
Unit Weight (lbs.)	0.579
Unit Weight (kg)	0.26
<b>FEATURES &amp; SPECIFICATIONS</b>	
IP68 Rated	No
IP20 Rated	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS; EIA/ECA-310-E
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[SRSKIRTEU](#)