

## USB-C Cable (M/M) - USB 2.0, 5A (100W) Rated, Right-Angle Plug, Black, 2 m (6.6 ft.)

MODEL NUMBER: U040-02M-C-5ARA



USB cable with right-angle plug connects a smartphone or other USB-C device to the USB-C port on your computer, charger or power bank.

### Features

#### USB-C Cable Connects Devices for Charging or Transferring Data

This USB cable (M/M) is compatible with any device with a USB-C or Thunderbolt 3 port, including MacBook Pros, Chromebooks and Windows laptops. It allows you to connect your notebook computer to a docking station, your Apple or Android smartphone to a wall charger or power bank, or an external hard drive to a PC or tablet, to name just a few valuable uses for the cable.

#### PD Charging Cable Supports up to 100W for Syncing and Charging Mobile Devices

The Power Delivery cable provides power output up to 20V 5A (100W), which is sufficient for fast charging, syncing and powering most large-capacity devices, including the MacBook Pro. It also supports USB 2.0 data transfer rates up to 480 Mbps. The USB-C to USB-C cable is backward compatible with previous USB generations, allowing you to use it with older equipment.

#### Right-Angle Plug Makes Connecting in Tight Spaces Easier

A space-saving right-angle USB-C connector is easy to install in confined spaces, such as behind your computer or workstation. The right-angle construction also helps relieve strain on the cable and connector and prevents the cable from bending awkwardly.

#### Reversible USB-C Connectors Attach in Either Direction

Unlike traditional USB cables that connect in only one direction, the reversible USB-C male connectors plug into a USB-C or Thunderbolt 3 port in either direction for an instant connection every time.

### Highlights

- Power Delivery cable supports 20V 5A (100W) power output for charging host device
- Supports USB 2.0 speeds up to 480 Mbps to ensure efficient data transfers
- Reversible USB-C plugs connect in either direction for immediate no-fuss use
- Space-saving right-angle USB-C plug allows easy connection in confined spaces
- USB-C to USB-C cable is compatible with all USB-C and Thunderbolt 3 devices

### Applications

- Charge and power your MacBook Pro, Windows laptop or other USB-C or Thunderbolt 3 device from a USB-C wall charger
- Transfer data between an external hard drive and your laptop or PC
- Connect your laptop to a docking station or hub with a USB-C or Thunderbolt 3 port

### System Requirements

Devices with USB-C or Thunderbolt 3 ports

### Package Includes

U040-02M-C-5ARA USB-C to USB-C Cable, M/M, Black, 2 m (6.6 ft.)

## Specifications

OVERVIEW	
UPC Code	037332263698
Technology	USB 2.0 (High Speed)
Cable Type	Passive
INPUT	
Maximum Input Amps	5



Powering Business Worldwide

TRIPP LITE  
SERIES

Maximum Input Watts	100
<b>POWER</b>	
USB Power Delivery (PD) Charging Support	Yes
USB Power Delivery (PD) Charging Specification	3.0
<b>CONNECTIONS</b>	
Side A - Connector 1	USB C (MALE) - RIGHT ANGLE
Side B - Connector 1	USB C (MALE)
Connector Plating	Nickel
Contact Plating	Gold
Connector Style	Angled
<b>PHYSICAL</b>	
Material of Construction	PVC
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	4.0MM
Cable Length (ft.)	6.6
Cable Length (m)	2.01
Cable Length (in.)	78.7
Shipping Dimensions (hwd / in.)	0.50 x 7.00 x 9.50
Shipping Weight (kg)	0.08
Unit Packaging Type	Polybag
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	14° to 140°F (-10° to 60°C)
Storage Temperature Range	-4° to 158°F (-20° to 70°C)
Operating Humidity Range	10% to 85%, Non-Condensing
Storage Humidity Range	10% to 85%, Non-Condensing
Power Provided to Connected Device(s)	100W (20V/5A)
<b>FEATURES &amp; SPECIFICATIONS</b>	
USB Specification	USB 2.0 (up to 480 Mbps)
<b>STANDARDS &amp; COMPLIANCE</b>	



Powering Business Worldwide

TRIPP LITE  
SERIES

Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[U040-02M-C-5ARA](#)