

Universal Reversible USB 2.0 Converter Adapter Cable (Reversible A to Down-angle 5Pin Mini B M/M), 3 ft. (0.91 m)

MODEL NUMBER: UR030-003-DNB



Universal / Reversible "A" connector allows plugging in any direction

Description

The UR030-003-DNB USB 2.0 Universal / Reversible "A" to Down-Angle Mini-B 5-pin device cable meets or exceeds USB 2.0 Specifications. Connects a digital camera, PDA, smartphone or other compatible device to a USB port on a computer or hub. Backward compatible with older USB 1.1 applications as well. Includes superior foil shielding for reliable, error-free data communications. Features nickel-plated connectors and gold-plated copper contacts for superior conductivity. The cable is manufactured with molded connectors and integral strain relief for extra durability and long life.

Features

- Universal / Reversible "A" connector plugs in any direction
- Down-Angle Mini B connector ideal in situations where space is at a premium, and reduces stress / excessive bending on the cable
- Meets or Exceeds USB 2.0 Specifications
- Connects to Cameras, Cell Phones, PDA's, etc with 5-Pin Mini-B USB connectors
- Supports faster data transfer rate (1.5 to 480 Mbps) for low speed and high speed devices including multimedia applications
- Premium double-shielded cables with tinned copper braid and aluminum Mylar foil
- Nickel plated connectors and gold plated copper contacts for superior conductivity.
- Molded connectors and integral strain relief for extra durability and long life.

Specifications

OVERVIEW	
UPC Code	037332182227
Technology	USB 2.0 (High Speed)
Cable Type	Passive

Highlights

- Universal / Reversible A connector eliminates guess-work as to connector orientation
- Down-Angle Mini B connector ideal in situations where space is at a premium, and reduces stress / excessive bending on the cable
- Meets or Exceeds USB 2.0 Specifications
- Connects to Cameras, PDA's, etc with Mini-B 5-Pin connectors

System Requirements

- Any USB device requiring a USB cable with Mini-B 5-Pin connector
- USB2.0 performance only when used with USB2.0 device and USB2.0 controller

Package Includes

- 3-ft. (0.91 m) USB2.0 Universal / Reversible A to Down-Angle Mini-B Device Cable (A Male to 5Pin Mini-B Male)



Powering Business Worldwide



CONNECTIONS	
Side A - Connector 1	REVERSIBLE USB A (MALE)
Side B - Connector 1	USB MINI-B 5-PIN (MALE)
Connector Style	Angled
PHYSICAL	
Cable Jacket Color	Black
Cable Length (ft.)	3
Cable Length (m)	0.91
Shipping Dimensions (hwd / in.)	7.00 x 9.00 x 0.50
Shipping Dimensions (hwd / cm)	17.78 x 22.86 x 1.27
Shipping Weight (lbs.)	0.11
Shipping Weight (kg)	0.05
ENVIRONMENTAL	
Operating Temperature Range	14° to 122°F (-10° to 50°C)
Storage Temperature Range	5° to 140°F (-15° to 60°C)
Operating Humidity Range	0% to 90% RH, Non-Condensing
Storage Humidity Range	0% to 90% RH, Non-Condensing
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[UR030-003-DNB](#)