



Search by SKU, Product Name or Keyword

**SEARCH**

**CART**

**ESSENTRA**

[Products](#) [Catalogs](#) [Free Samples](#) [Free CAD](#) [Knowledge Center](#) [Contact Us](#)

[Home](#) [Fiber, Wire & Cable Manage...](#) [Grommets](#) [Open Grommets](#)



**Open Hole Grommet, Black, Rubber, 1.500 in ID, 2.375 in OD, .375 in Thick, 2.000 in Hole Dia**

In Stock !

Item Code: GR3301A

Black Rubber Hole Grommet convert raw-edged 1.500 in (38.1 mm) diameter holes in panels and enclosures into smooth openings to protect up to N/A cables as they pass through.



Description	Quantity	Unit Price	Options
<b>Type</b> : Hole Grommet	<b>Standard Pack:</b> 450		<input type="text" value="1"/>
<b>Compatible Hole Diameter</b> : 2.000 in (50.8 mm)	<b>Order any quantity</b>		<b>Add to Cart</b>
<b>Inside Diameter</b> : 1.500 in (38.1 mm)	<b>1</b>	<b>: \$7.7234</b>	<input type="button" value="Request CAD"/>
<b>Panel Thickness</b> : .094 in (2.4 mm)	<b>25</b>	<b>: \$3.7768</b>	<input type="button" value="Free Sample"/>
<b>Color</b> : Black	<b>100</b>	<b>: \$1.8884</b>	<input type="button" value="Request Quote"/>
<b>Material</b> : Rubber	<b>200</b>	<b>: \$1.1988</b>	
<b>Overall Diameter</b> : 2.375 in (60.3 mm)	<b>450</b>	<b>: \$0.6864</b>	
<b>Overall Height</b> : .375 in (9.5 mm)	<b>1350</b>	<b>: \$0.6525</b>	
<b>Hole Diameter</b> : 2.000 in (50.8 mm)	<b>2250</b>	<b>: \$0.6185</b>	
<b>Full Material</b> : SBR	<b>3150</b>	<b>: \$0.584</b>	

**Print Page**

**Dependent Products**



Cable Clamps -  
Screw Mount, Wire  
Harness



Open Grommets -  
Hole Grommets



Standard Cable Ties  
- Locking, Nylon



Cable Clamps -  
Adhesive Mount,  
Adjustable

**Recently Viewed**

Help us improve our site

[Sign me up!](#)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Essentra:](#)

[GR3301A](#)