

QKITS, REFILL BAGS, Q BOX & MINI SPOOLS

Q2-F TYPE TUBING KIT, 6" LENGTH PCS.
ASSORTED SIZES / KITS 1 & 2 BLACK, KIT 4 ASSORTED COLORS
THIN WALL, ENVIRONMENT FRIENDLY, HIGHLY FLAME RETARDANT, POLYOLEFIN TUBING
SHRINK RATIO 2:1, OPERATING TEMPERATURE: -55°C to +135°C, MILITARY STANDARD: 23053/5



SMALL SIZES

P/N Q2-F-QK1-01-6IN-180
 Q2-F Kit 1 consists of 180 pcs.



Q2-F KIT 1
180 PCS.

Size		QTY	Color
Inch	mm		
3/64	1.6	40 pcs.	Black
1/16	2.0	36 pcs.	Black
3/32	3.1	32 pcs.	Black
1/8	3.7	28 pcs.	Black
3/16	5.2	24 pcs.	Black
1/4	6.8	20 pcs.	Black

REFILL BAGS



6" LENGTH

Q2-F, Kit 1 Refill Bags
 Consist of 6" length pcs.

Part Number	QTY	Color
Q2-F-RK1-3/64-01-6IN-40	40 pcs.	Black
Q2-F-RK1-1/16-01-6IN-36	36 pcs.	Black
Q2-F-RK1-3/32-01-6IN-32	32 pcs.	Black
Q2-F-RK1-1/8-01-6IN-28	28 pcs.	Black
Q2-F-RK1-3/16-01-6IN-24	24 pcs.	Black
Q2-F-RK1-1/4-01-6IN-20	20 pcs.	Black

LARGE SIZES

P/N Q2-F-QK2-01-6IN-82
 Q2-F Kit 2 consists of 82 pcs.



Q2-F KIT 2
82 PCS.

Size		QTY	Color
Inch	mm		
5/16	8.8	18 pcs.	Black
3/8	10.7	16 pcs.	Black
1/2	13.7	14 pcs.	Black
5/8	16.7	14 pcs.	Black
3/4	20.5	12 pcs.	Black
1	25.4	8 pcs.	Black

REFILL BAGS



6" LENGTH

Q2-F, Kit 2 Refill Bags
 Consist of 6" length pcs.

Part Number	QTY	Color
Q2-F-RK2-5/16-01-6IN-18	18 pcs.	Black
Q2-F-RK2-3/8-01-6IN-16	16 pcs.	Black
Q2-F-RK2-1/2-01-6IN-14	14 pcs.	Black
Q2-F-RK2-5/8-01-6IN-14	14 pcs.	Black
Q2-F-RK2-3/4-01-6IN-12	12 pcs.	Black
Q2-F-RK2-1-01-6IN-8	8 pcs.	Black

ASSORTED COLORS

P/N Q2-F-QK4-11-6IN-141
 Q2-F Kit 4 consists of 141 pcs.



Q2-F KIT 4
141 PCS.

Size		QTY	Color
Inch	mm		
1/16	2.0	39 pcs.	Assorted
1/8	3.7	31 pcs.	Assorted
1/4	6.8	23 pcs.	Assorted
3/8	10.7	19 pcs.	Assorted
1/2	13.7	19 pcs.	Assorted
1	25.4	10 pcs.	Assorted

REFILL BAGS



6" LENGTH

Q2-F, Kit 4 Refill Bags
 Consist of 6" length pcs.

Part Number	QTY	Color
Q2-F-RK4-1/16-11-6IN-39	39 pcs.	Assorted
Q2-F-RK4-1/8-11-6IN-31	31 pcs.	Assorted
Q2-F-RK4-1/4-11-6IN-23	23 pcs.	Assorted
Q2-F-RK4-3/8-11-6IN-19	19 pcs.	Assorted
Q2-F-RK4-1/2-11-6IN-19	19 pcs.	Assorted
Q2-F-RK4-1-11-6IN-10	10 pcs.	Assorted

Q BOX

Q BOX



VARIOUS LENGTHS
PER SIZE

Part Number	Size (Inch)	Box Length (Feet)
Q2-F-3/64-01-QX50FT	3/64	50
Q2-F-1/16-01-QX50FT	1/16	50
Q2-F-3/32-01-QX50FT	3/32	50
Q2-F-1/8-01-QX50FT	1/8	50
Q2-F-3/16-01-QX30FT	3/16	30
Q2-F-1/4-01-QX30FT	1/4	30
Q2-F-5/16-01-QX30FT	5/16	30
Q2-F-3/8-01-QX30FT	3/8	30
Q2-F-1/2-01-QX15FT	1/2	15
Q2-F-5/8-01-QX15FT	5/8	15
Q2-F-3/4-01-QX15FT	3/4	15



MINI SPOOLS

Part Number	Size (Inch)	Spool Length (Feet)
Q2-F-3/64-01-MS100FT	3/64	100
Q2-F-1/16-01-MS100FT	1/16	100
Q2-F-3/32-01-MS100FT	3/32	100
Q2-F-1/8-01-MS100FT	1/8	100
Q2-F-3/16-01-MS100FT	3/16	100
Q2-F-1/4-01-MS100FT	1/4	100
Q2-F-5/16-01-MS100FT	5/16	100
Q2-F-3/8-01-MS100FT	3/8	100
Q2-F-1/2-01-MS100FT	1/2	100
Q2-F-5/8-01-MS50FT	5/8	50
Q2-F-3/4-01-MS50FT	3/4	50
Q2-F-1-01-MS50FT	1	50
Q2-F-1 1/2-01-MS50FT	1 1/2	50
Q2-F-2-01-MS50FT	2	50

Q2-F3X TYPE TUBING KIT, 6" LENGTH PCS.
ASSORTED SIZES / BLACK
THIN WALL, HIGHLY FLEXIBLE, FLAME RETARDANT POLYOLEFIN TUBING
SHRINK RATIO 3:1, OPERATING TEMPERATURE: -55°C to +135°C, MILITARY STANDARD: 23053/5



ASSORTED SIZES

P/N Q2-F3X-QK1-01-6IN-106
 Q2-F3X Kit 1 consists of 106 pcs.



Q2-F3X KIT 1
106 PCS.

Size		QTY	Color
Inch	mm		
1/16	2.0	28 pcs.	Black
1/8	3.7	24 pcs.	Black
1/4	6.8	20 pcs.	Black
1/2	10.7	14 pcs.	Black
3/4	13.7	12 pcs.	Black
1	25.4	8 pcs.	Black

REFILL BAGS



6" LENGTH

Q2-F3X, Kit 1 Refill Bags
 Consist of 6" length pcs.

Part Number	QTY	Color
Q2-F3X-RK1-1/16-01-6IN-28	28 pcs.	Black
Q2-F3X-RK1-1/8-01-6IN-24	24 pcs.	Black
Q2-F3X-RK1-1/4-01-6IN-20	20 pcs.	Black
Q2-F3X-RK1-1/2-01-6IN-14	14 pcs.	Black
Q2-F3X-RK1-3/4-01-6IN-12	12 pcs.	Black
Q2-F3X-RK1-1-01-6IN-8	8 pcs.	Black

QKITS & REFILL BAGS

Q2-Z TYPE TUBING KIT, 6" LENGTH PCS.
ASSORTED SIZES / BLACK
THIN WALL, GENERAL PURPOSE, FLAME RETARDANT, POLYOLEFIN TUBING
SHRINK RATIO 2:1, OPERATING TEMPERATURE: -55°C to +125°C



SMALL SIZES

P/N Q2-Z-QK1-01-6IN-180
 Q2-Z Kit 1 consists of 180 pcs.



Q2-Z KIT 1
180 PCS.

Size		QTY	Color
Inch	mm		
3/64	1.6	40 pcs.	Black
1/16	2.0	36 pcs.	Black
3/32	3.1	32 pcs.	Black
1/8	3.7	28 pcs.	Black
3/16	5.2	24 pcs.	Black
1/4	6.8	20 pcs.	Black

REFILL BAGS



6" LENGTH

Q2-Z, Kit 1 Refill Bags
 Consist of 6" length pcs.

Part Number	QTY	Color
Q2-Z-RK1-3/64-01-6IN-40	40 pcs.	Black
Q2-Z-RK1-1/16-01-6IN-36	36 pcs.	Black
Q2-Z-RK1-3/32-01-6IN-32	32 pcs.	Black
Q2-Z-RK1-1/8-01-6IN-28	28 pcs.	Black
Q2-Z-RK1-3/16-01-6IN-24	24 pcs.	Black
Q2-Z-RK1-1/4-01-6IN-20	20 pcs.	Black

LARGE SIZES

P/N Q2-Z-QK2-01-6IN-82
 Q2-Z Kit 2 consists of 82 pcs.



Q2-Z KIT 2
82 PCS.

Size		QTY	Color
Inch	mm		
5/16	8.8	18 pcs.	Black
3/8	10.7	16 pcs.	Black
1/2	13.7	14 pcs.	Black
5/8	16.7	14 pcs.	Black
3/4	20.5	12 pcs.	Black
1	25.4	8 pcs.	Black

REFILL BAGS



6" LENGTH

Q2-Z, Kit 2 Refill Bags
 Consist of 6" length pcs.

Part Number	QTY	Color
Q2-Z-RK2-5/16-01-6IN-18	18 pcs.	Black
Q2-Z-RK2-3/8-01-6IN-16	16 pcs.	Black
Q2-Z-RK2-1/2-01-6IN-14	14 pcs.	Black
Q2-Z-RK2-5/8-01-6IN-14	14 pcs.	Black
Q2-Z-RK2-3/4-01-6IN-12	12 pcs.	Black
Q2-Z-RK2-1-01-6IN-8	8 pcs.	Black

Q5-2X TYPE TUBING KIT, 6" LENGTH PCS.
ASSORTED SIZES / BLACK
DUAL WALL, ADHESIVE-LINED, FLEXIBLE POLYOLEFIN TUBING
SHRINK RATIO 2:1, OPERATING TEMPERATURE: -55°C to +125°C, MILITARY STANDARD: 23053/4



ASSORTED SIZES

P/N Q5-2X-QK1-01-6IN-114
 Q5-2X Kit 1 consists of 114 pcs.



Q5-2X KIT 1
114 PCS.

Size		QTY	Color
Inch	mm		
1/8	3.7	28 pcs.	Black
3/16	5.2	24 pcs.	Black
1/4	6.8	20 pcs.	Black
3/8	10.7	16 pcs.	Black
1/2	13.7	14 pcs.	Black
3/4	20.5	12 pcs.	Black

REFILL BAGS



6" LENGTH

Q5-2X, Kit 1 Refill Bags
 Consist of 6" length pcs.

Part Number	QTY	Color
Q5-2X-RK1-1/8-01-6IN-28	28 pcs.	Black
Q5-2X-RK1-3/16-01-6IN-24	24 pcs.	Black
Q5-2X-RK1-1/4-01-6IN-20	20 pcs.	Black
Q5-2X-RK1-3/8-01-6IN-16	16 pcs.	Black
Q5-2X-RK1-1/2-01-6IN-14	14 pcs.	Black
Q5-2X-RK1-3/4-01-6IN-12	12 pcs.	Black

Q5-3X TYPE TUBING KIT, 6" LENGTH PCS.
ASSORTED SIZES / BLACK
DUAL WALL, ADHESIVE-LINED, FLEXIBLE POLYOLEFIN TUBING
SHRINK RATIO 3:1, OPERATING TEMPERATURE: -55°C to +125°C, MILITARY STANDARD: 23053/4



ASSORTED SIZES

P/N Q5-3X-QK1-01-6IN-114
 Q5-3X Kit 1 consists of 114 pcs.



Q5-3X KIT 1
114 PCS.

Size		QTY	Color
Inch	mm		
1/8	3.7	28 pcs.	Black
3/16	5.2	24 pcs.	Black
1/4	6.8	20 pcs.	Black
3/8	10.7	16 pcs.	Black
1/2	13.7	14 pcs.	Black
3/4	20.5	12 pcs.	Black

REFILL BAGS



6" LENGTH

Q5-3X, Kit 1 Refill Bags
 Consist of 6" length pcs.

Part Number	QTY	Color
Q5-3X-RK1-1/8-01-6IN-28	28 pcs.	Black
Q5-3X-RK1-3/16-01-6IN-24	24 pcs.	Black
Q5-3X-RK1-1/4-01-6IN-20	20 pcs.	Black
Q5-3X-RK1-3/8-01-6IN-16	16 pcs.	Black
Q5-3X-RK1-1/2-01-6IN-14	14 pcs.	Black
Q5-3X-RK1-3/4-01-6IN-12	12 pcs.	Black

Q5-F3X TYPE TUBING KIT, 6" LENGTH PCS.
ASSORTED SIZES / BLACK
DUAL WALL, ADHESIVE-LINED, FLEXIBLE POLYOLEFIN TUBING
SHRINK RATIO 3:1, OPERATING TEMPERATURE: -55°C to +125°C, MILITARY STANDARD: 23053/4



ASSORTED SIZES

P/N Q5-F3X-QK1-01-6IN-114
 Q5-F3X Kit 1 consists of 114 pcs.



Q5-F3X KIT 1
114 PCS.

Size		QTY	Color
Inch	mm		
1/8	3.7	28 pcs.	Black
3/16	5.2	24 pcs.	Black
1/4	6.8	20 pcs.	Black
3/8	10.7	16 pcs.	Black
1/2	13.7	14 pcs.	Black
3/4	20.5	12 pcs.	Black

REFILL BAGS



6" LENGTH

Q5-F3X, Kit 1 Refill Bags
 Consist of 6" length pcs.

Part Number	QTY	Color
Q5-F3X-RK1-1/8-01-6IN-28	28 pcs.	Black
Q5-F3X-RK1-3/16-01-6IN-24	24 pcs.	Black
Q5-F3X-RK1-1/4-01-6IN-20	20 pcs.	Black
Q5-F3X-RK1-3/8-01-6IN-16	16 pcs.	Black
Q5-F3X-RK1-1/2-01-6IN-14	14 pcs.	Black
Q5-F3X-RK1-3/4-01-6IN-12	12 pcs.	Black

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Qualtek:](#)

[Q2-F-RK4-1-11-6IN-10](#)