



DIP Reed Relays

[Products](#) [Databook Page DIP Reed Relays](#) [3D Model DIP Reed Relays](#) [Enquiry](#)



Description

The DIP Series is a very compact design having a low profile package and a high profile package. This series is compatible with all current brand DIP relays.

Features

- Low & high profile package
- Standard pin configurations
- Versions with diode available
- IC-pin compatible
- TTL drive possible
- 4.25 kVDC breakdown voltage – UL approval

Applications

- Test & Measurement
- Telecommunications
- Security

Specifications

Coil Voltage (VDC)	3 to 24
Coil Resistance (Ohm)	200 to 2000
Contact Form	1A, 1B, 1C, 2A
Rated Power (W)	0 to 15
Switching Voltage (VDC)	0 to 500
Switching Current (A)	0 to 1.0
Carry Current (A)	0 to 1.25
Breakdown Voltage (Minimum VDC)	250 to 1500

[Part Search](#) [Literature](#) [Applications](#) [Stock Check](#)

Product search DIP Reed Relays

No. / Desc.:

Item no.	Description	Number of contacts	Contact - form	Contact rating W	Switching voltage V
3205001051	DIP05-1C90-51L	1	Form C - Changeover	10 W	175 V
3205001151	DIP05-1C90-51D	1	Form C - Changeover	10 W	175 V
3205010013	DIP05-1B72-13L	1	B - NC	10 W	200 V
3205010019	DIP05-1B72-19L	1	B - NC	10 W	200 V
3205010119	DIP05-1B72-19D	1	B - NC	10 W	200 V
3205100012	DIP05-1A72-12L	1	A - NO	10 W	200 V
3205100112	DIP05-1A72-12D	1	A - NO	10 W	200 V
3205100113	DIP05-1A72-13D	1	A - NO	10 W	200 V
3205100312	DIP05-1A72-12A	1	A - NO	10 W	100 V
3205172010	DIP05-1A72-10L	1	A - NO	10 W	200 V
3205172011	DIP05-1A72-11L	1	A - NO	10 W	200 V
3205172013	DIP05-1A72-13L	1	A - NO	10 W	200 V
3205172111	DIP05-1A72-11D	1	A - NO	10 W	200 V
3205172211	DI05-1A72-11M	1	A - NO	10 W	200 V
3205172411	DIP05-1A72-11LHR	1	A - NO	10 W	200 V
3205172412	DIP05-1A72-12LHR	1	A - NO	10 W	200 V
3205172512	DIP05-1A72-12DHR	1	A - NO	10 W	200 V
3205172513	DIP05-1A72-13DHR	1	A - NO	10 W	200 V
3205172612	DIP05-1A72-12MHR	1	A - NO	10 W	200 V
3205172711	DIP05-1A72-11F	1	A - NO	10 W	200 V
3205172812	DIP05-1A72-12E	1	A - NO	10 W	200 V
3205172910	DIP05-1A72-10B	1	A - NO	10 W	200 V
3205175313	DIP05-1A75-13Q	1	A - NO	10 W	500 V
3205190251	DIP05-1C90-51M	1	Form C - Changeover	10 W	175 V
3205190351	DIP05-1C90-51Q	1	Form C - Changeover	10 W	175 V



Products for tomorrow...

- Reed Switches
- Reed Sensors & Magnets
- Reed Relays & Opto-couplers

General Purpose Reed Relays

- DIL Reed Relays
- NP Reed Relay
- DIP Reed Relays
- SIL Reed Relays
- MS Reed Relays
- BE Reed Relays

SMD Reed Relays








- Low Thermal Voltage Relays
- High Insulation Reed Relays
- High Voltage Reed Relays
- High Frequency Reed Relays

Reed Relay Module

- Ex-approved Reed Relays
- Latching Reed Relays
- Current Loop Reed Relays
- Opto-Couplers

- Liquid Level Sensors & Floats

?						
?	3205190751	DIP05-1C90-51F	1	Form C - Changeover	10 W	175 V
?	3205190851	DIP05-1C90-51E	1	Form C - Changeover	10 W	175 V
?	3205196151	DIP05-1C96-51D	1	Form C - Changeover	10 W	175 V
?	3205196751	DIP05-1C96-51F	1	Form C - Changeover	10 W	175 V
?	3205197151	DIP05-1C97-51D	1	Form C - Changeover	10 W	100 V
?	3205200021	DIP05-2A72-21L	2	A - NO	10 W	200 V
?	3205200121	DIP05-2A72-21D	2	A - NO	10 W	200 V
?	3205200321	DIP05-2A72-21F	2	A - NO	10 W	200 V
?	3205272321	DIP05-2A72-21A	2	A - NO	10 W	200 V
?	3205272621	DIP05-2A72-21R	2	A - NO	10 W	200 V
?	3212001051	DIP12-1C90-51L	1	Form C - Changeover	10 W	175 V
?	3212001151	DIP12-1C90-51D	1	Form C - Changeover	10 W	175 V
?	3212010019	DIP12-1B72-19L	1	B - NC	10 W	200 V
?	3212010119	DIP12-1B72-19D	1	B - NC	10 W	200 V
?	3212010219	DIP12-1B72-19M	1	B - NC	10 W	200 V
?	3212100012	DIP12-1A72-12L	1	A - NO	10 W	200 V
?	3212100112	DIP12-1A72-12D	1	A - NO	10 W	200 V
?	3212172010	DIP12-1A72-10L	1	A - NO	10 W	200 V
?	3212172011	DIP12-1A72-11L	1	A - NO	10 W	200 V
?	3212172013	DIP12-1A72-13L	1	A - NO	10 W	200 V
?	3212172111	DIP12-1A72-11D	1	A - NO	10 W	200 V
?	3212172312	DIP12-1A72-12A	1	A - NO	10 W	200 V
?	3212172410	DIP12-1A72-10C	1	A - NO	10 W	200 V
?	3212172412	DIP12-1A72-12LHR	1	A - NO	10 W	200 V
?	3212172510	DIP12-1A72-10A	1	A - NO	10 W	200 V
?	3212172512	DIP12-1A72-12DHR	1	A - NO	10 W	200 V
?	3212172712	DIP12-1A72-12F	1	A - NO	10 W	200 V
?	3212172911	DIP12-1A72-11S	1	A - NO	10 W	200 V
?	3212190251	DIP12-1C90-51M	1	Form C - Changeover	10 W	175 V
?	3212190651	DIP12-1C90-51DHR	1	Form C - Changeover	10 W	175 V
?	3212190751	DIP12-1C90-51F	1	Form C - Changeover	10 W	175 V
?	3212190951	DIP12-1C90-51QHR	1	Form C - Changeover	10 W	175 V
?	3212200021	DIP12-2A72-21L	2	A - NO	10 W	200 V
?	3212200121	DIP12-2A72-21D	2	A - NO	10 W	200 V
?	3212200321	DIP12-2A72-21F	2	A - NO	10 W	200 V
?	3212272221	DIP12-2A72-21M	2	A - NO	10 W	200 V
?	3215010119	DIP15-1B72-19D	1	B - NC	10 W	200 V
?	3215100111	DIP15-1A72-11D	1	A - NO	10 W	200 V
?	3215172010	DIP15-1A72-10L	1	A - NO	10 W	200 V
?	3215172012	DIP15-1A72-12L	1	A - NO	10 W	200 V
?	3215172013	DIP15-1A72-13L	1	A - NO	10 W	200 V
?	3215172019	DIP15-1B72-19L	1	B - NC	15 W	200 V
?	3215172112	DIP15-1A72-12D	1	A - NO	10 W	200 V
?	3215172410	DIP15-1A72-10C	1	A - NO	10 W	200 V
?	3215172510	DIP15-1A72-10A	1	A - NO	10 W	200 V
?	3215172711	DIP15-1A72-11F	1	A - NO	10 W	200 V
?	3215190051	DIP15-1C90-51L	1	Form C - Changeover	10 W	175 V
?	3215190151	DIP15-1C90-51D	1	Form C - Changeover	10 W	175 V
?	3215190751	DIP15-1C90-51F	1	Form C - Changeover	10 W	175 V
?	3215190851	DIP15-1C90-51S	1	Form C - Changeover	10 W	175 V
?	3215272021	DIP15-2A72-21L	2	A - NO	10 W	200 V
?	3215272121	DIP15-2A72-21D	2	A - NO	10 W	200 V
?	3224001051	DIP24-1C90-51L	1	Form C - Changeover	10 W	175 V
?	3224001151	DIP24-1C90-51D	1	Form C - Changeover	10 W	175 V
?	3224010019	DIP24-1B72-19L	1	B - NC	10 W	200 V
?	3224100012	DIP24-1A72-12L	1	A - NO	10 W	200 V
?	3224100013	DIP24-1A72-13L	1	A - NO	10 W	200 V
?	3224100111	DIP24-1A72-11D	1	A - NO	10 W	200 V
?	3224100112	DIP24-1A72-12D	1	A - NO	10 W	200 V
?	3224166016	DIP24-1A66-16L	1	A - NO	10 W	100 V
?	3224172010	DIP24-1A72-10L	1	A - NO	15 W	200 V
?	3224172212	DIP24-1A72-12M	1	A - NO	10 W	200 V
?	3224175019	DIP24-1B75-19L	1	B - NC	10 W	500 V
?	3224190251	DIP24-1C90-51M	1	Form C - Changeover	10 W	175 V

						
  3224190751	DIP24-1C90-51F	1	Form C - Changeover	10 W	175 V	
  3224200021	DIP24-2A72-21L	2	A - NO	10 W	200 V	
  3224200121	DIP24-2A72-21D	2	A - NO	15 W	200 V	

 [Products](#)  [Databook Page DIP Reed Relays](#)  [3D Model DIP Reed Relays](#)  [Enquiry](#)

Hotline: | [Europe: +49 \(0\)7731 8399 0](#) | [America: \(800\) 870-5385](#) | [Asia: +852 2955 1682](#)