



# Heyco® CPV Solar Connector Sets


## With Custom Termination Capability

TYPE	CABLE		PART NO.	TERMINATIONS		D in.	LENGTH * A ft.
	Gauge AWG	Type		B	C		
CPV-P Connection Cable	10	USE-2	<b>S6310-6.0</b>	CPV-P	none*	1/2	6.0
		PV 1000	<b>S6311-6.0</b>				
CPV-N Connection Cable	10	USE-2	<b>S6314-6.0</b>	CPV-N	none*	1/2	6.0
		PV 1000	<b>S6315-6.0</b>				
CPV-P/CPV-N Jumper Cable	10	USE-2	<b>S6318-6.0</b>	CPV-P	CPV-N	n/a	6.0
		PV 1000	<b>S6319-6.0</b>				
CPV/MC4 Conversion Cable	10	USE-2	<b>S6322-6.0</b>	CPV-P	MC-4-NEG	n/a	6.0
			<b>S6323-6.0</b>	CPV-N	MC-4-POS		
		PV 1000	<b>S6326-6.0</b>	CPV-P	MC-4-NEG		
			<b>S6327-6.0</b>	CPV-N	MC-4-POS		


\*Other lengths available. Consult Heyco for custom lengths, applied Ring/Spade Terminals and other configurations.

- Precut and terminated CPV assemblies.
- Constructed from UV resistant 10AWG UL/TUV approved solar cable.
- Suitable for UL and IEC solar installations.
- Heyco Connectors are UL and TUV approved.
- Connectors meet UL cold impact test of -35°C.
- Connectors meet all NEC requirements for solar installations.
- Maximum cable assembly current rating - 30 amps.
- MC4 conversion cables and additional cable lengths available upon request.

### CPV CONNECTION CABLES



### CPV JUMPER & CONVERSION CABLES



Material	Polycarbonate
Certifications	Recognized under the Component Program of Underwriters' Laboratories File E344722.
	Certification Number R60033714.
Flammability Rating	V0
Temperature Rating	-40°F (-40°C) to 185°F (85°C)
Maximum Temperature Rating	221°F (105°C)
IP Rating	IP 65 & IP 67

*Quick Specs*