




REV.	DATE	ECR NO.	DESCRIPTION
NC	02/06/97	XXXXXX	INITIAL RELEASE
A	01/10/14	2553	UPDATE DRAWING FORMAT AND CORRECT INSULATOR'S DIMENSION



- NOTES:
1. IMPEDANCE:50 OHM
 2. FREQUENCY RANGE: DC 0 – 11 GHz
 3. DIELECTRIC WITHSTANDING VOLTAGE:1500 VRMS. MIN.
 4. DURABILITY:500 CYCLES MIN.
 5. TEMPERATURE RANGE:–65°C TO +165°C

					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: <0.5 ± 0.05mm 0.5 – 6mm ± 0.10mm 6 – 30mm ± 0.20mm 30 – 120mm ± 0.30mm ANGLES ± 1° UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: <.020 ± 0.002" .020 – .236 = ± 0.004" .236 – 1.180 = ± 0.007" 1.180 – 4.724 = ± 0.012" ANGLES ± 1° DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex									
						DRAWN	S.LI		01/10/14										
						CHECKED													
						ISSUED					PART DESCRIPTION TNC PANEL RECEPT JACK								
						SHEET	1 OF 1												
										PART NO. 122385									
						CAD FILE C:/CONNEX/122385.DWG				DWG. NO.		122385.DWG		REV.	A	SIZE	A	SCALE	NA
4	LOCK RING	BRASS	NICKEL	1															
3	CONTACT PIN	PHOSPHOR BRONZE	GOLD	1															
2	INSULATOR	PTFE	NATURAL	1															
1	BODY	BRASS	NICKEL	1															
	DESCRIPTION	MATERIAL	FINISH	QTY															