



General Information

Kit Part Number:	2-2110838-9
Description:	Pre-Insulated Long Spring Spade Tongue Terminals Kit
Application:	HVAC Systems, Instrumentation and Controls, Lighting Applications, Motors, Panel Boxes, Power Supplies, Switchgear, Transportation
Family:	PLASTI-GRIP
TE Brand:	AMP Products
Solution:	MRO (Maintenance, Repair and Operation)
Product Type:	Terminals & Splices
Number of Pieces:	120
RoHS:	Yes

Specifications

Body and Plating:	Tin Plated, Brass, Phosphor Bronze
Insulation:	Vinyl
Stud/Tab Size:	8, 10
Temperature Rating:	90 Degrees C (Max)
Terminal Type:	Long Spring Spade Tongue
Tool Included:	No
Voltage Rating:	600V
Wire Gauge (AWG):	12-10, 16-14 , 22-16

Product Highlights

Product Highlights

Pre-insulated PLASTI-GRIP solderless terminals and splices are designed specifically to answer the need for inexpensive, insulated electrical terminations. They can be used in almost every type of commercial application and accommodate wire sizes from 22 AWG through 2/0 AWG. Carefully engineered application tooling has been developed to ensure uniformly high quality terminations. Tool and terminal have been designed as a team to promote ease and speed of application and at the same time to provide precise crimping pressure for every wire size. The wire and the terminal barrel form a homogeneous mass of metal, providing a connection of maximum conductivity, tensile strength, and high resistance to corrosion. The quality performance, the facility of installation and the inherent simplicity make them ideal for many industrial applications. PLASTI-GRIP products are available as rings, spades, flanged spaded, slotted rings, splices and several other varieties. Wire ranges for the terminals and splices are 22 AWG through 2/0 and stud sizes from #2 through 3/8".

Features and Benefits

- Vinyl insulation sleeve provides good dielectric strength and supports the wire insulation so that no bare wire is exposed
- Most product rated to 90 degrees C, with an operating voltage of 600 V
- Insulation is 94V-0 rated
- Funneled wire entry on terminal prevents turned back wire strands and permits rapid wire insertion during high speed production
- Serrations in the crimp barrel provide maximum contact and tensile strength after crimping

Applications

- HVAC
- Instruments / Controls

- Page 2 - Retrieved on Dec 07, 2011



Bill of Materials

Part No.	Qty In Kit	Description	Datasheet	P/N Details	Search Distributors Inventory
52454	20	Long Spring Spade Tongue Terminals, AWG 22-16 Stud size 8		Details	Search
52455	20	Long Spring Spade Tongue Terminals, AWG 22-16 Stud size 10		Details	Search
52464	20	Long Spring Spade Tongue Terminals, AWG 16-14 Stud 8		Details	Search
52465	20	Long Spring Spade Tongue Terminals, AWG 16-14 Stud 10		Details	Search
52474	20	Long Spring Spade Tongue Terminals, AWG 12-10 Stud 8		Details	Search
52475	20	Long Spring Spade Tongue Terminals, AWG 12-10 Stud 10		Details	Search

Recommended Tool

Part No.	Included in Kit
58433-3	No





