

8300 Vandal Resistant Switches - Designed to IP66



H8300RP ---

- ▶ Momentary or latching action
- ▶ Ratings up to 16A, 250Vac
- ▶ Single and double pole
- ▶ Stainless steel button & bezel
- ▶ Vandal resistant construction
- ▶ Choice of body styles
- ▶ 19.2mm or 22.5mm mounting holes
- ▶ Front panel sealed to IP66
- ▶ Raised, flat or domed actuator options

Approvals and specifications



16(4)A 250Vac T85, 1E4 (10,000 Operations)
 12(12)A 250Vac T105, 1E4 (10,000 Operations)
 8(8)A 250Vac T105, 5E4 (50,000 Operations)
 6(6)A 250Vac T125, 5E4 (50,000 Operations)



12A 250Vac DP, 13A 250Vac SP
 250Vac 1hp, 125Vac 1/2hp
 UL 85°C, file E45221, CSA file LR10990

In house test:

10(10)A 250Vac — Indicative rating only

3mm contact gap.
 Technical data on pages 4 & 5 (switches), 6 (indicators).

H 8300 R P

TERMINAL FUNCTION ACTUATOR BODY

vandal resistant switches

TERMINAL	FUNCTION	ACTUATOR	BODY
<p>C</p> <p>6.3 x 0.8</p> <p>H</p> <p>4.8 x 0.8</p>	<p>8300</p> <p>ON - OFF (alternate) Single pole</p>	<p>R (for P body only) Raised top (stainless steel)</p>	<p>P (for R actuator only) Stainless steel, Soft profile bezel</p> <p>Panel cut-out Panel thickness 0.75 - 8.0mm</p>
<p>K</p> <p>2.6</p> <p>1.5</p> <p>Solder</p> <p>T</p> <p>2.6</p> <p>1.5</p> <p>Solder</p>	<p>8301</p> <p>ON - OFF (momentary ON) Single pole</p>	<p>V Flat top (stainless steel)</p>	<p>M Stainless steel</p> <p>Panel cut-out Panel thickness 0.75 - 8.0mm</p>
<p>V</p> <p>4.3</p> <p>3.7 Ctrs</p> <p>Dual pin PCB</p> <p>X</p> <p>4.5</p> <p>0.8Sq PCB</p>	<p>8350</p> <p>ON - OFF (alternate) Double pole</p>	<p>P Domed top (stainless steel)</p>	<p>Panel cut-out Panel thickness 0.75 - 8.0mm</p>
	<p>8351</p> <p>ON - OFF (momentary ON) Double pole</p>		

Dimensions (mm)

8300RP (H terminals shown)

