

MODEL NUMBER
PWD-5526-04-NNN-79

NOTES:

1.0 ELECTRICAL SPECIFICATIONS:


- 1.1 FREQUENCY RANGE: 6.0 to 18.0 GHz
- 1.2 INSERTION LOSS: 1.5dB MAX.
- 1.3 AMPLITUDE BALANCE: 0.5dB
- 1.4 PHASE BALANCE: 20°
- 1.5 INPUT VSWR (AT J1): 1.75:1 MAX.
OUTPUT VSWR(AT J2-J5):
- 1.6 ISOLATION: 15dB MIN.
- 1.7 INPUT POWER: 30 WATTS MAX.

2.0 FINISHING

- 2.1 GREY OVER MIL-E-15090 TYPE II, CLASS 2
OVER MIL-C-5541 CLASS 3A
MEETS MIL-F-14072
MEETS MIL-E-5400

- 2.2 MARKING: MARK UNIT AS SHOWN
USING BLUE INK
(REF.: SLK-09015-82-01)

3.0 DIMENSIONS IN PARENTHESIS ARE
IN MILLIMETERS.



NOTICE: The information contained in this drawing is proprietary and must not be used without the permission of Cinch Connectivity Solutions.

UNLESS OTHERWISE NOTED DIMENSIONS ARE IN INCHES AND TOLERANCES ARE:
3 PLACE DECIMALS ±.005
2 PLACE DECIMALS ±.02
FRACTIONS ±1/64
PARALLELITY: T.I.R. _____
FLATNESS: T.I.R. _____
CONCENTRICITY: T.I.R. _____
ANGLES AND PERPENDICULARITY: ±1°

CAGE CODE
34078 **MIDWEST MICROWAVE**



TITLE
POWER DIVIDER
OUTLINE DRAWING

DRAWN/DATE
A.BEATTY
12/15/93
CHECKED/DATE

ENG./DATE
P.GOODMAN
1/11/94
APPROVED/DATE

DRAWING NUMBER
PWD-5526-04-NNN-79-01
REV. B

SCALE: 2=1 SHEET 1 of 1

REV.	DESCRIPTION	DATE
-	RELEASED	1/13/94
A	ECN 17674	10/11/00
B	ECN 17678	10/12/00

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cinch Connectivity Solutions:](#)

[PWD-5526-04-NNN-79](#)