




DWG STATUS						ZONE	REVISION HISTORY				AUTH			
DATE	STG	REV	N/P	CHG							DR	APVD 1	APVD 2	
13FE86	R	A	-	-			RELEASED				860005	JK	OF	AVS
16JL86	R	-	-	-			REVISED DIMS - 5 PLCS				107194	DJT	FH	
24JN92	R	A1	-	-			ADDED NOTE 6, KPC CHART AND 'FLEX AREA' NOTE				144769	TPM	TPM	
23SE93	R	A2	-	-			MAT'L SPEC WAS M-2231-002				154098	GH	GH	
19DE06	R	A3	-	-			MATERIAL SPEC WAS R0100180				288083	TLD	TLD	ET

NOTES

- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN.
- MATERIAL RECYCLING CODE PER ISO 11469. (2.3)X(0.1) CHARACTERS AS SHOWN TO BE LOCATED ON ANY EXTERIOR SURFACE. OPTIONAL CONSTRUCTION TO BE NO MATERIAL RECYCLE CODE.
- THIS PART IS NOT CONTROLLED FOR AUTOMATIC FEEDING.
- (2.3)X(0.1) DELPHI CORPORATE BRAND TO BE LOCATED ON ANY EXTERIOR SURFACE, PREFERABLY VISIBLE AT FINAL ASSEMBLY. OPTIONAL CONSTRUCTION FOR EXISTING TOOLING MAY BE "PED" OR NO LOGO.
- 0.10 MAX FLASH PERMITTED IN CABLE AREAS.

TOLERANCE UNLESS OTHERWISE SPECIFIED:
DECIMAL: ANGULAR $\pm 2^\circ$
ONE PLACE ± 0.3
TWO PLACE ± 0.15

PART DRAWING	
STYLE	
VOLUME (CM ³)	DISTR CODE
UNLESS OTHERWISE SPECIFIED THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994 AS AMENDED BY THE GM GLOBAL DIMENSIONING AND TOLERANCING ADDENDUM-2001. SEPARATE PATTERNS OF FEATURES MAY BE GAGED SEPARATELY REGARDLESS OF DATUM REFERENCES.	
ALL DIMENSIONS ARE IN MILLIMETERS	
REFERENCE	
THIRD ANGLE PROJECTION	DO NOT SCALE USE MATH DATA

DELPHI	
DELPHI PACKARD ELECTRICAL/ELECTRONIC ARCHITECTURE WARREN, OH	
DR	DATE
APVD1 JON KRAUSE	03MR86
APVD2 G FERANCE	04MR86
APVD3 A VAN SLYKE	03AP86
APVD4 J R ROSS	03AP86
APVD5	
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 10949001	
MATERIAL M4694002 PA66 HI IM BLK	
DRAWING NAME MOUN CLIP IGN 8MM	
DRAWING NUMBER 12059530	
SIZE A1	SCALE NONE
FRAME NO 1 OF 1	SHEET NO 1 OF 1
STG R	REV A3
N/P -	