

3900 Metal Lever Switches 16A 250Vac



- ▶ Metal lever switches
- ▶ Ratings up to 20A, 277V ac
- ▶ Single and double pole
- ▶ Choice of circuits including 3 position and momentary
- ▶ 6.3mm and solder terminals
- ▶ Guard option



16(4)A 250Vac T85 (3900 & 3950)
10(4)A 250Vac T85 (All other circuits)



UL CSA 20A 125/277Vac (ON-OFF Circuits)
UL CSA 16A 125/277Vac (Other Circuits)
UL CSA 7A 72Vdc, 14A 36Vdc
UL 250Vac 1hp, 125Vac 1/2hp
UL 85°C, file E45221, CSA file LR10990


Inrush rating - Contact factory for details



RoHS compliant

Approvals and ratings vary with function.
3mm contact gap except where marked μ .
Technical data on pages 4 & 5.

ORDER FORMAT



TERMINAL	FUNCTION	ACTUATOR
C 6.3 x 0.8 10.5	Single pole 3900 ON - OFF 3901 ON - OFF (momentary ON) 3902 ON - OFF (momentary OFF) 3910 ON - ON 3911 ON - ON (momentary 1 side) 3920 ON - OFF - ON μ 3921 ON - OFF - ON μ (momentary 1 side) 3922 ON - OFF - ON μ (momentary 2 sides)	Double pole 3950 ON - OFF 3951 ON - OFF (momentary ON) 3952 ON - OFF (momentary OFF) 3960 ON - ON 3961 ON - ON (momentary 1 side) 3970 ON - OFF - ON μ 3971 ON - OFF - ON μ (momentary 1 side) 3972 ON - OFF - ON μ (momentary 2 sides)
S 10.5 Screw & clamp		B 17.5 metal
T 10.5 3.1 Solder		C 14.0 metal
		D 25.4 metal
		E 38.1 metal
		F 17.5 nylon Switches with F toggles have double pole bodies, regardless of circuit Metal toggle finish is nickel plate