

5

4

3

2

1

DRAWING NO.
27-9300-XX

REVISIONS

01	OFFICIAL RELEASE				2009.09.0
	08-18-09	L	L	T	H

D



Description: See table I
 Part No: 27-9300-XX
 Application: Attenuation
 Crimp Tool: N/A
 Impedance: 50 ohm
 Frequency Range: 0~2 GHz
 Material: Body Brass Nickel plated
 Insulator Delrin
 Contact Brass Gold plated
 Nut Zinc Nickel plated
 Label Self adhesive paper
 RoHS Compliance: Yes
 Technical Detail: Refer to Emerson Document P/N 27-0000

C

受控 CONTROLLED DOCUMENT

编号 P/N	27-9300-CUST	版本 Rev	01	日期 Rel'd Date	SEP 14,09
-----------	--------------	-----------	----	------------------	-----------

B


**DIM OUTLINE**

Table I

P/N	Description	VSWR	Attenuation Tolerance
27-9300-3	3DB BNC ATTENUATOR PAD	1.1 TO 1GHz	±0.4 dB TO 1GHz
27-9300-6	6DB BNC ATTENUATOR PAD	1.2 TO 2GHz	±0.45 dB TO 2GHz
27-9300-10	10DB BNC ATTENUATOR PAD	1.35 TO 4GHz	±0.65 dB TO 4GHz
27-9300-20	20DB BNC ATTENUATOR PAD	1.65 TO 8GHz	±1.0 dB TO 8GHz

A

TOLERANCE UNLESS OTHERWISE SPECIFIED		DRAWN BY LINDA.WU	DATE 08-18-09
DECIMALS	mm	CHECKED BY LINDA.WU	DATE 08-18-09
X	± 0.5	APPROVED BY THOMAS	DATE 08-18-09
X.X	± 0.3		
X.XX	± 0.1		
ANGLES	± 0.5°	U/M	mm

CUSTOMER COPY

TITLE
6DB/3DB/20DB/10DB BNC
ATTENUATOR PADSHEET 1 OF 1
DRAWING NO. 27-9300-XX
SIZE ATHIS DRAWING WAS PRODUCED BY COMPUTER,
DO NOT SCALE DRAWING OR UPDATE MANUALLY.

5

4

3

2

1