



Relays, Contactors & Switches > Switches > Slide Switches



Configuration (Pole-Throw): **Single Pole - Four Throw**

Mounting Angle: **Vertical**

Contact Base Material: **Copper Alloy**

Number of Actuators: **Single**

Number of Positions: **4**

Features

Product Type Features

Terminal Configuration	Standard
Actuator Style	Extended, Top

Configuration Features

Configuration (Pole-Throw)	Single Pole - Four Throw
Number of Actuators	Single
Number of Positions	4

Body Features

Actuator Material	Nylon
Actuator Color	Black

Contact Features

Contact Base Material	Copper Alloy
Contact Current Rating	.3 A
Switch Contact Plating Material	Silver

Mechanical Attachment

PCB Mount Retention	With
PCB Mount Retention Type	Guide Post
Mounting Angle	Vertical
Mounting Type	Through Hole

Product Compliance


[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUL 2019 (201) Candidate List Declared Against: JUN 2016 (169)
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Also in the Series | [Alcoswitch MSSA](#)



[Slide Switches\(26\)](#)

Customers Also Bought



TE Part #2-796608-1
6WVW-09-008=#6
TRIBARRIER




TE Part #2-796608-3
6WVW-15-008=#6
TRIBARRIER

TE Part #1-328690-2
JAM NUT, GOLD PLATED



TE Part #104432-1
02 MODII HDR DRST B/A
W/HD

TE Part #1986563-4
SSB7TP040402=TERM
BLOCK ASSY



TE Part #7-146267-0
40 MODII HDR DRST B/A
100 W/HD



TE Part #5-5102084-7
18 MODII HORZ DR CE
EESS 100CL



TE Part #6-1825011-4
ASF62RG04=6PDT
AUTOSLIDE



TE Part #2176307-1
RP 1E 0.1W 12K4 0.1%
25PPM 5K RL



TE Part #4-2176307-6
RP 1E 0.1W 36K5 0.1%
25PPM 5K RL

Documents

Product Drawings

MSSA145004=SW SLIDE, SP4T AG

English