



Multi-Use Duct Tape

3900

Technical Data

February, 2013

Product Description 3M™ Duct Tape 3900 is a general purpose conformable cloth duct tape made with polyethylene film over cloth scrim and a synthetic rubber adhesive. A good choice for general maintenance, bundling, wrapping, attaching, sealing, protecting, and color coding.

Product Construction	Backing	Adhesive	Colors	Standard Roll Length	Standard Width
	Polyethylene film over cloth scrim	Synthetic rubber	Blue, black, olive, red, silver, white, yellow	60 yds. (54.8 m)	1.88 in. (48 mm)

Typical Physical Properties

Note: The following technical information and data should be considered representative or typical only, and should not be used for specification purposes.

		ASTM Test Method
Adhesion to Steel:	72 oz./in. width (79 N/100 mm)	D-3330
Tensile Strength:	32 lbs./in. width (560 N/100 mm)	D-3759
Elongation at Break:	24%	D-3759
Thickness:	8.1 mils (0.21 mm)	D-3652
Temperature Use Range:	Up to 200°F (93°C)	

Features

- Aggressive synthetic rubber adhesive provides instant adhesion to a wide variety of surfaces
- Cloth scrim tears straight in both directions.
- Cloth scrim has high tensile strength, ideal for bundling materials.
- Polyethylene backing resists moisture prolonging the tape bond in moist or humid environments.
- Conformable and can be applied to irregular surfaces.
- Seven colors are available for color coding or to match a surface.

Application Ideas

- General shop and temporary repair activities.
- Sealing, holding, protecting, bundling, color coding.
- Applications requiring moisture resistance.

3M™ Multi-Use Duct Tape

3900

Storage Store under normal conditions of 60° to 80°F (16° to 27°C) and 40 to 60% R.H. in the original carton.

Shelf Life To obtain best performance, use this product within 12 months from date of manufacture.

Technical Information The technical information, recommendations and other statements contained in this document are based upon tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed.

Product Use Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.

Warranty, Limited Remedy, and Disclaimer Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.



This product was manufactured under a quality system registered to ISO 9001 standards.



Industrial Adhesives and Tapes Division

3M Center, Building 225-3S-06
St. Paul, MN 55144-1000
800-362-3550 • 877-369-2923 (Fax)
www.3M.com/industrial



Recycled Paper
40% pre-consumer
10% post-consumer

3M is a trademark of 3M Company.
Printed in U.S.A.
©3M 2013 (2/13)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[3M:](#)

[3900-Black](#) [3900-Blue](#) [3900-Olive](#) [3900-Red](#) [3900-Silver](#) [3900-White](#) [3900-Yellow](#)