

CY8C4247AZA-M475T

Status: **In Production**



Product Specs	Pricing & Inventory	Packaging/Ordering	Quality and RoHS	Technical Documents
CY8C4247AZA-M475T				DESIGN SUPPORT
Automotive Qualified	Y			Development Kits Forums Knowledge Base Packaging Product Brochures Quality & Reliability Samples Technical Support Technical Training Third Party Network (CYPros)
CPU Core	ARM Cortex-M0			
CapSense	N			
Dedicated ADC (#Max Resolution @ Sample Rate)	SAR (1, 12-bit @ 1 msp/s)			
EEPROM (KB)	0			
Flash (KB)	128			
JTAG and SI ID	0x11A4			
LCD Direct Drive	N			
Max. Operating Frequency (MHz)	48			
Max. Operating Temp. (°C)	85			
Max. Operating Voltage (V)	5.50			
Min. Operating Temp. (°C)	-40			
Min. Operating Voltage (V)	1.71			
No. of CAN Controllers	0			
No. of Continuous Time Blocks	2			
No. of DMA Channels	8			
No. of Dedicated Comparators	2			
No. of Dedicated Timer/Counter/PWM Blocks	8			
No. of GPIOs	51			
No. of Op Amps	4			
No. of SIO	0			
No. of Serial Communication Blocks	4			
No. of USB IO	0			
No. of Universal Analog Blocks	0			
No. of Universal Digital Blocks	4			
PLL	N			
SRAM (KB)	16			
Series	PSoC 4200M			
Tape & Reel	Y			
USB (Type)	None			

PRICING & INVENTORY AVAILABILITY					
1-9 unit Price*	10-24 unit Price*	25-99 unit Price*	100-249 unit Price*	250-999 unit Price*	1000+ unit Price*
Contact Sales					

Availability	Quantity	Ships In	Buy from Cypress	Buy from Distributors
Out of Stock	0	Please click here to check lead times	Contact Sales	Contact Sales

* Prices are shown in United States dollars and are for budgetary use only for volume of 1ku

PACKAGING/ORDERING	
Package	TQFP
No. of Pins	44
Package Dimensions	393 L x 1.4 H x 393 W (Mils)
Package Weight	338.95 (mgs)
Package Cross Section Drawing	Download
Package Carrier	REEL
Standard Pack Quantity	1500
Minimum Order Quantity (MOQ)	1500
Order Increment	1500
Estimated Lead Time (days)	91
HTS Code	8542.31.0001
ECCN	(A,3)
ECCN Suball	3A991

QUALITY AND ROHS	
Moisture Sensitivity Level (MSL)	3
Peak Reflow Temp. (°C)	260 (Cypress Reflow Profile)
RoHS Compliant	Y Print RoHS Certificate of Compliance
PB Free	Y
Lead/Ball Finish	Ni/Pd/Au
Marking	Cypress Marking Format
IPC 1752 Material Declaration	
IPC 1752 MATERIAL DECLARATION TQFP64 (10X10 mm) (AZ64)_ASEK_Au WIRE_PURE Sn_HENKEL 8340_HITACHI CEL9200THF Last Update: Oct 30, 2019	
Device Qualification Reports	
FIT/MTBF, ESD (HBM/CDM) and Latch-up data available in the Device Qualification Report.	
QTP#162707: AUTOMOTIVE PSoC 4100M and PSoC 4200M DEVICE FAMILY SBPFHD-10P, FAB25 (AL BEOL INTERCONNECT).pdf Last Update: Mar 06, 2019	

TECHNICAL DOCUMENTS
Application Notes (17)
AN84858 - PSoC®4 Programming Using an External Microcontroller (H5SP) Jan 19, 2020
AN93637 - PSoC® 4 Sensorless Field-Oriented Control (FOC) Dec 30, 2019
AN82156 - PSoC® 3, PSoC 4, and PSoC 5LP - Designing PSoC Creator™ Components With UDB Datapaths Oct 02, 2019
AN82250 - PSoC Creator - Implementing Programmable Logic Designs with Verilog Sep 22, 2019
Show More

SOLUTIONS

Automotive
Industrial
Consumer

PRODUCTS

Wireless
Microcontrollers (MCUs)
Memory
Universal Serial Bus (USB)
Power Management
Touch Sensing
Clocks & Buffers

DESIGN SUPPORT

Community
Videos
Quality & Reliability
Product Roadmaps

ABOUT US

Investors
Careers

CORPORATE HEADQUARTERS

Cypress Semiconductor Corp.
198 Champion Court
San Jose, CA 95134 USA
Tel: +1-408-943-2600

CUSTOMER SERVICE SUPPORT

+1-800-541-4736
Hours:
8:00AM - 5:00PM (local time)
[Create a MyCase](#)
[Cypress Developer Community](#)

INTERNATIONAL SUPPORT

+1-408-943-2600
United States +1-800-541-4736
Hours:
4:30AM - 1:30PM (pacific time)
7:30PM - 4:30AM (standard time)

OTHER REQUESTS

[Contact Us](#)
[Report a Website Problem](#)
[Report a Security Vulnerability](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cypress Semiconductor:](#)

[CY8C4247AZA-M475T](#)