


DIN 46228

# NON-INSULATED CORD END TERMINALS


**MAXIMUM ELECTRIC CURRENT:**

|        |    |    |    |
|--------|----|----|----|
| A.W.G. | 18 | 16 | 14 |
| AMP.   | 17 | 18 | 30 |

**TERMINAL MATERIAL: COPPER TUBE. (TIN PLATED)**

| WIRE RANGE<br>A.W.G.<br>mm <sup>2</sup> | ITEM NO. | DIMENSION |      |      |     |      |     |      |     | CRIMPING TOOL                                                                                                                   |
|-----------------------------------------|----------|-----------|------|------|-----|------|-----|------|-----|---------------------------------------------------------------------------------------------------------------------------------|
|                                         |          | L         |      | D    |     | C    |     | W    |     |                                                                                                                                 |
|                                         |          | inch      | mm   | inch | mm  | inch | mm  | inch | mm  |                                                                                                                                 |
| 18<br>A.W.G.<br><br>1.0 mm <sup>2</sup> | EN1006   | .236      | 6.0  |      | 1.7 |      | 1.4 |      | 2.5 | K.S. MODEL <b>KST2000L</b><br>WITH DIE INDEX<br>NO:1<br><br>OR<br><br>K.S. MODEL <b>LY8-060</b><br>WITH DIE INDEX<br>NO:1-1.5   |
|                                         | EN1007   | .276      | 7.0  |      |     |      |     |      |     |                                                                                                                                 |
|                                         | EN1008   | .315      | 8.0  |      |     |      |     |      |     |                                                                                                                                 |
|                                         | EN1010   | .394      | 10.0 |      |     |      |     |      |     |                                                                                                                                 |
|                                         | EN1012   | .472      | 12.0 |      |     |      |     |      |     |                                                                                                                                 |
|                                         | EN1015   | .591      | 15.0 |      |     |      |     |      |     |                                                                                                                                 |
|                                         | EN1018   | .709      | 18.0 |      |     |      |     |      |     |                                                                                                                                 |
|                                         | EN1020   | .787      | 20.0 |      |     |      |     |      |     |                                                                                                                                 |
|                                         | EN1025   | .984      | 25.0 |      |     |      |     |      |     |                                                                                                                                 |
| 16<br>A.W.G.<br><br>1.5 mm <sup>2</sup> | EN1506   | .236      | 6.0  |      | 2.0 |      | 1.7 |      | 2.8 | K.S. MODEL <b>KST2000L</b><br>WITH DIE INDEX<br>NO:1.5<br><br>OR<br><br>K.S. MODEL <b>LY8-060</b><br>WITH DIE INDEX<br>NO:1-1.5 |
|                                         | EN1507   | .276      | 7.0  |      |     |      |     |      |     |                                                                                                                                 |
|                                         | EN1508   | .315      | 8.0  |      |     |      |     |      |     |                                                                                                                                 |
|                                         | EN1510   | .394      | 10.0 |      |     |      |     |      |     |                                                                                                                                 |
|                                         | EN1512   | .472      | 12.0 |      |     |      |     |      |     |                                                                                                                                 |
|                                         | EN1515   | .591      | 15.0 |      |     |      |     |      |     |                                                                                                                                 |
|                                         | EN1518   | .709      | 18.0 |      |     |      |     |      |     |                                                                                                                                 |
|                                         | EN1520   | .787      | 20.0 |      |     |      |     |      |     |                                                                                                                                 |
| 14<br>A.W.G.<br><br>2.5 mm <sup>2</sup> | EN2506   | .236      | 6.0  |      | 2.6 |      | 2.3 |      | 3.4 | K.S. MODEL <b>KST2000L</b><br>WITH DIE INDEX<br>NO:2.5<br><br>OR<br><br>K.S. MODEL <b>LY8-060</b><br>WITH DIE INDEX<br>NO:2.5   |
|                                         | EN2507   | .276      | 7.0  |      |     |      |     |      |     |                                                                                                                                 |
|                                         | EN2508   | .315      | 8.0  |      |     |      |     |      |     |                                                                                                                                 |
|                                         | EN2510   | .394      | 10.0 |      |     |      |     |      |     |                                                                                                                                 |
|                                         | EN2512   | .472      | 12.0 |      |     |      |     |      |     |                                                                                                                                 |
|                                         | EN2515   | .591      | 15.0 |      |     |      |     |      |     |                                                                                                                                 |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[KS Terminals:](#)

[EN1006](#) [EN2507](#) [EN16-15](#)