


NON-INSULATED RING TERMINALS


MAXIMUM ELECTRIC CURRENT:

A.W.G.	400	500	600
AMP.	545	620	690

TERMINAL MATERIAL: COPPER
SURFACE TREATMENT: TIN PLATED

WIRE RANGE A.W.G. mm ²	ITEM NO.		STUD SIZE		DIMENSION inch mm							CRIMPING TOOL	Q'TY BOX
	BRAZED SEAM	BUTTED SEAM	d2		W	F	L	E	D	d1	T		
400/500 MCM 200 mm ²	RNB200-8		5/16	.331 8.4	1.732 44.0	.965 24.5	2.835 72.0	1.240 31.5	1.283 32.6	.945 24.0	.157 4.0	IZUMI MODEL 12K-1 12#A WITH DIE INDEX NO.:200 OR K.S. MODEL KSTP-325 WITH DIE INDEX NO.:240	10
	RNBL200-8		5/16	.331 8.4		1.437 36.5	3.555 90.3						10
	RNB200-10		3/8	.413 10.5		.965 24.5	2.835 72.0						10
	RNBL200-10		3/8	.413 10.5		1.437 36.5	3.555 90.3						10
	RNB200-11		7/16	.453 11.5		.965 24.5	2.835 72.0						10
	RNB200-12		1/2	.512 13.0									10
	RNBL200-12		1/2	.512 13.0		1.437 35.5	3.555 90.3						10
	RNB200-14		9/16	.591 15.0		.965 24.5	2.835 72.0						10
	RNB200-16		5/8	.669 17.0									10
	RNBL200-16		5/8	.669 17.0		1.437 36.5	3.555 90.3						10
	RNB200-18		11/16	.748 19.0									10
	RNB200-20		3/4	.827 21.0									10
	RNB200-22		7/8	.906 23.0		1.437 37.5	3.583 91.0						10
	RNB200-24		15/16	.984 25.0									10
	RNB200-27		1	1.102 28.0									10
400/500 MCM 200 mm ²	RNB250-10		3/8	.413 10.5	1.732 44.0			1.240 31.5	1.287 32.7	.945 24.0	.157 4.0		5
	RNB250-12		1/2	.512 13.0		.965 24.5	2.835 72.0						5
	RNB250-16		5/8	.669 17.0									5
500/600 MCM 325 mm ²	RNB325-8		5/16	.331 8.4	1.988 50.5			1.398 35.5	1.480 37.6	1.102 28.0	.169 4.3	IZUMI MODEL 12K-1 12#A WITH DIE INDEX NO.:325 OR K.S. MODEL KSTP-325 WITH DIE INDEX NO.:400	5
	RNB325-10		3/8	.413 10.5		1.319 33.5	3.465 88.0						5
	RNBL325-10		3/8	.413 10.5		1.772 45.0	4.154 105.5						5
	RNB325-11		7/16	.453 11.5		1.319 33.5	3.465 88.0						5
	RNB325-12		1/2	.512 13.0									5
	RNBL325-12		1/2	.512 13.0		1.772 45.0	4.154 105.5						5

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

KS Terminals:

[RNB200-10](#) [RNB200-12](#) [RNB200-16](#) [RNB200-20](#) [RNB200-22](#) [RNB200-27](#) [RNB325-12](#) [RNBL200-12](#) [RNBL200-16](#) [RNBL325-12](#)