

simpleANT3B-CAL

**Calibrated Survey Tripleband + L-band
RTK GNSS antenna (IP67)**


SKU: AS-ANT3B-CAL-L1256-SMATNC-01



Dimensions: 152x152x67 mm

Antenna

Frequency	GPS L1/L2/L5/L6 GLONASS G1/G2/G3 BeiDou B1/B2/B3 Galileo E1/E5b/E6
Polarization	RHCP
Axial ratio @ zenith	≤ 3 dB
V.S.W.R.	≤ 1.5
Gain	5.5dBi (Zenith)
Impedance	50 Ω
Horizontal coverage angle	360°



Calibration Files available at:
<https://geodesy.noaa.gov/ANTCAL/>
Manufacturer: AS- - ArduSimple
Antenna: AS-ANT3BCAL01

Electrical

Gain	40 \pm 2dB
Noise figure	≤ 1.5 dB
Passband fluctuation	± 1 dB
Supply voltage	3.0~12V DC
Current consumption	≤ 50 mA @ 3V
V.S.W.R.	≤ 1.5

Mechanical

Connector	TNC Female (1.5m to SMA male and 2.5m to TNC Male included)
Mounting	5/8" x 11TPI thread
Weight	490g

Environmental

Operating temperature	-40°C~+85°C
Ingress Protection	IP67 (excluding air vent that can be sealed by mounting pole)
Environmentally friendly	ROHS Compliant

© 2024 ArduSimple – info@ardusimple.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ArduSimple:](#)

[AS-ANT3B-CAL-L1256-SMATNC-01](#)