






SYMBOL DEFINITION		
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL  DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO OF INSPECTIONS REQUIRED	18
	LAST NO. USED	16

MISSING SYMBOLS
NO MISSING SYMBOL NUMBER

DWG STATUS					ZONE	REVISION HISTORY	AUTH	DR	APVD 1	APVD 2
DATE	STG	REV	N/P	CHG						
26FE07	R	13	-	-		ALL ACTIVE PARTS - CREATED PART DRAWING	400697	AC	FR	PYP
12JN07	R	14	-	-		ALL PARTS - REDRAWN TO PD; 13652872 - RELEASED	401665	ECB	AUG	GGI
29AP08	R	15	-	-		ALL ACTIVE PARTS -ADDED CARRIER STRIP OPTIONAL CONSTRUCTION TYPE 102	404514	LHT	GEM	LHT
05AU08	R	16	-	-		ALL ACTIVE PARTS -REMOVED CARRIER STRIP OPTIONAL CONSTRUCTION TYPE 102	405648	LHT	VMR	LHT
28OC08	R	17	-	-		12064906 - OBSOLETE AND REPLACED BY 13652872	406605	MDH	FKV	JAW
09FE09	R	18	-	-		ALL ACTIVE PARTS - UPDATED MAT'L CALLOUT; 12064904-05 - OBSOLETE	407307	JTV	AUG	RAP
20AP09	R	19	-	-		12064904 - REINSTATED	407792	RRR	JAA	RRR
19JN09	R	20	-	-		12064904 - OBSOLETE	408238	RRR	JVM	RRR
24JA12	R	21	-	-		ALL ACTIVE PARTS - ADDED "CABLE SIZE (MM²)" COLUMN ON CHART	416803	JGM	JAA	RSQ
27SE16	R	22	-	-		13652872 - OBSOLETE	434383	AGH	VMR	AGH
11AU20	R	23	-	-		12084688-89 & 12124369 - DIM 11.1 +0.2/-0.15 WAS 11.1 +/-0.15	552207	AHY	AHY	AGH



(3)
0.25 MAX DIFFERENCE-BOTH WINGS



NOTES

- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:



DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.

CARRIER STRIP VIEW-TYPE 101 CARRIER STRIP OPTIONAL CONSTRUCTION

SCALE 6:1

-	-	-	0.406 X 11.13	COPPER ALLOY	12124369	A6	-	TIN PLATED COPPER ALLOY	0.35 - 0.8	2.4	0.5	0.35	0.76	9.42	4.71
-	-	-	0.406 X 11.13	COPPER ALLOY	12124033	A	-	TIN PLATED COPPER ALLOY	-	2.4	0.5	0.35	0.76	16.51	8.26
12064906	B4	-	0.406 X 11.13	COPPER ALLOY	13652872	01	AE	TIN PLATED COPPER ALLOY	4 - 6	5.84	1.98	0.35	0.76	16.51	8.26
12064905	B4	-	0.406 X 11.13	COPPER ALLOY	12084689	A6	-	TIN PLATED COPPER ALLOY	3 - 5	4.57	1.39	0.35	0.76	16.51	8.26
12064904	C6	-	0.406 X 11.13	COPPER ALLOY	12084688	B6	-	TIN PLATED COPPER ALLOY	0.8 - 2	3.68	0.88	0.35	0.76	9.42	4.71
PART NO	REV	N/P	MAT'L SIZE	MAT'L SPEC	PART NO	REV	N/P	MAT'L SPEC	SIZE (MM²)	B ±0.25	C ±0.15	D MAX	(E)	G ±0.15	H ±0.15
UNPLATED					PLATED				CABLE						

(12)	PROCESS SENSITIVE DIMENSION
DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED	
DIMENSIONAL RANGE (MM)	CHART ID
FROM 0 TO 12	> 12
TOLERANCE UNLESS OTHERWISE SPECIFIED	
±0.1	±0.2
ANGULAR TOLERANCE	±2°

A LINE DRAWN THROUGH A PART NUMBER INDICATES THAT PHYSICAL PARTS ARE NOT AVAILABLE FOR ORDERING.	
PART NUMBERS THAT DO NOT HAVE A LINE PRESENT INDICATE THAT PHYSICAL PARTS ARE AVAILABLE FOR ORDERING.	
CONTACT APTIV SALES TO ASSURE AVAILABILITY OF PARTS.	
DWG TYPE PART DRAWING	
STYLE	
VOLUME (CM³)	DISTR CODE D
UNLESS OTHERWISE SPECIFIED THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994 AS AMENDED BY THE QM GLOBAL DIMENSIONING AND TOLERANCING ADDENDUM-2001. SEPARATE PATTERNS OF FEATURES MAY BE GAGED SEPARATELY REGARDLESS OF DATUM REFERENCES.	
ALL DIMENSIONS ARE IN MILLIMETERS	
REFERENCE	
THIRD ANGLE PROJECTION 	DO NOT SCALE 

• APTIV •	
CONNECTION SYSTEMS	
WARREN, OH	
COPYRIGHT 2007 APTIV. ALL RIGHTS RESERVED.	
THIS DRAWING IS THE PROPERTY OF APTIV AND CONTAINS APTIV CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD MATH DATA, AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.	
DR	DATE
APVD1 A. CARBONEY	26FE07
APVD2 FCO. RESENDIZ	02MR07
APVD3 P. YABUR	09MR07
APVD4	
APVD5	
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER APTIV 10949001	
MATERIAL SEE CHART	
DRAWING NAME TAXI TERM SPLICE	
DRAWING NUMBER 12064907	
SIZE A1	SCALE 8:1
FRAME NO 1 OF 1	SHEET NO 1 OF 1
STG R	REV 23
N/P -	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[12124369](#)