









ASSEMBLY-NO.:	PART-REV	CODING	MATERIAL/WEIGHT
33285164	01	CODE A	ALL PARTS VO / 20,0
33285165	01	CODE B	
33285167	01	CODE C	
33285168	01	CODE D	
33346265	01	CODE A	ALL PARTS NVO / 19,4
33347851	01	CODE B	
33347841	01	CODE C	
33347822	01	CODE D	

POSITION	1		2								3	4		5	
NAME	HOUSING		INSERT								HOUSING SEAL	SECONDARY LOCK		SLIDER	
MATERIAL	PBT GF30 FR17	PBT GF30	PBT GF30 FR17				PBT GF30				LSR 50 SHORE	PBT GF30 FR17	PBT GF30	PBT GF30 FR17	PBT GF30
COLOR:	BLACK	BLACK	BLACK	GRAY	GREEN	BLUE	BLACK	GRAY	GREEN	BLUE	REDDISH-BROWN	ORANGE	YELLOW	ORANGE	YELLOW
PART-NO.:	33282971	33344858	33283255	33283276	33283277	33283280	33345108	33347338	33347339	33347340	33283921	33282493	33344867	33282491	33344853
-	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---
-	1	---	1	---	---	---	---	---	---	---	1	1	---	1	---
-	1	---	---	1	---	---	---	---	---	---	1	1	---	1	---
-	1	---	---	---	1	---	---	---	---	---	1	1	---	1	---
-	1	---	---	---	---	1	---	---	---	---	1	1	---	1	---
-	---	1	---	---	---	---	1	---	---	---	1	---	1	---	1
-	---	1	---	---	---	---	---	1	---	---	1	---	1	---	1
-	---	1	---	---	---	---	---	---	1	---	1	---	1	---	1
-	---	1	---	---	---	---	---	---	---	1	1	---	1	---	1


DWG STATUS					ZONE	REVISION HISTORY	AUTH	DR	APVD 1	APVD 2
DATE	STG	REV	N/P	CHG						
19NO18	R	01				INITIAL RELEASE		P.BAL	P.NAJ	M.GRU
14MR19	R	01	AA		B6	REFERENCE HELLERMANN TYTON DWG-NO. ADDED		K.FAR	M.GRU	K.PIT
27OC20	R	01	AB		G11 B6	PART AVAILABILITY FOR PART NUMBERS 33346265, 33347851, 33347841, 33347822 UPDATED NOTES UPDATED		P.NAJ	M.GRU	


CLOSED POSITION



NOTES	
-	ON MAIN VIEW ASSEMBLY 33285164 SHOWN (CODE A)
-	DELIVERED CONDITION AS ON MAIN VIEWS - SECONDARY LOCK AND SLIDER IN OPEN POSITION
	ASSEMBLY INSTRUCTION NO.:
-	35269106-CUS71 - PRELIMINARY ASSEMBLY
-	35269106-CUS72 - HARNESS ASSEMBLY
-	35269103-CUS73 - CAR ASSEMBLY
-	35269102-CUS73 - CAR ASSEMBLY
	MATING PARTS:
-	7 WAY 1.5/2.8 MALE PANEL MOUNT ASM DWG-NO.: 35153955
-	7 WAY 1.5/2.8 MALE STRAP MOUNT ASM DWG-NO.: 35153956
-	BACKSHELL 90 DEG APTIV DWG-NO.: 35024554 (HT DWG-NO.: 17-2275-001-CSG)
-	BACKSHELL 180 DEG APTIV DWG-NO.: 35024538 (HT DWG-NO.: 17-1461-001-CSG)
-	PROTECTION CAP APTIV DWG-NO.: 35149886 (HT DWG-NO.: 17-2266-001-CSG)
	MATING TERMINAL SYSTEM:
-	1.5 TERMINAL DWG-NO.: 15432214
	MAX WIRE CROSS SECTION: 1.0MM²
	RECOMMENDATION FOR 1.5 TERMINAL WITH WIRE CROSS SECTION 1.5MM² - USE COMBINATION:
-	TE TERMINAL: MCP 1.5, DWG NO.: 1418884-3
	SEAL: 964972-1
	MAX INSULATION CRIMP DIMENSIONS:
	HEIGHT: 3.40; WIDTH: 3.30
-	2.8 TERMINAL DWG-NO.: 15446676
	MAX WIRE CROSS SECTION: 2.5MM²
1	APTIV LOGO
2	MATERIAL NAME ACCORDING TO VDA 260
3	TOOL CAVITY NUMBER
4	PART CAVITY NUMBER
5	MOVING DISTANCE OF SECONDARY LOCK
6	MOVING DISTANCE OF SLIDER

		DIMENSIONAL RANGE (MM)							CHART				E1
☐ DIM TO CHECK	FROM	> 0	> 20	> 30	> 70	> 100	> 150	> 200	> 250	> 300	> 400		
☐ DIM FOR HELP	TO												
TOLERANCE UNLESS OTHERWISE SPECIFIED													
☐ THEORETIC DIM		±0.15	±0.2	±0.3	±0.4	±0.5	±0.6	±0.8	±1	±1.2	ANGULAR TOLERANCE ±2°		

DWG TYP		PART DRAWING		DISTR CODE	
WEIGHT (GR)		SEE CHART		D	
VOLUME (CM ³)		---			
ROUTING					
UNLESS OTHERWISE SPECIFIED					
GENERAL TOLERANCES ACCORDING TO:					
SEE CHART					
GD&T ACCORDING TO:					
ISO 1101					
REFERENCE					
FIRST ANGLE PROJECTION					
					
DO NOT SCALE					
USE MATH DATA				NIX	



• APTIV •

CONNECTION SYSTEMS
KRAKOW, POLAND
COPYRIGHT 2018 APTIV. ALL RIGHTS RESERVED.
THIS DRAWING IS THE PROPERTY OF APTIV AND CONTAINS APTIV CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD MATH DATA, AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.

TEN RYSUNEK JEST WLASNOSCIA APTIV I ZAWIERA POUFNE INFORMACJE. POWIELANIE, ROZPOWIECZANIE I WYKORZYSTYWANIE TEGO DOKUMENTU LUB ZWIĄZANYCH Z NIM DANYCH CAD, JAK RÓWNIEŻ PRZEKAZYWANIE INNYM JAKIEKOLWIEK ICH ZAWARTOSCÍ BEZ NADANIA WYRAŻNYCH UPRAWNIENÍ, JEST ZABRONIONE.

DR	P.BALAJI	DATE	18NO18
APVD1	P.NAJDUCH	19NO18	
APVD2	M.GRUDZEWSKI	20NO18	
APVD3			
APVD4			
APVD5			

SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER APTIV 10949001
SUBSTANCJE NIEBEZPIECZNE I POWTÓRNIIE PRZETWORZONE OKRESLA APTIV 10949001

SEE CHART

DRAWING NAME
7 WAY 1.5 / 2.8
CTCS FEMALE ASSEMBLY

DRAWING NUMBER					
35153947					
SIZE	SCALE	FRAME NO	SHEET NO	STG	REV
A1	2:1	1 OF 1	1 OF 1	R	01

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[33285165](#)