







TYPE 202
20-35 MM²
SAME AS TYPE 201
EXCEPT AS SHOWN




TYPE 203
20-35 MM²
SAME AS TYPE 201
EXCEPT AS SHOWN




TYPE 204
20-35 MM²
SAME AS TYPE 201
EXCEPT AS SHOWN




TYPE 205
12-19 MM²
SAME AS TYPE 201
EXCEPT AS SHOWN




TYPE 206
12-19 MM²
SAME AS TYPE 205
EXCEPT AS SHOWN




TYPE 207
20-35 MM²
SAME AS TYPE 201
EXCEPT AS SHOWN




TYPE 208
20-35 MM²
SAME AS TYPE 201
EXCEPT AS SHOWN




TYPE 208
20-35 MM²
SAME AS TYPE 201
EXCEPT AS SHOWN



TYPE 209
8 MM²
SAME AS TYPE 201
EXCEPT AS SHOWN




TYPE 210
20-35 MM²
SAME AS TYPE 201
EXCEPT AS SHOWN




TYPE 211
20-35 MM²
SAME AS TYPE 201
EXCEPT AS SHOWN


DRAWING NUMBER
33128259
SIZE A1x3 SCALE 4:1 FRAME NO. 2 OF 2 REV. 18




TYPE 212
12-19 MM²
SAME AS TYPE 205
EXCEPT AS SHOWN




TYPE 201
20-35 MM²




TYPE 213
20-35 MM²
SAME AS TYPE 201
EXCEPT AS SHOWN







TYPE 214
20-35 MM²
SAME AS TYPE 205
EXCEPT AS SHOWN





TYPE 215
12-19 MM²
SAME AS TYPE 205
EXCEPT AS SHOWN



TYPE 216
12-19 MM²
SAME AS TYPE 205
EXCEPT AS SHOWN



SECTION A-A
SCALE 6:1



- NOTES
- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND
AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION
(SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL
OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL
BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
 - FOR TERMINALS WITH STOCK THICKNESS OF 1.3MM OR GREATER
AND TOOLING PRODUCED AFTER 01A1414 REFER TO ADDITIONAL
TOLERANCE CHART.
 - HEX NUT MUST WITHSTAND A MINIMUM PUSH OUT FORCE OF 800 N.
 - HEX NUT MUST FREELY ROTATE WHEN A MIN TORQUE VALUE OF 2 NM
IS APPLIED.

PART	NO	REV	N/P	TYPE	SIZE (MM²)	10	TERMINAL	NUT	W
35084281	02	AB	216	12-19	5	35084279	33276563	90°	
35084280	02	AA	215	12-19	5	35084279	33276563	90°	
35056168	02	AA	214	12-19	5	35056167	33276563	90°	
33380285	02	AB	213	20-35	2	33380280	33276563	90°	
33380284	02	AB	212	12-19	5	33380279	33276563	90°	
33380283	02	AB	211	20-35	2	33380278	33276563	90°	
33380281	02	AB	210	20-35	2	33380276	33276563	90°	
33338316	02	AB	209	8	8	33338315	33276563	90°	
33291202	03	AB	208	20-35	2	33291201	33276563	90°	
33276570	03	AB	207	20-35	2	33276562	33276563	90°	
33276569	04	AB	206	12-19	5	33276561	33276563	90°	
33276568	03	AA	205	12-19	5	33276560	33276563	90°	
33276567	04	AB	204	20-35	2	33276559	33276563	90°	
33276566	03	AA	203	20-35	2	33276558	33276563	90°	
33276565	03	AB	202	20-35	2	33276557	33276563	90°	
33276564	03	AB	201	20-35	2	33276556	33276563	90°	

TOLERANCE CHART FOR TERMINALS			
WITH A STOCK THICKNESS OF 1.3MM OR GREATER AND TOOLING PRODUCED AFTER 01A1414			
DIMENSIONAL RANGE (MM)			
FROM	TO	ANGULAR	TOLERANCE UNLESS OTHERWISE SPECIFIED
0	15	>10°	±0.15
15	30	>10°	±0.3
30	45	>10°	±0.4
45	60	>10°	±0.5
60	75	>10°	±0.6
75	90	>10°	±0.7

CONNECTION SYSTEMS

WARRANTY

APPROVED BY: JOSE LUIS TAPIA

DATE: 2000C15

APPROVED BY: RENE GONZALEZ

DATE: 03NOV15

33128259

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[35084280](#)