





NOTES	
-	ON MAIN VIEW ASSEMBLY 33343722 SHOWN (CODE A)
-	DELIVERED CONDITION AS ON MAIN VIEWS - SECONDARY LOCK IN OPEN POSITION
-	ASSEMBLY INSTRUCTION NO.: 35269105-CUS71 - PRELIMINARY ASSEMBLY 35269105-CUS72 - HARNESS ASSEMBLY 35269102-CUS73 - CAR ASSEMBLY
-	MATING PARTS: - 10 WAY 1,5/2,8 FEMALE CONNECTOR ASM DWG-NO.: 35123488 - FIXING SLIDE APTIV DWG-NO.: 33390630 (HT DWG-NO.: 17-1487-001-CS6) - BACKSHELL 90 DEG APTIV DWG-NO.: 33390631 (HT DWG-NO.: 17-2276-001-CS6) - BACKSHELL 180 DEG APTIV DWG-NO.: 33390632 (HT DWG-NO.: 17-1486-001-CS6) - PROTECTION CAP APTIV DWG-NO.: 35426250 (HT DWG-NO.: 17-2272-001-CS6)
-	MATING TERMINAL SYSTEM: - 1.5 TERMINAL DWG-NO.: 15396739 - MAX WIRE CROSS SECTION: 1.0MM² - RECOMMENDATION FOR 1.5 TERMINAL WITH WIRE CROSS SECTION 1.5MM² - USE COMBINATION: TE TERMINAL: TAB 1.6, DWG NO.: 1703278-5 SEAL: 2112323-1 - MAX INSULATION CRIMP DIMENSIONS: HEIGHT: 3.40; WIDTH: 3.40 - 2.8 TERMINAL DWG-NO.: 13548085 - MAX WIRE CROSS SECTION: 2.5MM²
1	APTIV LOGO
2	MATERIAL NAME ACCORDING TO VDA 260
3	DATE INSERT
4	TOOL CAVITY NUMBER
5	INDEX REPLACEMENT INSERT
6	PART CAVITY NUMBER
7	MOVING DISTANCE OF SECONDARY LOCK



			9			8	7	6	5			4				
				POSITION	1								2		3	4
				NAME	MALE HOUSING PANEL MOUNT								MALE SECONDARY LOCK		SL SEAL	FIXING SEAL
				MATERIAL	PBT GF30 FR17				PBT GF30				PBT GF30 FR17	PBT GF30	LSR 50 SHORE	LSR 70 SHORE
				COLOR:	BLACK	GRAY	GREEN	BLUE	BLACK	GRAY	GREEN	BLUE	ORANGE	YELLOW	REDDISH-BROWN	REDDISH-BROWN
				PART-NO.:	33343470	33343472	33343487	33343489	33349766	33349772	33349773	33349774	33342244	33350073	33283927	33339919
ASSEMBLY-NO.:	PART-REV	CODING	MATERIAL/WEIGHT	-	---	---	---	---	---	---	---	---	---	---		
33343722	01	CODE A	ALL PARTS VO / 29.2	-	1	---	---	---	---	---	---	1	---	1	1	
33343766	01	CODE B		-	---	1	---	---	---	---	---	1	---	1	1	
33343767	01	CODE C		-	---	---	1	---	---	---	---	1	---	1	1	
33343773	01	CODE D		-	---	---	---	1	---	---	---	1	---	1	1	
33350430	01	CODE A	ALL PARTS NVO / 28.4	-	---	---	---	---	1	---	---	---	1	1	1	
33350431	01	CODE B		-	---	---	---	---	---	1	---	---	1	1	1	
33350432	01	CODE C		-	---	---	---	---	---	---	1	---	---	1	1	
33350433	01	CODE D		-	---	---	---	---	---	---	1	---	1	1	1	

MOUNTING BRACKET THICKNESS	FIXING SLIDE APTIV/HT PART-NO.:	COLOR
-	PBT GF30 FR17 PBT GF30	-
1MM	33342242 / 151-02383 33350093 / 151-02382	NATURAL
1.5MM	33339586 / 151-02387 33350096 / 151-02386	GRAY
2MM	35037428 35037429	BLUE
2.5MM	33339587 / 151-02391 33350042 / 151-02390	RED
3MM	33339588 / 151-02395 33350046 / 151-02394	YELLOW
3.5MM	35037426 35037427	GRAY
4MM	35037424 35037425	GREEN



NOTE 7 (1.7)

W-W

(33.35)

48.3 ±0.5

NOTE 1

(19.1)

(30.5)

(2.5)


(WB)

NOTE 2

NOTE 3

1

39.8 +0.4 -0.65



		SHIM CORNER TOLERANCE									
☐ DIM TO CHECK	DIMENSIONAL RANGE (MM)				CHART E1						
	FROM	> 0	> 20	> 30	> 70	> 100	> 150	> 200	> 250	> 300	
☐ DIM FOR HELP	TO	20	30	70	100	150	200	250	300	400	
TOLERANCE UNLESS OTHERWISE SPECIFIED											
☐ THEORETIC DIM		±0.15	±0.2	±0.3	±0.4	±0.5	±0.6	±0.8	±1	±1.2	
ANGULAR TOLERANCE ±2°											

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[33343722](#)