








TYPE 102
SAME AS TYPE 101
EXCEPT AS SHOWN




TYPE 105
SAME AS TYPE 101
EXCEPT AS SHOWN







TYPE 103
SAME AS TYPE 101
EXCEPT AS SHOWN



TYPE 106
SAME AS TYPE 101
EXCEPT AS SHOWN



TYPE 101




- NOTES

1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:

DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.

2. PART IS MANUFACTURED TO GEOMETRIC TOLERANCES, CENTERLINE DIMENSIONS ARE FOR REFERENCE ONLY.
3. SEALING CODE 4 - DESIGN WILL MEET REQUIREMENTS OF SAC/USCAR-2 CONNECTOR SYSTEM ENVIRONMENTAL TEST FLOWCHART (PRESSURE/VACUUM AND SUBMERSION).
4. THIS PRODUCT IS NOT CATEGORIZED AS AN APPEARANCE ITEM, MINOR IMPERFECTIONS INCLUDING, BUT NOT LIMITED TO, FLOW MARKS, COLOR BLEMSHES, GATE VESICLE, AND SOFT FLASH THAT DO NOT AFFECT THE FIT, FORM, OR FUNCTION OF THE PART ARE PERMISSIBLE PER ENP-4-3.CS.01.
5. FOR APPLICATION DATA SEE THE INDIVIDUAL APPLICATION DRAWINGS.
6. ASSEMBLY TO BE USED WITH APPROPRIATE APTIV HOLDER DESIGN.
7. ASSEMBLY TO BE PROCESSED USING APTIV CONNECTION SYSTEMS BEST PRACTICE METHODS AND/OR CONNECTOR ASSEMBLY INSTRUCTIONS AND APPLICABLE REPAIR PROCEDURES.
8. BEFORE TERMINAL ASSEMBLY: VERIFY THAT PLR IS IN THE PRE-STAGE POSITION ON THE CONNECTOR. IF NOT: RETURN PLR TO PRE-STAGE POSITION.
9. FOR DIFFERENT PUNCH PATTERN CONFIGURATIONS (IF AVAILABLE) SEE SHEET 2
10. FOR ASSEMBLIES WITHOUT CPA SEE DRAWING 19532402

HEET 2	(N/A) PROCESS SENSITIVE DIMENSIONS																					
	DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED																					
	DIMENSIONAL RANGE (MM)	CHART																				
	<table> <tr> <td>FROM</td><td>> 0</td><td>> 10</td><td>> 30</td><td>> 100</td><td>> 150</td><td>> 200</td><td>> 250</td><td>> 300</td><td>> 400</td></tr> <tr> <td>TO</td><td>20</td><td>30</td><td>70</td><td>100</td><td>150</td><td>200</td><td>250</td><td>300</td><td>400</td></tr> </table>	FROM	> 0	> 10	> 30	> 100	> 150	> 200	> 250	> 300	> 400	TO	20	30	70	100	150	200	250	300	400	TOLERANCE UNLESS OTHERWISE SPECIFIED ANGULAR TOLERANCE $\pm 2^\circ$
FROM	> 0	> 10	> 30	> 100	> 150	> 200	> 250	> 300	> 400													
TO	20	30	70	100	150	200	250	300	400													

LINE DRAWING THROUGH A PART NUMBER INDICATES THAT PHYSICAL PARTS ARE NOT AVAILABLE FOR ORDERING. PART NUMBERS THAT DO NOT HAVE A LINE PRESENT INDICATE THAT PHYSICAL PARTS ARE AVAILABLE FOR ORDERING. CONTACT APPLICATOR SALES TO ASSURE AVAILABILITY OF PARTS.	
NEW TITLE PART DRAWING	
TITLE	
VOLUME (TOP)	DISTR CODE
D	
UNLESS OTHERWISE SPECIFIED THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.100-1994 STANDARD FOR THE FIRST ANGLE DRAWING CONVENTION AND TOLERANCING ADDENDUM 2011. SEPARATE PATTERNS OF FEATURES MAY BE GAGED SEPARATELY. KNOWLEDGE OF DATA REFERENCES.	
ALL DIMENSIONS ARE IN MILLIMETERS	
REFERENCE	THIRD ANGLE PROJECTION
	DO NOT SCALE USE MATH DATA
	

• A P T I V •					
CONNECTION SYSTEMS					
ARRIVE, O.R.					
COPYRIGHT 1973 APTI, ALL RIGHTS RESERVED.					
THIS DRAWING IS THE PROPERTY OF APTI AND CONTAINS APTI DESIGN INFORMATION. IT IS TO BE USED FOR THE DESIGN AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED DATA DATA. IT WILL BE COMBINED WITH ANY OTHER DOCUMENTS TO PROVIDE A COMPLETE AUTHORIZATION. IS PROHIBITED.					
DATE					
DR					
APPROV	HECTOR CLAUDIO				16/JA/3
APPROV	HECTOR CLAUDIO				17/JA/3
APPROV	GERARDO GOMEZ, I.				18/JA/3
APPROV					
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER API V (1094920)					
MATERIAL SEE CHART					
DRAWING NAME					
TAXI ASM CONN 8 F OCS 1.5 STD					
DRAWING NUMBER					
15514673					
SIZE A1x3	COLOR	FRAME NO 1 OF 2	DESK NO 1 OF 2	UNIT NO 1 OF 1	REV NO 1

15514672	05	AF	106	15514665	15514685	15514684	15514683	15514678	15519096	F
15514671	05	AF	105	15514664	15514684	15514683	15514682	15514678	15519096	E
15514670	05	AG	104	15514663	15514685	15514684	15514683	15514678	15519096	D
15514669	05	AG	103	15514662	15514685	15514684	15514683	15514678	15519096	C
15514668	05	AG	102	15514661	15514685	15514684	15514683	15514678	15519096	B
15514667	06	AA	101	15514659	15514685	15514684	15514683	15514678	15519096	A
PART NO	REV	N/P	TYPE	CONNECTOR	PLR	SEAL CONN	SEAL CBL	RETAINER	CPA	USCAR OPTION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[15514669](#)