





	PART-NO.:	PART-REV	DATE DATUM	CABLE Ø KABEL Ø	MATERIAL WERKSTOFF	SIM RAL	B	D	E	W	(GR)	(CM³)
	13834633	01	01JL10	1.2 - 1.9 MM	LSR 50 SHORE 2% GRN	6010	0.8	3.45	6.9	4.25	0.195	0.173
	13834634	01	01JL10	1.8 - 2.4 MM	LSR 50 SHORE 2% YEL	1007	1.35	3.85	6.9	4.65	0.188	0.166
	13834635	01	01JL10	2.1 - 3.0 MM	LSR 50 SHORE 2% WHT	9010	1.65	4.35	6.9	5.15	0.187	0.165
①	35545727	01	13MR21	1.8 - 2.4 MM	LSR 50 SHORE 2% BLU	5010	1.35	3.45	6.9	4.25	0.173	0.158
①	35545726	01	13MR21	2.1 - 3.0 MM	LSR 50 SHORE 2% GRA	7000	1.65	3.45	6.9	4.25	0.158	0.144

DWG STATUS					ZONE	REVISION HISTORY	AUTH	DR	APVD 1	APVD 2
DATE	STG	REV	N/P	CHG						
01JL10	R	01				INITIAL RELEASE / ERSTFREIGABE		A.SEN	J.SCH	M.SKR
18MR11		01	AA		A8	INFORMATION ABOUT VALIDATION ADDED INFORMATION UEBER VALIDATION HINZU		V.KAS	M.HOR	SYS
27JU16	R	01	AB		F5	CABLE Ø/KABEL Ø 1.8-2.4 WAS/WAR 1.8-2.3		P.MAY	K.STO	SYS
04MY21	R	01	AC		F6 D6/D5 F4	NEW PN 35545727 & 35545726 ADDED DIM4.6 REMOVED & DIM2.9, DIM1.0 & DIM ØB ADDED B VALUE ADDED TO TABLE		R.SUR	K.PAT	T.BOL



SCALE / MASSSTAB:
1 0 1

SCALE / MASSSTAB:
5 : 1

DWG. TYPE		D
PART DRAWING		
WEIGHT (GR)	DISTR. CODE	
SEE CHART		
VOLUME (CM ³)		
SIEME TABELLE		
ROUTING		

UNLESS OTHERWISE SPECIFIED

GENERAL TOLERANCES
ACCORDING TO:


SEE CHART
SIEHE TABELLE

GD&T
ACCORDING TO:

ISO 1101

REFERENCE

FIRST ANGLE PROJECTION



DO NOT
SCALE

USE MATH
DATA



• A P T I V •

DELPHI DEUTSCHLAND GMBH
D-42119 WUPPERTAL

COPYRIGHT 2010 DELPHI CORPORATION AND/OR ITS AFFILIATES.
ALL RIGHTS RESERVED.

REVISED 2016

THIS DRAWING IS THE PROPERTY OF DELPHI CORPORATION
AND CONTAINS DELPHI CONFIDENTIAL INFORMATION.
THE REPRODUCTION, DISTRIBUTION AND UTILIZATION
OF THIS DOCUMENT OR ITS RELATED CAD MATH DATA,
AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHERS,
WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.

DIESE ZEICHNUNG IST EIGENTUM DER FIRMA DELPHI UND ENTHAELT DELPHI
VERTRAULICHE INFORMATIONEN DIE REPRODUKTION, VERTEILUNG UND
NUTZUNG DIESES DOKUMENTES ODER DEREN ZUGEHOEIGEN CAD DATEN, ODER
AUCH ALS KOMMUNIKATION VON BELIEBIGEN INHALT ZU ANDEREN, IST OHNE
BERECHTIGUNGSPRUEFUNG DURCH DIE DELPHI CORPORATION UNZULAESSIG

		DATE
DR	A. SENEL	30 JUN 10
APVD1	J. SCHATTLING	01 JUL 10
APVD2	M. SIKORA	16 SEP 10
APVD3		
APVD4		
APVD5		

SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER APTIV 10949001
POTENTIELL GEFAEHRLICHE STOFFE UND REZYKLATANTEIL
GEMAESS DELPHI 10949001

MATERIAL

SEE CHART/SIEHE TABELLE

DRAWING NAME
SINGLE WIRE SEAL
EINZELDRAHTDICHTUNG

DRAWING NUMBER						
1 38 346 36						
SIZE	SCALE	FRAME NO	SHEET NO	STG	REV	N/P
A2	10:1	1 OF 1	1 OF 1	R	01	AC

VALIDATION BASED ON GTS

- PRESSURE LEAK TEST BASED ON THERMAL AGE AND SHOCK 0.5 BAR/30'
- THERMAL AGIN 300h 150°
- THERMAL SHOCK 300 CYCLES

①

VALIDATION ANGELEHNT AN GTS

- WASSERDRUCK-DICHTIGKEITS-TEST ANGELEHNT AN THERMISCHER ALTERUNG UND SCHOCK 0.5 BAR/30'
- THERMISCHE ALTERUNG 300h 150°
- THERMISCHER SCHOCK 300 ZYKLEN


KEY PRODUCT CHARACTERISTICS					
 SAFETY/COMPLIANCE	 FIT/FUNCTION	TOTAL ON DRAWING	0		
		LAST NO. USED	0		
 S/C CHECKPOINTS	 F/F CHECKPOINTS				
NO & TYPE	DESCRIPTION	RATIONALE		PTS	ZONE

REMARKS:

- NOT DIMENSIONED GEOMETRY HAS TO BE TAKEN FROM THE CORRESPONDING 3D DATA-FILE
- MAXIMUM DRAFT ANGLE 0° 30'
- MATERIAL SPECIFICATION: SILICON, AUTOLUBRICATION 50 SHORE 2% OIL
- SEALING AREA - RIBS MUST BE FREE OF FLASH, WITHOUT PARTING LINES, CUTS, SINKS, VOIDS AND KNIT.

BEMERKUNGEN:

- NICHT BEMASSTE GEOMETRIEN SIND DEN ENTSPRECHENDEN 3D DATENFILE ZU ENTNEHMEN
- ZULAESSIGE ENTFORMUNGSSCHRAEGE MAX. 0° 30'
- WERKSTOFF: SILIKON,
SELBSTSCHMIEREND 50 SHORE 2% OEL
- DICHTFLAECHEN - RIPPEN MUSSEN GRATFREI,
OHNE TRENNLINIEN, EINFALL, LUECKEN
SCHNITTE UND KERBEN SEIN.



☐ DIM TO CHECK PRUEFMASSE	DIMENSIONAL RANGE (MM)				
☐ DIM FOR HELP HILFSMASSE	FROM	0	> 3	> 6	> 10
		3		10	18
☐ THEORETIC DIM THEORE. MASSE	TOL. UNLESS OTHERWISE SPECIFIED				
		± 0.1	± 0.2	± 0.3	± 0.4
	ANGULAR TOLERANCE ± 2°				

Р

E

□

C

E

A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[35545727](#)