











SYMBOL DEFINITION		MISSING SYMBOLS	
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO OF INSPECTIONS REQUIRED	NO MISSING SYMBOL NUMBER	
	15		
	LAST NO. USED		15

CWS STATUS					REVISION HISTORY					AUTH	DR	APVD	APVD
DATE	STG	REV	N/P	CHG	ZONE								
17MR00	R	01	-	-		ALL ACTIVE PARTS - REDRAWN TO PD AND (20.7) WAS 20.7				199687	DAA	EAR	JA
06OC03	R	02	-	-		12015823, 12034046, 12015858 & 12129494 - REMOVED COLUMN V FROM CHART				246966	HAM	HAM	TM
19OC04	R	03	-	-		ALL ACTIVE PARTS - ADDED TERMINAL ID NOTE AND REMOVED PXX FROM GRAPHICS				260108	CTR	JAA	MKM
07JA05	R	04	-	-		12129494 - UPDATED PDM ATTRIBUTES				263066	HAM	HAM	WTM
21JUL05	R	05	-	-		12015858 & 12066214 - CREATED NISSAN CUSTOMER PART DRAWING				265749	JTV	FKV	TV
09MR06	R	06	-	-		12052217, 12066214 & 12129494 - UPDATED PDM ATTRIBUTES				276484	JTV	AUG	JS
03OC07	R	07	-	-		ALL PARTS - UPDATED PDM ATTRIBUTES				402517	JS	JS	WTM
05FE09	R	08	-	-		ALL ACTIVE PARTS - REVISED MAT'L CALLOUT TO GENERIC CALLOUT; 12020137 & 12052837 - WAS UNPLATED; 12015823 - OBSOLETE AND REPLACED BY 12034046; 12033821 - OBSOLETE AND REPLACED BY 12015858; 12103347 - OBSOLETE AND REPLACED BY 12066214 AND 12162131 - OBSOLETE AND REPLACED BY 12129494				407283	EAJ	FKV	RAP
20SE10	R	09	-	-		ALL ACTIVE PARTS - REVISED TOLERANCES COLUMN L				412089	AHY	JVM	JCO
12AUI5	R	10	-	-		15326543 MAKE OBSOLETE				429950	RCE	LES	VMP



TYPE 102
SAME AS TYPE 101
EXCEPT AS SHOWN

TYPE 101



TYPE 103
SAME AS TYPE 101
EXCEPT AS SHOWN

TYPE 104
SAME AS TYPE 101
EXCEPT AS SHOWN

- NOTES
- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED: DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
 - MAXIMUM BOX WIDTH AFTER CRIMPING IS 4 WHEN CRIMPED TO WIRE WITH CROSS SECTIONAL AREA OF 1 MM² OR LARGER.
 - DO NOT PROBE, TEST OR OTHERWISE CONTACT THE INTERIOR REGION (THE SPRING OR ANY MOVING PART) OF THIS TERMINAL. SEVERE DAMAGE CAN OCCUR, COMPROMISING THE PERFORMANCE OF THE ELECTRICAL INTERFACE.
 - "PXX" INDICATES P PLUS LAST TWO DIGITS OF MAKE DIE SERIES NUMBER (P01, P02, P03, ECT).

			0.406X32.54			12052837	08	AA	TIN PLATED COPPER ALLOY	3		12	3.04-3.2	104	4.6±0.4	6±0.4	0.7
			0.406X32.54			12020137	09	AA	TIN PLATED COPPER ALLOY	0.35		22	1.35-2	101	2.2±0.4	3.6±0.4	0.5
			0.406X32.54			15326543	A6		HIGH PERFORMANCE COPPER ALLOY	1-2		15	2.48-3.97	104	3.7±0.4	6±0.4	0.7
			0.406X32.54			12191316	D5		HIGH PERFORMANCE COPPER ALLOY	2-3		13	2.45-3.8	104	4±0.4	5.6±0.4	0.7
12162131	B4		0.406X32.54		COPPER ALLOY	12129494	D8		TIN PLATED COPPER ALLOY	2-3		13	2.45-3.8	104	4±0.4	5.6±0.4	0.7
12103347	D4		0.406X32.54		COPPER ALLOY	12066214	E7		TIN PLATED COPPER ALLOY	1-2		15	2.48-3.97	104	3.7±0.4	6±0.4	0.7
			0.406X32.54			12052284	E		TIN PLATED COPPER ALLOY	3		12	3.04-3.2	104	4.6±0.4	6±0.4	0.7
			0.406X32.54			12052217	D10		TIN PLATED COPPER ALLOY	0.35-0.5		21	1.84-2.51	102	2.4±0.2	3.8±0.3	0.5
12033821	L5		0.406X32.54		COPPER ALLOY	12015858	N7		TIN PLATED COPPER ALLOY	3-5		11	3.49-5.24	104	4.6±0.4	7.6±0.4	1
12033608	F		0.406X32.54		COPPER ALLOY					0.22		24	1.29-1.86	102	2.2±0.15	3.6±0.4	0.5
			0.406X32.54			12020136	F		TIN PLATED COPPER ALLOY	0.35		22	1.35-2	101	2.2±0.4	3.6±0.4	0.5
12020135	F		0.406X32.54		COPPER ALLOY	12080138	G		TIN PLATED COPPER ALLOY	TWO 0.35		222	1.35-2	101	3.6±0.4	5.3±0.4	0.5
			0.406X32.54			12015856	G		TIN PLATED COPPER ALLOY	0.5-0.8		19	2.03-3.12	103	3.2±0.4	5±0.4	-
12015826	G		0.406X32.54		COPPER ALLOY	12015859	H		TIN PLATED COPPER ALLOY	(1) 1-2 & (1) 0.5-0.8		1519	2.48-3.97 & 2.03-3.12	101	5.6±0.4	8.8±0.4	0.7
12015825	E		0.406X32.54		COPPER ALLOY					3-5		11	3.49-5.24	101	4.6±0.4	7.6±0.4	1
12015824	F		0.406X32.54		COPPER ALLOY	12015857	G		TIN PLATED COPPER ALLOY	1-2		15	2.48-3.97	101	3.7±0.4	6±0.4	0.7
12015823	L8		0.406X32.54		COPPER ALLOY	12034046	H11		TIN PLATED COPPER ALLOY	0.5-0.8 (1) 1-2 & (1) 0.5-0.8		19 1519	2.03-3.12 2.48-3.97 & 2.03-3.12	102 101	3.2±0.4 5.6±0.4	5±0.4 8.8±0.4	- 0.7
12015134	D		0.406X35.71		COPPER ALLOY												
12015084	D		0.406X35.71		COPPER ALLOY					3-5		11	3.49-5.24	101	4.6±0.4	7.6±0.4	1
12015083	D		0.406X35.71		COPPER ALLOY					1-2		15	2.48-3.97	101	3.7±0.4	6±0.4	0.7
12015054	D		0.406X35.71		COPPER ALLOY					0.5-0.8		19	2.03-3.12	101	3.2±0.4	5±0.4	-
PART NO	REV	N/P	MAT'L SIZE	MAT'L DESCRIPTION	PART NO	REV	N/P	MAT'L SPEC	SIZE (MMF)	ID	DIA	BLANK TYPE	E	F	L±0.3		
			UNPLATED					PLATED									

PROCESS SENSITIVE DIMENSION		DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED		DIMENSIONAL RANGE (MM)		CHART ID	
FROM	TO	FROM	TO	FROM	TO	FROM	TO
0	12	0	12	0	12	0	12
10.1	10.2	10.1	10.2	10.1	10.2	10.1	10.2
ANGULAR TOLERANCE 12°							

THIRD ANGLE PROJECTION		DO NOT SCALE		USE MATH DATA	

DELPHI
DELPHI PACKARD ELECTRICAL/ELECTRONIC ARCHITECTURE
WARREN, OH
COPYRIGHT DELPHI CORPORATION AND/OR ITS AFFILIATES. ALL RIGHTS RESERVED.

THIS DRAWING IS THE PROPERTY OF DELPHI CORPORATION AND CONTAINS DELPHI CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS CONTENTS OR DATA, WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.

DATE

DR

APVD1 E. MONCISVAIS 30NY96

APVD2 ENRIQUE BAEZ 30NY96

APVD3 ENRIQUE BAEZ 30NY96

APVD4

APVD5

SUBSTANCES OF CONCERN AND RECYCLED CONTENT, PER DELPHI (0244990)

MATERIAL SEE CHRT

DRAWING NAME TAXI TERM F W/P 280

DRAWING NUMBER 12015082

SIZE A0 SCALE 8:1 FRM NO 1 OF 1 SHEET NO 1 OF 1 STG REV N/P R 10

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[12015858](#) [12015858-L](#) [12015858-MR](#)