







STRIP .22
DEDUCT .38



1. WHEN CRIMPED ON CABLE THESE DIMENSIONS INCREASE BY .032 APPROXIMATELY.
2. OIL IS PERMISSIBLE ON TERMINAL.

TOLERANCE UNLESS
OTHERWISE SPECIFIED:

DECIMAL: ANGULAR ± 2

TWO PLACE ± 0.010

THREE PLACE ± 0.005

<div>DELPHI</div> <div>DELPHI PACKARD ELECTRICAL/ELECTRONIC ARCHITECTURE</div> <div>WARREN, OH</div> <div>COPYRIGHT 2006 DELPHI CORPORATION AND/OR ITS AFFILIATES.</div> <div>ALL RIGHTS RESERVED.</div> <div>THIS DRAWING IS THE PROPERTY OF DELPHI CORPORATION</div> <div>AND CONTAINS DELPHI CONFIDENTIAL INFORMATION.</div> <div>THE REPRODUCTION, DISTRIBUTION AND UTILIZATION</div> <div>OF THIS DOCUMENT OR ITS RELATED CDD WITH DATA,</div> <div>AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHERS,</div> <div>WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.</div>							
DR						DATE	
APVD:	TERRI	DAVIS				11SE06	
APVD:	TERRI	DAVIS				11SE06	
APVD:	ERIC	TRACEY				11SE06	
APVD:							
APVD:							
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 19949801							
MATERIAL SEE CHART							
DRAWING NAME							
TAXI TERM M 56 SERIES							
DRAWING NUMBER							
02977221							
SIZE	SCALE	FRAME	SHEET	N	ST6	REV	N/P

										121-16862		B	COPPER ALLOY											18-20	.095-.081		.160/.145	.180-.025	.053	.020	.055	.015	.020	.500	1		1	11																									
										121-16863		B3	COPPER ALLOY											14-16	.120-.101		.150	.205-.025	.053	.045	.075	.010	.020	.500	1		1	11																									
02997421	L3	.0320X.719		COPPER ALLOY												TWO 14-W		.120-.101		.240	.330	.030	.065	.013	.185	.010	.020	.625	2		2	1																															
02997462	M	.0320X.719		COPPER ALLOY												18-20 H.W.		.123-.107	1	.160/.145	.205	.030	.065	.020	.075	.015	.020	.625	1		2	1																															
02962009	L3	.0320X.719		COPPER ALLOY		02965479		L3	COPPER ALLOY	02977219		L	COPPER ALLOY			12		.145-.139		.195	.255	.030	.065	.080	.110	.010	.020	.625	1		2																																
02965509	M	.0320X.719		COPPER ALLOY		02965440		M2	COPPER ALLOY	18-20		.095-.081	1	.160/.145	.180-.025	.053	.020	.055	.015	.020	.500	1		1	1	1	1	1	1	1	1																																
02962450	L3	.0320X.719		COPPER ALLOY		02962958		L3	COPPER ALLOY	14-16		.120-.101		.150	.205-.025	.053	.045	.075	.010	.020	.500	1		1	1	1	1	1	1	1	1																																
PART NO	REV	N/P	MAT'L SIZE	MAT'L SPEC	PART NO	REV	N/P	MAT'L SIZE	MAT'L SPEC	PART NO	REV	N/P	MAT'L SIZE	MAT'L SPEC	PART NO	REV	N/P	MAT'L SIZE	MAT'L SPEC	PART NO	REV	N/P	MAT'L SIZE	MAT'L SPEC	PART NO	REV	N/P	MAT'L SIZE	MAT'L SPEC	PART NO	REV	N/P	MAT'L SIZE	MAT'L SPEC	CABLE GAUGE	CABLE DIA.	STAMP	C	D	E	F	G	H	J	K	L	WING CONST	TERM STRIP	HOLE CONST														
UNPLATED																																SILVER PLATED																															

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[02962958-L](#)