








SYMBOL DEFINITION			MISSING NUMBERS			DWG STATUS			ZONE	REVISION HISTORY			AUTH	DR	APVD	
			19,			DATE	STG	REV	N/P	CHG						
THE NUMBER INSIDE THE SYMBOL CORRESPONDS TO THE NUMBER ON THE INSPECTION REPORT FOR THIS DRAWING/PART NUMBER	TOTAL NO. OF SYMBOLS ON DRAWING	13		10N000	R	D1	-	-	-	-	CLEARED REVISION COLUMN; REDRAWN			000009	RAB	TLP
				07DE00	R	D2	-	-	-	UPDATED PDM ATTRIBUTES			205113	CJC	CJC	
	LAST NO. USED	29		18JA01	R	D3	-	-	-	-	ADDED OPTIONAL CONSTRUCTION			206108	CJC	CJC
				25AU03	R	D4	-	-	-	-	UPDATED PDM ATTRIBUTES			244950	HAM	HAM





OPTIONAL CONSTRUCTION PREFERRED



- NOTES
- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED: DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
 - RECOMMENDED HOLE SIZE FOR CLIP 6.1-6.6 DIA. HOLE IN 3.81 THICK STOCK.
 - THIS PART TO FIT 25MM CONVOLUTED CONDUIT.
 - THIS CLIP CAN NOT BE USED IN AN APPLICATION IN WHICH MORE THAN 45N FORCE IS APPLIED AGAINST X-TREE FEATURE.
 - MATERIAL RECYCLING CODE >PA66< PER ISO 11469. (2.3)X(0.1) RAISED CHARACTERS AS SHOWN TO BE LOCATED ON ANY EXTERIOR SURFACE. OPTIONAL CONSTRUCTION TO BE NO MATERIAL RECYCLING CODE.
 - (2.3)X(0.1) RAISED DELPHI CORPORATE BRAND TO BE LOCATED ON ANY EXTERIOR SURFACE, PREFERABLY VISIBLE AT FINAL ASSEMBLY. OPTIONAL CONSTRUCTION TO BE "PED" OR NO LOGO.



OPTIONAL CONSTRUCTION PREFERRED



DWO TYPE		PART DRAWING	
STYLE			
VOLUME (CM³)	5.462	DISTR CODE	D
ROUTING	6900		
UNLESS OTHERWISE SPECIFIED			
THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994 AS AMENDED BY THE 2018 DIMENSIONING AND TOLERANCING ADDENDUM-2018. SEPARATE PATTERNING OF FEATURES MAY BE GIVEN SEPARATELY REGARDLESS OF DATUM REFERENCES.			
ALL DIMENSIONS ARE IN MILLIMETERS			
REFERENCE			
THIRD ANGLE PROJECTION			
DO NOT SCALE			
USE MATH DATA			

(29) PROCESS SENSITIVE DIMENSION		DIMENSIONAL RANGE (MM)		CHART		E	
FROM	0	> 20	> 30	> 70	> 100		
TO	20	30	70	100			
TOLERANCE UNLESS OTHERWISE SPECIFIED							
1±0.15 1±0.2 1±0.3 1±0.4 1±0.5							
ANGULAR TOLERANCE 12°							

DELPHI		DELPHI PACKARD ELECTRIC SYSTEMS		WARREN, OH	
DR		DATE			
APVD1		26APB5			
APVD2 F. HESTON		30APB5			
APVD3 K.B. GERM					
APVD4					
APVD5					
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 10949001					
MATERIAL W3592001 PA66 HS 1M-BLK					
DRAWING NAME		MOUN CLIP 25 MM CDT			
DRAWING NUMBER		12059270			
SIZE	SCALE	FRAME NO	SHEET NO	STG	REV
A0	5:1	1	1	1	D4

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[12059270](#)