

②




Technical drawing of the 'L' model, showing a side view and a front view. The side view shows a height of 17.3. The front view shows a width of 13.8 and a depth of 12.5.

SECONDARY LOCKING
IN END LOCKED POSITION
ZWEITE KONTAKTSICHERUNG
IN ENDRASTSTELLUNG

SCALE / MASSSTAB:
2:1

WITH MATING PART
FLIEGENDE KUPPLUNG

SCALE / MASSSTAB:
2:1



KEY PRODUCT CHARACTERISTICS					
 SAFETY/COMPLIANCE		 FIT/FUNCTION		TOTAL ON DRAWING	0
 S/C CHECKPOINTS		 F/F CHECKPOINTS		LAST NO. USED	0
NO & TYPE	DESCRIPTION	RATIONALE		PTS	ZONE
-	-	-		-	-

REMARKS:

- KEYING A / OPTION 1 DRAWN
- DELIVERY STATUS AS DRAWN
- LETTERS AND ENGRAVINGS RAISED
- SIGN PLANE RECESSED
- SPC: STATISTICAL PROCESS CONTROL
- MAXIMUM CABLE CROSS SECTION 0.75 MM²
- MAXIMUM INSULATION CABLE DIAMETER 1.9 MM
- TERMINAL: MICRO TERMINAL SYSTEM 0.64;
- ① BASIC APPLICATION SEE DWG-NO.: 13506002
- MATING PART:
- RECEPTACLE HOUSING 4 WAY DWG-NO.: 13543933

BEMERKUNGEN:

- CODIERUNG A / VARIANTE 1 GEZEICHNET
- ANLIEFERUNGSGEZUSTIMT WIE GEZEICHNET
- SCHRIFTEN UND GRAVUREN ERHABEN
- SCHRIFTLAECHE VERTIEFT
- SPC: STATISTISCHE PROZESSKONTROLLE
- MAX. ZULAESSIGER LEITUNGSGRUEENSCHNITT 0,75 MM²
- MAX. AUSSENDURCHMESSER ISO LIEFERUNG 1,9 MM
- KONTAKTSYSTEM: MICRO THERMAL SYSTEM 0,64;
- STANDARD SYSTEM SIEHE ZCHG-NR.: 1350602;
- PASSENDES GEGENSTUECK:
- FLASCHENTECHNUELSENGEMAEUSE 4 POL., ZCHG-NR.: 13543933

		DIMENSIONAL RANGE (MM)								CHART	
		FROM	> 0	> 20	> 30	> 70	> 100	> 150	> 200	> 250	> 300
		TO	20	30	70	100	150	200	250	300	400
☐	DIM TO CHECK PRUEFMASSE										
☐	DIM FOR HELP HILFSSMASSE										
TOLERANCE UNLESS OTHERWISE SPECIFIED											
☐	THEORETIC THEORE. MASSE	±0.15	±0.2	±0.3	±0.4	±0.5	±0.6	±0.8	±1	±1.5	±2
ANGULAR TOLERANCE ±2°											

[illegible]

SCALE / MASSTAB:
1 : 1



TYP PART DRAWING WEIGHT (GRI) 2.2 VOLUME (DM³) ROUTING		DISTR CODE D	
UNLESS OTHERWISE SPECIFIED GENERAL TOLERANCES ACCORDING TO: SEE CHART SIEHE TABELLE GD&T ACCORDING TO: ISO 1101			
REFERENCE PART DRAWING			
FIRST ANGLE PROJECTION 			
DO NOT SCALE USE MATH DATA			
			

• APTIV •

CONNECTION SYSTEMS

D-42119 WUPPERTAL

COPYRIGHT 2008 APTIV. ALL RIGHTS RESERVED.

THIS DRAWING IS THE PROPERTY OF APTIV AND CONTAINS APTIV CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD DATA, AS WELL AS ANY DISSEMINATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.

DIESE ZEICHNUNG IST EIGENTUM DER FIRMA APTIV UND ENTHÄLT APTIV VERTRAULICHE INFORMATIONS BEZÜGLICH KONSTRUKTION, VERTEILUNG UND NUTZUNG DIESER DOKUMENTE ODER DEREN ZUGEHÖRIGE CAD DATEN, ODER AUCH DAS KOPIEREN VON DEREN INHALT ANSONSTEN OHNE AUSDRÜCKLICHE BERECHTIGUNGSPERMISSION DURCH APTIV UNZULÄSSIG.

		DATE	
DR	W. TARNAWSKI	13	J 07
APR02	O. HACKEL	18	AP 08
APR03	M. SIKORA	21	MY 08
APR04			
APR05			
APR06			

SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER APTIV (10494001)
 POTENTIAL DEFRAUDABLE STOFFE UND REZUKLATIONS-
 GEHALT NACH APTIV (10494001)

MATERIAL:

SEE CHART / SIEHE TABELLE

RANKING NAME

TAB HOUSING 4 WAY
 FOR MTS 0.64

FLACHSTECKERGEKKE 4 POL.
 FUER MTS 0.64

RANKING NUMBER

36

SIZE	SCALE	FRAME NO	1 SHEET	1	STO	REV	NUP
4	5:1	1	O	F	I	R	02

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[13654869](#)