





NOTE	SPECIFICATIONS
1	MALE CONNECTOR ACCORDING TO APTIV SPECIFICATION: CAGE TBD
2	MALE CONNECTOR ACCORDING TO: -TEMPERATURE CLASS T2 -ENGINE VIBRATOR CLASS V1 -SEALING CLASS E0
3	USER'S MANUAL: PU164
4	DELIVERY CONNECTOR WEIGHT : 3,9g
5	NO WAFER HINGE OR WAFER HINGE BROKEN ALLOWED
6	VISUAL DEFECTS ON NO FUNCTIONNAL AREAS ALLOWED
	MATERIAL CODE
	MOLD CAVITY NUMBER
	PART REVISION NUMBER
	WAY NUMBERS
	SUPPLIER LOGO
	PART NUMBER
	DATE CLOCK
	MODULE NAME AND ASSEMBLY DIRECTION

	DIM TO CHECK	DIMENSIONAL RANGE (MM)	CHART	E1
	DIM FOR HELP	FROM TO	> 0 > 20 > 30 > 70 > 100 > 150 > 200 > 250 > 300 > 400	
	THEORETIC DIM		TOLERANCE UNLESS OTHERWISE SPECIFIED	
			±0.15 ±0.2 ±0.3 ±0.4 ±0.5 ±0.6 ±0.8 ±1 ±1.2	
			ANGULAR TOLERANCE ±2°	



DWG STATUS

DATE06JA22

STGR

REV R

N/P01

CHG

ZONE

REVISION HISTORY

AUTH

DR P.BAL

APVD1 J.LAL

APVD2 J.WOI

INITIAL RELEASE

14-Feb-22

Time: 08:34:11

3D VIEW

SCALE 1:1

DWG TYP

PART DRAWING

WEIGHT (GR)

SEE NOTE

VOLUME (CM³)

ROUTING

DISTR CODE

D

UNLESS OTHERWISE SPECIFIED

GENERAL TOLERANCES ACCORDING TO:

SEE CHART

GD&T ACCORDING TO:

ISO 1101

REFERENCE

FIRST ANGLE PROJECTION

DO NOT SCALE

USE MATH DATA

• APTIV •

CONNECTION SYSTEMS

Chennai, India

COPYRIGHT 2022 APTIV. ALL RIGHTS RESERVED.

THIS DRAWING IS THE PROPERTY OF APTIV AND CONTAINS APTIV CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD MATH DATA, AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.

DR P.BALAJI

APVD1 J.LALU

APVD2 MOINEAU JOHANN

APVD3

APVD4

APVD5

SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER APTIV 10949001

MATERIAL

SEE TABLE

DRAWING NAME

MODULE A 22 WAYS

DRAWING NUMBER

33400753

SIZE A1

SCALE 2:1

FRAME NO 1 OF 1

SHEET NO 1 OF 1

STG R

REV 01

N/P

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[33400753](#)