



DO NOT SCALE

PACKARD ELECTRIC DIVISION
GENERAL MOTORS CORPORATION
WARREN, OHIO



KNURL DETAIL - 24 T.P.I. FETTER

SCALE 20:1

- NOTES —1. HARDNESS TO BE ROCKWELL "B" 85-105
(TO BE CHECKED ON THREADED END.)
2. ZINC PLATE AND RED CHROMATE TREATMENT
PER GM-4342-M CODE 20 Z 24.
3. PART MUST BE FREE OF RUST AND OILY GRIT.
4. BOLT MUST WITHSTAND 100 IN-LBS THREAD STRIP
TORQUE.
5. "*" THIS DIMENSION MUST BE MAINTAINED
THROUGHOUT LENGTH OF HEAD.
6. PARTS TO BE SHIPPED TO CUSTOMER IN
PACKAGES OF 13.6 KG (30LBS.) MAX.

[illegible]

PART NO.
1218 6210

OBSOLETE

PED/INTEGRATED EMS		FILE SPEC: *****USER***** DGN#SPECIFICATION***** *****TIME*****	
THIRD ANGLE PROJECTION		ENGLISH DIMENSIONS ARE IN INCHES UNLESS OTHERWISE SPECIFIED.	
			
CODE NO. 6901		TOLERANCE UNLESS OTHERWISE SPECIFIED DECIMAL: TWO PLACE $\pm .01$ THREE PLACE $\pm .005$	
Q.C. -R-304		ANGULAR $\pm 3^\circ$	
DWG. DATE 030C95	SCALE 2:1	DR. RON BURNS	030C95
EST. NO.		CK. RON BURNS	DATE 030C95
REFERENCE NO. 12015116		APPR. J. HORIUCHI	DATE 170C95
		APPR.	DATE
MATERIAL SPEC. GM 260M (1018-1020) STEEL			
NAME BOLT - ROUND HEAD W/6 LOBED RECESS			
PART NO. 1218 6210			SIZE C

PACKARD ELECTRIC

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)
[12186210](#)