

Crimp Information Sheet

DELPHI

Terminal Part Number: 10717434
 Surface Plating: SN
 Material Thickness [mm]: -
 Cross Section [mm²]: 0,50 | 0,75 | 1,00

*This document is non-contractual
and for information only.*

*For more information, please
consult your local sales office*

Cable Type codes: 2010
 Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY
 Insulation Range Φ [mm]: 1,30 - 2,10
 Seal(s): NONE

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
2010 0,50		1,50	80	1,35	0,05	2,20	0,10	2,65	0,10	3,10	0,10
2010 0,75		1,75	120	1,45	0,05	2,25	0,10	2,80	0,10	3,10	0,10
2010 1,00		1,95	160	1,55	0,05	2,25	0,10	2,90	0,10	3,10	0,10

Cable type code legend:

2010: ACW0219, FIAT T2 FLRY, FL RENAULT R1, FL RENAULT R3, FLR
 (AGP0219), FLR2X-A, FLR4Y-A, FLR9Y, FLRX-B, FLRY-A, FLRYB, FLRY-B



Industry Designator: DIN

Conductor Material: COPPER

Conductor Plating: NONE

Insul. Material: PA, POLYOLEFIN, PP, PVC, SYNTHRESIN, XLCOPOLY, XLPBT, XLPE,
 XLPE/PVDF, XLPVC

Insul. Wall Designator: THIN



Terminal Part Number: 10717434

Surface Plating: SN

Material Thickness [mm]: -

Cross Section [mm²]: 0,50

Cable Type codes: 2010 + 2010

Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY

Seal(s): NONE

This document is non-contractual
and for information only.

For more information, please
consult your local sales office

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
2010 0,50 + 2010 0,50	TOP	1,50 + 1,50	80	1,35	0,05	2,25	0,10	3,30	0,10	3,25	0,10

Cable type code legend:

2010: ACW0219, FIAT T2 FLRY, FL RENAULT R1, FL RENAULT R3, FLR (AGP0219), FLR2X-A, FLR4Y-A, FLR9Y, FLRX-B, FLRY-A, FLRYB, FLRY-B



Industry Designator: DIN

Conductor Material: COPPER

Conductor Plating: NONE

Insul. Material: PA, POLYOLEFIN, PP, PVC, SYNTHRESIN, XLCOPOLY, XLPBT, XLPE, XLPE/PVDF, XLPVC

Insul. Wall Designator: THIN



Crimp Information Sheet

DELPHI

Terminal Part Number: 10717434
 Surface Plating: SN
 Material Thickness [mm]: -
 Cross Section [mm²]: 0,50 | 0,75 | 1,00

*This document is non-contractual
 and for information only.*



*For more information, please
 consult your local sales office*

Cable Type codes: 2011
 Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY
 Insulation Range Φ [mm]: 2,00 - 2,70
 Seal(s): NONE

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
2011 0,50		2,15	80	1,35	0,05	2,20	0,10	2,80	0,10	3,10	0,10
2011 0,75		2,28	120	1,45	0,05	2,25	0,10	2,90	0,10	3,10	0,10
2011 1,00		2,54	160	1,55	0,05	2,25	0,10	3,00	0,10	3,10	0,10

Cable type code legend:

2011: FL33X, FLK, FLY, FLYKW, IH WIRE
 Industry Designator: DIN
 Conductor Material: COPPER
 Conductor Plating: NONE
 Insul. Material: P/EST, PE, PVC, XLPE
 Insul. Wall Designator: REGULAR



Terminal Part Number: 10717434
Surface Plating: SN
Material Thickness [mm]: -
Cross Section [mm²]: 0,50 | 0,60 | 0,75 | 1,00

This document is non-contractual
and for information only.



For more information, please
consult your local sales office

Cable Type codes: 2044
Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY
Insulation Range Φ[mm]: 1,40 - 2,10
Seal(s): NONE

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
2044 0,50		1,50	80	1,35	0,05	2,25	0,10	2,65	0,10	3,15	0,10
2044 0,60		1,80	80	1,50	0,05	2,40	0,10	3,00	0,10	2,90	0,10
2044 0,75		1,78	120	1,45	0,05	2,25	0,10	2,80	0,10	3,15	0,10
2044 1,00		1,96	160	1,55	0,05	2,30	0,10	2,90	0,10	3,20	0,10

Cable type code legend:

2044: A3Z, F3Z, FL RENAULT A3Z
Industry Designator: NRA
Conductor Material: COPPER
Conductor Plating: NONE
Insul. Material: XLPA/PVDF, XLPE, X-POLY ZH
Insul. Wall Designator: THIN



Terminal Part Number: 10717434
Surface Plating: SN
Material Thickness [mm]: -
Cross Section [mm²]: 0,35 | 0,50

This document is non-contractual
and for information only.



For more information, please
consult your local sales office

Cable Type codes: 2044 + 2044
Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY
Seal(s): NONE

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
2044 0,35 + 2044 0,50		1,33 + 1,50	50	1,60	0,05	2,40	0,10	3,35	0,10	2,95	0,10

Cable type code legend:

2044: A3Z, F3Z, FL RENAULT A3Z
Industry Designator: NRA
Conductor Material: COPPER
Conductor Plating: NONE
Insul. Material: XLPA/PVDF, XLPE, X-POLY ZH
Insul. Wall Designator: THIN



Terminal Part Number: 10717434
Surface Plating: SN
Material Thickness [mm]: -
Cross Section [mm²]: 0,50 | 0,60 | 1,00 | 1,50

This document is non-contractual
and for information only.



For more information, please
consult your local sales office

Cable Type codes: 2054
Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY
Insulation Range Φ[mm]: 1,40 - 2,40
Seal(s): NONE

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
2054 0,50		1,55	70	1,50	0,05	2,40	0,10	2,95	0,10	2,90	0,10
2054 0,60		1,83	80	1,50	0,05	2,40	0,10	3,00	0,10	2,90	0,10
2054 1,00		2,07	115	1,65	0,05	2,40	0,10	3,10	0,10	2,95	0,10
2054 1,50		2,25	120	1,70	0,05	2,40	0,10	2,90	0,10	2,90	0,10

Cable type code legend:

2054: PSA T2 IR, PSA T3 IR, PSA T3 ZH IR, PSA T4 LH IR
Industry Designator: PSA
Conductor Material: COPPER
Conductor Plating: NONE
Insul. Material: POLYOLEFIN, PVC, X-POLY
Insul. Wall Designator: IR



Terminal Part Number: 10717434

Surface Plating: SN

Material Thickness [mm]: -

Cross Section [mm²]: 0,35

Cable Type codes: 2054 + 2054

Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY

Seal(s): NONE

This document is non-contractual
and for information only.

For more information, please
consult your local sales office

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
2054 0,35 + 2054 0,35		1,33 + 1,33	50	1,55	0,05	2,40	0,10	3,30	0,10	2,95	0,10

Cable type code legend:

2054: PSA T2 IR, PSA T3 IR, PSA T3 ZH IR, PSA T4 LH IR



Industry Designator: PSA

Conductor Material: COPPER

Conductor Plating: NONE

Insul. Material: POLYOLEFIN, PVC, X-POLY

Insul. Wall Designator: IR



Terminal Part Number: 10717434
Surface Plating: SN
Material Thickness [mm]: -
Cross Section [mm²]: 0,50 | 0,75 | 1,00

This document is non-contractual
and for information only.



For more information, please
consult your local sales office

Cable Type codes: 2055
Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY
Insulation Range Φ[mm]: 1,40 - 2,10
Seal(s): NONE

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
2055 0,50		1,50	80	1,35	0,05	2,25	0,10	2,55	0,10	3,15	0,10
2055 0,75		1,70	120	1,45	0,05	2,25	0,10	2,70	0,10	3,15	0,10
2055 1,00		1,93	160	1,55	0,05	2,30	0,10	2,80	0,10	3,20	0,10

Cable type code legend:

2055: AGP0119, RENAULT F3Z
Industry Designator: NRA
Conductor Material: COPPER
Conductor Plating: NONE
Insul. Material: POLYOLEFIN
Insul. Wall Designator: THIN



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[10717434](#)