





MISSING SYMBOLS		DWG STATUS				ZONE	REVISION HISTORY	AUTH	DR	APV	P2
		DATE	TSB	REV	N/P						
NO MISSING SYMBOL NUMBER		01DEC3	R	01	-	-	SHEET 2 PART DRAWING CREATED AND RELEASED.	248906	JEB	JEB	RAF
		13JAO4	R	02	-	-	15482715-RELEASED; 15485959-RELEASED; 15485963-RELEASED; ALL PARTS-REVISED NOTE 21: PARTS+DIM 9 WAS 16 +0.3, DIM (25) WAS 25 +0.15	253040	ADK	END	RAF
		16MR04	R	03	-	-	ALL PARTS - ADDED NOTE & DIMS 3 PLCS; 2X (4) TYP WAS 2X 4 TYP & 2X (2.7) TYP WAS 2X 2.1 TYP; REV'D NOTE #2: MATL SPEC WAS M5302XXX - C102	252912	MAC	MAC	RAF
		07AP04	R	04	-	-	ALL PARTS - (9,5) WAS 9,5	253575	EES	EES	RAF
		26MY04	R	05	-	-	ALL PARTS - ADDED "NO. OF WIRES" RETURN TO CHART & ADDED BUNDLE SIZES 15485963, 15485961, 15485959 - REVISED MATERIAL SPEC	255191	EES	EES	RAF
		29JNO4	R	06	-	-	15476582, 15482713, 15482715 - 17 WAS 12; 7.7 +0.3 WAS 12.7 +0.3	256415	ADK	ADK	RAF
		22JUL04	R	07	-	-	15496902-RELEASED; 15496903-RELEASED; 15498973-RELEASED	257060	CJP	CJP	RAF
		16SEO5	R	08	-	-	13523333 ADDED AND RELEASED	272542	MM	MM	LN
		21OC05	R	09	-	-	19,4 TIN PLATING SEE NOTE 4 25,5 MAX ALLOWABLE WAS 19,5 TIN PLATING	273949	MM	MM	LN



TYPE 201, 202, 203

## NOTES




1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:  
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND  
AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION  
(SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL  
OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL  
BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
2. TERMINAL MUST BE MADE USING FIN-LUBE 0177 STAMPING LUBE OIL.  
ANY OTHER LUBRICANT MUST BE APPROVED BY PRODUCT ENGINEERING.
3. TERMINALS ARE TO BE SINGULATED FROM CARRIER AND PLACED  
IN CLEAN PLASTIC BAGS PRIOR TO STORAGE AND SHIPMENT.
4. PRE-PLATED SELECTIVE MATTE TIN (99.9%) AS DIMENSIONED.



TYPE 201  
SCALE 1:1

15496902	01	AA	-	M5621LN3 - C102	210	NO	6.5-13.5	1-12
15496902	01	-	-	M5302B85 - C102	209	NO	6.5-13.5	1-12
15496903	01	-	-	M5302B85 - C102	208	NO	6.5-13.5	1-12
15498973	01	-	-	M5302B85 - C102	207	NO	6.5-13.5	1-12
15485963	01	AD	-	M5302B85 - C102	206	NO	6.5-13.5	1-12
15485961	01	AD	-	M5302B85 - C102	205	YES	6.5-13.5	1-12
15485959	01	AD	-	M5302B85 - C102	204	NO	6.5-13.5	1-12
15476582	02	-	-	M5302B91 - C102	203	YES	6.5-13.5	1-12
15482713	02	-	-	M5302B91 - C102	202	YES	6.5-13.5	1-12
15482715	02	-	-	M5302B91 - C102	201	YES	6.5-13.5	1-12
PART NO	REV	N/P	STATUS	MATERIAL SPECIFICATION	TYPE	ANTI-ROTATION	BUNDLE SIZE MM <sup>2</sup>	NO. OF WIRES (MIN-MAX)

20		PROCESS SENSITIVE DIMENSION	
DIMENSIONS ENCLOSED IN ( ) INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED			
DIMENSIONAL RANGE (MM)		CHART C	
FROM	0		
TO	12	>12	
TOLERANCE UNLESS OTHERWISE SPECIFIED			
	±0.1	±0.2	
ANGULAR TOLERANCE ±2°			

DWG TYPE		PART DRAWING	
STYLE			
VOLUME (CM)		DISTR CODE	
		D	
UNLESS OTHERWISE SPECIFIED			
<p>THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994          AS AMENDED BY THE 2018 DIMENSIONING AND TOLERANCE          PRACTICE ADDENDUM - 1997. ALL GEOMETRIC TOLERANCES          AND RELATED DATUMS APPLY. RULE #1 PERFECT FORM AT          MMC. DOES NOT RELATE TO SURFACE FEATURES.          SEPARATE POSITION CALLOUTS ARE REQUIRED SEPARATELY,          REGARDLESS OF DATUM REFERENCE.          ALL DIMENSIONS ARE IN MILLIMETERS</p>			
REFERENCE			
THIRD ANGLE PROJECTION	DO NOT SCALE		
	USE MATH DATA		

<h1 style="text-align: center;">DELPHI</h1> <p style="text-align: center;">DELPHI PACKARD ELECTRIC SYSTEMS WARREN, OH</p>					
DR		DATE			
APV01	J. BANKSTON	01DE03			
APV02	J. BANKSTON	01DE03			
APV03	R. PUHL	02DE03			
APV04					
APV05	SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 109493001				
MATERIAL SEE CHART					
DRAWING NAME					
TAXI TERM RING					
DRAWING NUMBER					
15485965					
SIZE A0	SCALE 2:1	FRAME 1 OF 1	SHEET NO 2 OF 2	STD R9	REV N/

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[15485963](#)