

# MEA-2410-SMA

2.4/5.0 GHz ISM Connector Mount  
Part #: 100-00275-01

## Description

The MEA-2410-SMA connector mount Antenna is a low profile antenna solution, with a very high-performance ideal for maintaining constant network connectivity. The MEA-2410-SMA covers all WiFi, BT, ZigBee, and ISM standard frequencies. This is an ideal antenna for telematics systems, remote surveillance, asset tracking and any IOT system applications. The MEA-2410-SMA is easy to install with maximum durability offering IP67 rated housing and anti-rotation mounting. The high performance and low profile make this antenna ideal for the most challenging installations.

## Electrical Specification

Parameter	Specification	
Frequency Range	2410-2490 MHz	4920-5925MHz
Band	2.4 GHz	5.0GHz
Return Loss	-14.7 dB	-12.8 dB
VSWR	1.4:1	1.7:1
Efficiency	60%	83%
Peak Gain	4.0 dBi	5.2 dBi
Average Gain	-2.2 dB	-0.9 dB
Impedance	50 $\Omega$	
Polarization	Linear	
Radiation Pattern	Omni-Directional	
Max Input Power	25 W	

## Mechanical Specification

Parameter	Specification
Antenna Dimensions	Ø 10 x 56 mm
Operating Temperature	-40°C to + 85°C
Mounting Type	Connector Mount
Connector	Most RF Connectors
Radome/Color	ABS UV Stable/ Black
Substance Compliance	RoHS

\*Mounted on Ground Plane 70 x 35 cm








## Features

- 2.4/5.0 GHz ISM, 2410-2490MHz, 4920-5925MHz
- Easy mounting: Connector Mount
- High Gain
- Dimensions Ø 10 x 56 mm

## Applications

- WIFI applications
- Navigation and telematics systems
- IoT applications
- Automotive connectivity
- Multimedia
- Fleet management
- HD video and audio streaming



Maxtena Inc.  
 7361 Calhoun Place, Suite 102  
 Rockville, MD 20855  
 1-877-629-8362  
[info@maxtena.com](mailto:info@maxtena.com)  
[www.maxtena.com](http://www.maxtena.com)



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Maxtena:

[MEA-2410-SMA](#)