






SYMBOL DEFINITION		MISSING SYMBOLS	
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL ( ) DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO OF INSPECTIONS REQUIRED	NO MISSING SYMBOL NUMBER	
	11		
	LAST NO. USED		
	11		

DWG STATUS				ZONE	REVISION HISTORY	AUTH	DR	APVD1	APVD2
DATE	STG	REV	N/P						
12JL05	R	01	-	-	ALL ACTIVE PARTS - REDRAWN TO PD AND UPDATED MAT'L SPEC	269828	AMG	AMG	ET
23AU05	R	02	-	-	02962967 - MATERIAL SPEC WAS M0592202	271562	PCP	PCP	ET
18SE07	R	03	-	-	02962967 - OBSOLETE; 02973872 - MAT'L SPEC WAS M2043002, ADDED APPLICATION DATA & APPEARANCE ITEM NOTES, REMOVED MATING COMPONENTS NOTE AND REVISED MAT'L CALLOUT TO GENERIC CALLOUT	402367	RTV	JVM	JCC
16SE08	R	04	-	-	02962967 - REINSTATED	406104	FBF	ERM	JCC




MATING END



CABLE END

NOTES

- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:  
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
- MATERIAL RECYCLING CODE PER ISO 11469. (.100)X(.010) RAISED CHARACTERS AS SHOWN TO BE LOCATED ON ANY EXTERIOR SURFACE. OPTIONAL CONSTRUCTION TO BE NO MATERIAL RECYCLING CODE.
- (.100)X(.010) RAISED DELPHI CORPORATE BRAND TO BE LOCATED ON ANY EXTERIOR SURFACE, PREFERABLY VISIBLE AT FINAL ASSEMBLY. OPTIONAL CONSTRUCTION TO BE "PED" OR NO LOGO.
- THIS PRODUCT IS NOT CATEGORIZED AS AN APPEARANCE ITEM, MINOR IMPERFECTIONS INCLUDING, BUT NOT LIMITED TO, FLOW MARKS, COLOR BLEMISHES, GATE VESTIGE, AND SOFT FLASH THAT DO NOT AFFECT THE FIT, FORM, OR FUNCTION OF THE PART ARE PERMISSIBLE PER NAP 4.10-18.
- FOR APPLICATION DATA SEE THE INDIVIDUAL APPLICATION DRAWINGS.



PART NO	REV	N/P	STATUS	MATERIAL SPECIFICATION AND COLOR	VOLUME CM³
08900322	D4	-	OBSOLETE	POLYAMIDE COMPOUND LT GRAY	-
02973872	O5	-		POLYAMIDE COMPOUND BLACK	1.823
02962967	D8	-		ABS COMPOUND NATURAL	1.823

DIMENSIONAL RANGE (IN)	CHART	H
FROM 0	>.750	>2.50
TO .750	1.250	2.750
	4.000	>4.000

TOLERANCE UNLESS OTHERWISE SPECIFIED  
 ±.005 | ±.010 | ±.012 | ±.016 | ±.020  
 ANGULAR TOLERANCE ±2°

DWG TYPE PART DRAWING	
STYLE	
VOLUME (CIP) SEE CHART	DISTR CODE D
UNLESS OTHERWISE SPECIFIED THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994 AS AMENDED BY THE 0M GLOBAL DIMENSIONING AND TOLERANCING ADDENDUM-2001. SEPARATE PATTERNS OF FEATURES MAY BE GAGED SEPARATELY REGARDLESS OF DATUM REFERENCES.	
ALL DIMENSIONS ARE IN INCHES	
THIRD ANGLE PROJECTION	DO NOT SCALE USE MATH DATA

**DELPHI**  
 DELPHI PACKARD ELECTRICAL/ELECTRONIC ARCHITECTURE  
 WARREN, OH

DR	DATE
APVD1 ANDRES MENDEZ	12JL05
APVD2 ANDRES MENDEZ	12JL05
APVD3 ERIC TRACEY	15JL05
APVD4	
APVD5	

SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 10945001

MATERIAL SEE CHART

DRAWING NAME  
TAXI CONN F 56 SERIES

DRAWING NUMBER  
**02973874**

SIZE	SCALE	FRAME NO	SHEET NO	STG	REV	N/P
A1	5:1	1 OF 1	1 OF 1	R	04	-

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[02962967](#)