



PEC3103M1Q

ESD Protection

Voltage

3.3 V



Features

- IEC61000-4-2(ESD): ± 30 kV Air, ± 30 kV Contact
- IEC61000-4-4(EFT): 40 A(5/50 ns)
- IEC61000-4-5(Lightning): 5 A(8/20 uS)
- Low leakage current, maximum of 1uA at rated voltage
- Ultra low capacitance
- Low clamping voltage
- Lead free in compliance with EU RoHS 2.0
- Green molding compound as per IEC 61249 standard

Mechanical Data

- Case: Molded plastic, DFN1006-2L
- Terminals: Solder plated, solderable per MIL-STD-750, Method 2026
- Approx. Weight: 0.00002 ounces, 0.0006 grams

DFN1006-2L



Maximum Ratings and Thermal Characteristics (T_A = 25 °C unless otherwise noted)

PARAMETER	SYMBOL	LIMIT	UNITS
ESD IEC61000-4-2(Air)	V _{ESD}	± 30	kV
ESD IEC61000-4-2(Contact)		± 30	
Operating Junction Temperature Range	T _J	-55~150	°C
Storage Temperature Range	T _{STG}	-55~150	°C



PEC3103M1Q

Electrical Characteristics ($T_A = 25^\circ\text{C}$ unless otherwise noted)

PARAMETER	SYMBOL	TEST CONDITION	MIN.	TYP.	MAX.	UNITS
Reverse Stand-Off Voltage	V_{RWM}	-	-	-	3.3	V
Punch-Trough Voltage	V_{PT}	$I_{PT} = 2\ \mu\text{A}$	3.5	-	-	V
Snap-Break Voltage	V_{SB}	$I_{SB} = 50\ \text{mA}$	2.8	-	-	V
Reverse Leakage Current	I_R	$V_R = 3.3\ \text{V}$	-	-	0.5	μA
Clamping Voltage	V_{CL}	$I_{PP} = 1\ \text{A}, t_p = 8/20\ \mu\text{s}$	-	-	6	V
		$I_{PP} = 5\ \text{A}, t_p = 8/20\ \mu\text{s}$	-	-	8	
Clamping Voltage TLP (Note 1)	$V_{CL}^{(1)}$	$I_{PP} = 8\ \text{A}, t_p = 100\ \text{ns}$	-	7	-	V
		$I_{PP} = 16\ \text{A}, t_p = 100\ \text{ns}$	-	8.5	-	
Dynamic Resistance	R_{DYN}	$t_p = 100\ \text{ns}$	-	0.19	-	Ω
Off State Junction Capacitance	C_J	0Vdc Bias $f = 1\ \text{MHz}$	-	-	10	pF

NOTES:

1. Testing using Transmission Line Pulse (TLP) conditions: $Z_0 = 50\ \Omega$, $t_p = 100\ \text{ns}$.



PEC3103M1Q

TYPICAL CHARACTERISTIC CURVES




Fig.1 Typical Peak Clamping Voltage




Fig.2 Pulse Waveform




Fig.3 Typical Junction Capacitance




Fig.4 TLP Measurement





PEC3103M1Q

Part No Packing Code Version

Part No Packing Code	Package Type	Packing Type	Marking	Version
PEC3103M1Q_R1_00001	DFN1006-2L	10K / 7" Reel	K3	Halogen Free

Packaging Information & Mounting Pad Layout





PEC3103M1Q

Disclaimer

- Reproducing and modifying information of the document is prohibited without permission from Panjit International Inc..
- Panjit International Inc. reserves the rights to make changes of the content herein the document anytime without notification. Please refer to our website for the latest document.
- Panjit International Inc. disclaims any and all liability arising out of the application or use of any product including damages incidentally and consequentially occurred.
- Panjit International Inc. does not assume any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.
- Applications shown on the herein document are examples of standard use and operation. Customers are responsible in comprehending the suitable use in particular applications. Panjit International Inc. makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.
- The products shown herein are not designed and authorized for equipments requiring high level of reliability or relating to human life and for any applications concerning life-saving or life-sustaining, such as medical instruments, transportation equipment, aerospace machinery et cetera. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Panjit International Inc. for any damages resulting from such improper use or sale.
- Since Panjit uses lot number as the tracking base, please provide the lot number for tracking when complaining.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panjit:

[PEC3103M1Q_R1_00001](#)