









TYPE 102
SAME AS TYPE 101
EXCEPT AS SHOWN
(OPTION B)




6.93 ±0.1 6.93 ±0.1





TYPE 103
SAME AS TYPE 101
EXCEPT AS SHOWN
(OPTION C)




TYPE 104
SAME AS TYPE 101
EXCEPT AS SHOWN
(OPTION D)



SECTION A - A



TYPE 101
(OPTION A)



NOTES

- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND
AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION
(SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL
OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL
BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
- THIS PART ACCEPTS THE FOLLOWING COMPONENTS OR EQUIVALENT:
TERMINAL 13526678 & 13526680
MAX INSULATION CRIMP MUST BE LESS
THAN 3.1 HIGH AND 2.75 WIDE.
- FOR MATING CONFIGURATION REQUIREMENTS, SEE CHART.
- TERMINAL POSITION REQUIRES THE USE OF THE DELPHI BUILD/RING OUT
HOLDER OR DELPHI APPROVED EQUIVALENT. FAILURE TO DO SO CAN RESULT
IN UNSEATED TERMINALS.
- PARTS NOT DESIGNED TO ACCEPT CPA.

PART NO	REV	N/P	MATERIAL SPECIFICATION AND COLOR	VOLUME	TYPE	OPTION	MATING CONNECTOR / EWCAP P/N
13586109	01	AB	M4695007 PBT GRN	2.037	104	D	150-U-002-1-D01
13586108	01	AB	M4695027 PBT RST	2.182	103	C	150-U-002-1-C01
13586107	01	AB	M4695003 PBT GRA	2.179	102	B	150-U-002-1-B01
13586106	01	AB	M4695002 PBT BLK	2.179	101	A	150-U-002-1-A01

DIMENSIONAL RANGE (MM)		CHART	ET
FROM	> 0	> 20	> 30
TO	20	30	70
	70	100	150
	150	200	250
	250	300	400
	400	500	600
	600	700	800
	800	900	1000
	1000	1100	1200
	1200	1300	1400
	1400	1500	1600
	1600	1700	1800
	1800	1900	2000
	2000	2100	2200
	2200	2300	2400
	2400	2500	2600
	2600	2700	2800
	2800	2900	3000
	3000	3100	3200
	3200	3300	3400
	3400	3500	3600
	3600	3700	3800
	3800	3900	4000
	4000	4100	4200
	4200	4300	4400
	4400	4500	4600
	4600	4700	4800
	4800	4900	5000
	5000	5100	5200
	5200	5300	5400
	5400	5500	5600
	5600	5700	5800
	5800	5900	6000
	6000	6100	6200
	6200	6300	6400
	6400	6500	6600
	6600	6700	6800
	6800	6900	7000
	7000	7100	7200
	7200	7300	7400
	7400	7500	7600
	7600	7700	7800
	7800	7900	8000
	8000	8100	8200
	8200	8300	8400
	8400	8500	8600
	8600	8700	8800
	8800	8900	9000
	9000	9100	9200
	9200	9300	9400
	9400	9500	9600
	9600	9700	9800
	9800	9900	10000

DIM TYPE		PART DRAWING
STYLE		
VOLUME (QTY)	SEE CHART	
DISTR CODE		
UNLESS OTHERWISE SPECIFIED		
THIS DOCUMENT IS IN ACCORDANCE WITH ISO 9001:1994		
AS ISSUED BY THE IN CHARGE SUPERVISOR		
FEATURES MAY BE ADDED SEPARATELY PER DELPHI 10949001		
ALL DIMENSIONS ARE IN MILLIMETERS		
REFERENCE		
THIRD ANGLE PROJECTION		
DO NOT SCALE		
USE MATH DATA		

DELPHI	
DELPHI PACKARD ELECTRICAL/ELECTRONIC ARCHITECTURE	
WYOMING, OH	
DR	DATE
APV01 M. CHRESTAY	050C05
APV02 M. CHRESTAY	050C05
APV03 W. MEASE	060C05
APV04	
APV05	
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 10949001	
MATERIAL SEE CHART	
DRAWING NAME	
TAXI CONN F GT FBT 150	
DRAWING NUMBER	
13520380	
SIZE	SCALE
A0	3:1
FRAME NO	1 OF 1
SHEET NO	11
REV	R 08
N/P	-

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[13586108](#)