





PART NO	1216 0855
---------	-----------

[illegible]

NOTE : 75% TOLERANCE DUE TO 
DOES NOT APPLY TO
RESISTANCE.



1/8"-27 DRYSEAL PTF-SAE SHORT
ROLLED THREAD. THREAD MUST
PASS APPROPRIATE PTF
L₁ AND L₂ RING GAUGES.

<h1> Ugraphics II </h1>		<h1> METRIC </h1>	
THIRD ANGLE PROJECTION		DIMENSIONS ARE IN MILLIMETERS UNLESS OTHERWISE SPECIFIED	
		TOLERANCE UNLESS OTHERWISE SPECIFIED DECIMAL: ANGULAR $\pm 2^\circ$	
CODE NO 6901		ONE PLACE ± 0.3 TWO PLACE ± 0.15 DES	
DWG DATE 21JL94		DR F.D.SILVIO 120C94	
SCALE NONE		CK F.D.SILVIO 120C94	
REFERENCE NO 12160855 "R10" SIZE		APPR VOL CM ³	
MATERIAL SPEC SEE DRAWING			
NAME TEMP SENSOR ASM			
PART NUMBER 12160855		SIZE A2	
PRODUCT INFORMATION DWG			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)
[12160855](#)