



[illegible]

OBSOLETE

PART NO
1218 6548

- NOTES — 1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND
AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION.
(SEE MATH MODEL FOR PRECISE DIMENSION)
ALL RADII 0.40
2. MATING COMPONENTS:
CONNECTOR TO ACCEPT 2146138 OR EQUIVALENT.
CAVITIES 3M, 3N, 4M, 4N, 7A, 7B, 7E, 7F, 7J, 7K TO ACCEPT
12034047 OR EQUIVALENT.
CAVITIES 3P, 4P, 7G, 7H, TO ACCEPT 12020119 OR EQUIVALENT.
CAVITIES 1A, 1B, 1C, 1D, 1E, 1F, 1G, 1H, 1J, 1K, 1L, 1M, 1N, 2A, 2B,
2C, 2D, 2E, 2F, 2G, 2H, 2J, 2K, 2L, 2M, 2N, 3A, 3B, 3C, 3D, 3H, 3J, 3K,
3L, 4A, 4B, 4C, 4D, 4E, 4H, 4J, 4K, 4L, 5A, 5B, 5C, 5D, 5E, 5H, 5J, 5K,
5L, 6A, 6B, 6C, 6D, 6E, 6H, 6J, 6K, 6L, 8A, 8B, 8C, 8D, 8E, 8F, 8H, 8J,
8K, 8L, 8M, 8N, 9A, 9B, 9C, 9D, 9E, 9F, 9G, 9H, 9J, 9K, 9L, 9M, 9N, 9P,
9Q, 9R. TO ACCEPT 12040993 TERMINAL OR EQUIVALENT
SECONDARY LOCKS 12059978, 12186244, 12059980, OR EQUIVALENT.
3. RETAINER MUST WITHSTAND A MINIMUM FORCE OF 890N APPLIED
AXIALLY TO THE THREADED END OF THE BOLT.
4. BOLT MUST ROTATE FREELY AFTER RETAINER RING IS IN PLACE.
5. THIS ASSEMBLY IS TO BE BOLTED TO 12146138 CONNECTOR WITH A
TORQUE ON THE BOLT OF 3.0 N-M TO 5.0 N-M.
6. FOR POLYESTER IN-PROCESS MOISTURE AND PART DEGRADATION
LIMITS, SEE ESO-1502 CLASS II.
7. THIS PART IS NOT CONTROLLED FOR AUTOMATIC FEEDING.
8. THIS PART DOES NOT REQUIRE SPECIAL PACKAGING.

			
THIRD ANGLE PROJECTION		TOLERANCE UNLESS OTHERWISE SPECIFIED DECIMAL: ANGULAR $\pm 2^\circ$	
		ONE PLACE ± 0.3 TWO PLACE ± 0.15	
CODE NO	QC	DESALBERTO VITE 09JA96	
6901		DRALBERTO VITE 09JA96	
DWG DATE 09JA96		KALBERTO VITE 09JA96	
SCALE 2:1		APPR	
REFERENCE NO 12146140		VOL CM ³	
MATERIAL SPEC			
SEE DRAWING			
NAME			
ASM CONN 102M M/P MXD			
PART NUMBER			SIZE
1218 6548			A1
PRODUCT INFORMATION DWG			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[12186548](#)