


OPTIONAL CONSTRUCTION
SAME EXCEPT AS SHOWN
SCALE 2:1

OPTIONAL CONSTRUCTION
FOR 15475295
SAME EXCEPT AS SHOWN
SCALE 2:1




MATERIAL RECYCLING CODE OPTIONAL



ASSEMBLY VIEW
SCALE 2:1

13813420	01	-	RESTRICTED	POLYAMIDE COMPOUND BLACK	-	-
1549248	02	AF	RESTRICTED	POLYAMIDE COMPOUND GRAY	15475295	-
15475295	02	AH	-	POLYAMIDE COMPOUND GRAY	-	SEE NOTE #8
15449890	04	AE	-	POLYAMIDE COMPOUND BLACK	-	-
15422831	04	AB	-	POLYAMIDE COMPOUND GRAY	15475295	-
PART NO	REV	N/P	RESTRICTED USAGE	MATERIAL SPECIFICATION AND COLOR	REPLACED BY	SEE NOTE

SYMBOL DEFINITION			MISSING SYMBOLS	
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO OF INSPECTIONS REQUIRED		NO MISSING SYMBOL NUMBER	
	LAST NO. USED		7	



NOTES

- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
 - DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
 - MATERIAL RECYCLING CODE PER ISO 11469. (1.5)X(0.1) CHARACTERS AS SHOWN TO BE LOCATED ON ANY EXTERIOR SURFACE. OPTIONAL CONSTRUCTION TO BE NO MATERIAL RECYCLING CODE.
 - FOR Ø 6.3-Ø 7 mm HOLE WITH PANEL THICKNESS OF 0.8-6.3 mm.
 - WIRE ASSEMBLY DIA:
 - MINIMUM - APPROXIMATELY 4-6 MM
 - MAXIMUM - 28mm TAPED BUNDLE
 - 22mm CONDUIT SECURED BUNDLE
 - (1.5)X(0.1) DELPHI CORPORATE BRAND TO BE LOCATED ON ANY EXTERIOR SURFACE, PREFERABLY VISIBLE AT FINAL ASSEMBLY. OPTIONAL CONSTRUCTION FOR EXISTING TOOLING MAY BE "PED" OR NO LOGO.
 - TEMPERATURE RANGE: -40°C TO 125°C
 - THIS PRODUCT IS NOT CATEGORIZED AS AN APPEARANCE ITEM. MINOR IMPERFECTIONS INCLUDING, BUT NOT LIMITED TO, FLOW MARKS, COLOR BLEMISHES, GATE VESTIGE, AND SOFT FLASH THAT DO NOT AFFECT THE FIT, FORM, OR FUNCTION OF THE PART ARE PERMISSIBLE PER DPNP-4.7-CS-01.
 - FOR P/N WET PACKING IS RECOMMENDED

ASSEMBLY PROCESSING NOTES

- APPLY WITH MANUAL PANDUIT GUN GS2B OR EQUIVALENT. GUN SETTING AT STANDARD AND 6-8 RANGE. IF PNEUMATIC USE: PANDUIT GUN PPTS, GUN SETTING SAME AS ABOVE.

3		PROCESS SENSITIVE DIMENSION		ALL DIMENSIONS ARE IN MILLIMETERS	
DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED				REFERENCE	
DIMENSIONAL RANGE (MM)				CHART SET	
FROM	TO	> 20	> 30	> 70	> 100
		> 150	> 200	> 250	> 300
		> 350	> 400	> 450	> 500
TOLERANCE UNLESS OTHERWISE SPECIFIED					
		+0.15	+0.2	+0.3	+0.4
		+0.5	+0.6	+0.7	+0.8
		+1.0	+1.2	+1.5	+1.6
THIRD ANGLE PROJECTION					
DO NOT SCALE					
USE MATH DATA					
NX					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[15449890-B](#)