




SYMBOL DEFINITION		
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL  DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO OF INSPECTIONS REQUIRED	7
	LAST NO. USED	7

MISSING SYMBOLS		DWG STATUS				ZONE	REVISION HISTORY	AUTH	DR	1	
		DATE	STG	REV	N/P					APVD 1	APVD 2
NO MISSING SYMBOL NUMBER		30MY96	-	-	-	-	ALL PARTS - PID REDRAWN FROM SEPARATE OD & UPDATED - NO REV UPDATE REQ'D	172603	JCS	WTP	WTP
		30MY97	-	-	-	-	ALL PARTS - REVISED NOTES #1 & #3 - NO REV UPDATE REQ'D	180366	JIL	JVS	JVS
		220C97	-	-	-	-	ALL PARTS - PID UPDATED - NO REV UPDATE REQ'D	183104	EML	JVM	JVM
		12MR98	-	-	-	-	ALL PARTS - REVISED - NO REV UPDATE REQ'D	186137	ROM	OOD	OOD
		15AP09	R	05	-	-	ALL PARTS - RESTRICTED & ADDED "RESTRICTED USAGE" AND "REPLACED BY" COLUMNS FROM CHART	407809	JAR	JVM	MGC
		09SE10	R	06	-	-	ALL PARTS - REDRAWN	411744	MAB	JVM	FRE
		28MY12	R	07	-	-	ALL PARTS - REVISED PLATING NOTES	418348	AH	AH	AH

MATERIAL:

TERMINAL - 0.25 MM THK CDA 510 HALF HARD PHOSPHOR BRONZE

SLEEVE - STAINLESS STEEL UNPLATED

PLATING NOTE:

TERMINAL IS SELECTIVELY NICKEL, TIN & GOLD PLATED.

NOTES

1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:

DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.

2. REFERENCE MATING COMPONENTS OR EQUIVALENT:

HEADER CONNECTOR 12129025
PIN 12092396

3. FORCE REQUIRED TO PULL SLEEVE FROM TERMINAL AFTER ASSEMBLY, 60N MINIMUM.

4. MAXIMUM CURRENT CAPACITY IS 7 AMPS.

5. TERMINALS MUST FIT A MAX 2.54 MM DIA GAGE HOLE 12±0.3 MM DEEP AFTER CRIMPING.

12084913	H3		0.35 - 0.5	1.92	21	2.1	RESTRICTED	15359001
12084912	K3		0.8	2.04	18	2.5	RESTRICTED	15359002
PART NO	REV	STATUS	SIZE (MM²)	±0.08 DIA	ID NO	D ±0.2	RESTRICTED USAGE	REPLACED BY
			CABLE					

1 PROCESS SENSITIVE DIMENSION	
DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED	
DIMENSIONAL RANGE (MM)	CHART D
FROM 0	>12
TO 12	>12
TOLERANCE UNLESS OTHERWISE SPECIFIED	
±0.1	±0.2
ANGULAR TOLERANCE ±2°	

A LINE DRAWN THROUGH A PART NUMBER INDICATES THAT PHYSICAL PARTS ARE NOT AVAILABLE FOR ORDERING.	
PART NUMBERS THAT DO NOT HAVE A LINE PRESENT INDICATE THAT PHYSICAL PARTS ARE AVAILABLE FOR ORDERING.	
CONTACT DELPHI SALES TO ASSURE AVAILABILITY OF PARTS.	
DWG TYPE	
PART DRAWING	
STYLE	
VOLUME (CNP)	
DISTR CODE	
UNLESS OTHERWISE SPECIFIED	
THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994 AS AMENDED BY THE 2001 GLOBAL DIMENSIONING AND TOLERANCING ADDENDUM-2001. SEPARATE PATTERNS OF FEATURES MAY BE GAGED SEPARATELY REGARDLESS OF DATUM REFERENCES.	
ALL DIMENSIONS ARE IN MILLIMETERS	
REFERENCE	
THIRD ANGLE PROJECTION	
DO NOT SCALE	
USE MATH DATA	

DELPHI	
DELPHI PACKARD ELECTRICAL/ELECTRONIC ARCHITECTURE	
WARREN, OH	
COPYRIGHT 1996 DELPHI CORPORATION AND/OR ITS AFFILIATES. ALL RIGHTS RESERVED.	
THIS DRAWING IS THE PROPERTY OF DELPHI CORPORATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD MATH DATA, AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION IS PROHIBITED.	
DR	DATE
APVD1 JUAN M.CANO	30MY96
APVD2 W. TURNBULL	30MY96
APVD3 V. BANCROFT	19JN96
APVD4	
APVD5	
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 10949001	
MATERIAL SEE DRAWING	
DRAWING NAME	
TAXI ASM TERM F MIC/P 100W	
DRAWING NUMBER	
12084911	
SIZE A1	SCALE 10:1
FRAME NO 1 OF 1	SHEET NO 1 OF 2
STG R	REV 07
N/P -	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[12084912-L](#) [12084913-L](#) [12084913](#)