


- **Designed for Front-end GPS Applications**
- **Low Insertion Loss**
- **3.0 x 3.0 x 1.3 mm Surface-mount Case**
- **No Matching Circuit Required**
- **Complies with Directive 2002/95/EC (RoHS)**
- **Moisture Sensitivity Level: 1**

Maximum Ratings at +25 °C Unless Stated Otherwise

Rating	Symbol	Value	Units
Maximum Input Signal Level		+10	dBm
DC Voltage on any Non-ground Terminal	WVdc	4	Volts
Operating Temperature Range	T _A	-40 to +95	°C
Storage Temperature Range on Tape and Reel	T _{STG}	-40 to +85	°C
Lead Soldering Temperature for 10 Seconds	T _{WAVE}	260	°C
Peak Reflow Solder Temp for 40 Seconds	T _{Reflow}	235	°C
Suitable for lead-free soldering - Max Soldering Temperature		260°C for 30 s	

SF1186E-2

1575.42 MHz
SAW Filter



SM3030-6

Electrical Characteristics

Characteristic	Sym	Notes	Min	Typ	Max	Units
Center Frequency	f _O			1575.42		MHz
1 dB Bandwidth			2.046	15.3		MHz
Passband Amplitude Ripple, f _O ±2.0 MHz				0.1	2.0	dB _{P-P}
Passband VSWR				1.4	2.0	
Insertion Loss				2.68	3.5	dB
Attenuation Referenced to 0 dB:						
850 MHz			45	51.2		dB
1500 MHz			40	52.7		
1535.42 MHz			20	38.9		
1615.42 MHz			20	58.8		
1640 MHz			45	59.1		
1700 MHz			50	56.7		
Temperature Coefficient			-30			ppm/°C
Operating Temperature	T _A		-40		+95	°C
Single-ended Input /Output Impedance Match		No matching network required for operation at 50 ohms				
Case Style		SM3030-6 3 x 3 mm Nominal Footprint				
Lid Symbolization	Y=year, WW=week, S=shift		979 YWWWS			

Electrical Connections

Pin #	Description	Pin #	Description
1	Ground	4	Ground
2	Input	5	Output
3	Ground	6	Ground




CAUTION: Electrostatic Sensitive Device. Observe precautions for handling.

NOTES:


1. The design, manufacturing process, and specifications of this device are subject to change.
2. US or International patents may apply.
3. RoHS compliant from the first date of manufacture.

Transfer function :

(1) S21 response (span : 300 MHz)




(2) S21 response (span : 3 GHz)




Reflection Functions:



S11



S22




Reflection Functions:



SM3030-6 Case

6-Terminal Ceramic Surface-Mount Case

3.0 X 3.0 mm Nominal Footprint



Foot Print Dimensions in Nominal Inches


Case Dimensions						
Dimension	mm			Inches		
	Min	Nom	Max	Min	Nom	Max
A	2.87	3.0	3.13	0.113	0.118	0.123
B	2.87	3.0	3.13	0.113	0.118	0.123
C	1.12	1.25	1.38	0.044	0.049	0.054
D	0.77	0.9	1.03	0.030	0.035	0.040
E	2.67	2.80	2.93	0.105	0.110	0.115
F	1.47	1.6	1.73	0.058	0.063	0.068
G	0.72	0.85	0.98	0.028	0.033	0.038
H	1.37	1.5	1.63	0.054	0.059	0.064
I	0.47	0.6	0.73	0.019	0.024	0.029
J	1.17	1.3	1.43	0.046	0.051	0.056

Electrical Connections		
Connection		Terminals
Port 1	Single-ended Input	2
Port 2	Single-ended Output	5
	Ground	All others
Single-ended Operation Only		
Dot indicates Pin 1		

Case Materials	
Solder Pad Plating	0.3 to 1.0 μ m Gold over 1.27 to 8.89 μ m Nickel
Lid Plating	2.0 to 3.0 μ m Nickel
Body	Al ₂ O ₃ Ceramic

TOP VIEW

BOTTOM VIEW



See Detail "A"

Diagram illustrating the experimental setup for measuring the wavelength of light using a double-slit interference pattern. The distance between the two slits is 12.0 cm. The central maximum is marked with a dashed line. The distance to the 100th order maximum is labeled "100 REF." and the distance to the "B" order maximum is labeled ""B" REF."

Technical drawing of a circular part. The drawing shows a cross-section of a cylinder with a central hole. The outer diameter is 20.2, the inner diameter is 13.0, and the wall thickness is 2.0. The drawing includes a center line and a section line.

Technical drawing of a 12x12 inch plate with dimensions and section lines. The drawing includes a top view and two cross-sections, A-A and B-B.

Top View Dimensions:

- Overall width: 12.0
- Overall height: 12.0
- Pin diameter: $\varnothing 1.5$
- Pin spacing (center-to-center): 2.0, 4.0, 8.0
- Pin #1 location: 0.3 from the left edge, 3.35 from the bottom edge
- Section A-A: 1.75 from the top edge, 5.5 from the bottom edge
- Section B-B: 3.35 from the left edge, 8.0 from the right edge
- Radius: R0.3 (MAX.) at the top left corner, R0.5 (TYP.) at the bottom right corner


Section A-A: A cross-section showing the plate thickness and the location of the pin.

Section B-B: A cross-section showing the plate thickness and the location of the pin.

USER DIRECTION OF FEED: Indicated by an arrow pointing to the right.

Recommended Reflow Profile

1. Preheating shall be fixed at 150~180°C for 60~90 seconds.
2. Ascending time to preheating temperature 150°C shall be 30 seconds min.
3. Heating shall be fixed at 220°C for 50~80 seconds and at 260°C+0/-5°C peak (10 seconds).
4. Time: 5 times maximum.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[RFMi:](#)

[SF1186E-2](#)