




# DDR5

The Global Leader in Specialized Storage and Memory Solutions



## KEY FEATURES

- 2X DDR4 speed
- PMIC for efficient power management
- On-die ECC
- 1.1V lower power consumption
- Up to 128 Gb Density with 4-Layer TSV
- RDIMM with precise temperature control

ATP's DDR5 solutions are expected to deliver performance and reliability improvements over the previous generation, especially for critical computing applications.

As the next-generation DRAM specification, DDR5 is poised to exceed DDR4 in every way. DDR5 promises faster performance, higher memory bandwidth, higher densities, and a new power management structure that delivers better power efficiency. All of these advantages, and more, are expected to meet the ever-growing memory needs of present and future applications.

Both DDR4 and DDR5 dual-inline memory modules (DIMMs) still have 288 pins, but with DDR5's higher bandwidth, this means it can transmit data faster. While the pin count is the same, DDR5 DIMMs will not fit in DDR4 sockets as the alignment key is located differently and the pinouts have been changed to accommodate the new features.

Technologies	30μ" Golden Finger	ATP TDBI	Wide Temperature	Anti-Sulfur Resistors	Conformal Coating	PCB Chamfer
RDIMM	●	●	▲	▲	-	▲
ECC CUDIMM	●	●	▲	▲	▲	▲
Non-ECC CUDIMM	▲	●	▲	▲	▲	▲
ECC CSO-DIMM	●	●	▲	▲	▲	▲
Non-ECC CSO-DIMM	▲	●	▲	▲	▲	▲
RDIMM	●	●	▲	▲	-	▲
ECC UDIMM	●	●	▲	▲	▲	▲
Non-ECC UDIMM	▲	●	▲	▲	▲	▲
ECC SO-DIMM	●	●	▲	▲	▲	▲
Non-ECC SO-DIMM	▲	●	▲	▲	▲	▲

## Specifications

DDR5									
DIMM Type	RDIMM	ECC UDIMM	ECC CUDIMM	Non-ECC UDIMM	Non-ECC CUDIMM	ECC SO-DIMM	ECC CSO-DIMM	Non-ECC SO-DIMM	Non-ECC CSO-DIMM
Density	16 GB to 256 GB	16 GB to 64 GB		8 GB to 64 GB		16 GB to 64 GB		8 GB to 64 GB	
Speed up to (MT/s)*	6400*	5600	6400*	5600	6400*	5600	6400*	5600	6400*
PCB Height	Low profile / VLP**	Low profile / VLP**		Low profile		Low profile		Low profile	
Operating Temperature	0°C to 85°C / -40°C to 85°C								

\*Available in 2H 2025

\*\* VLP: 0.74"



The Global Leader in Specialized Storage and Memory Solutions

## WE BUILD WITH YOU

Product spec and its related information are subject to change without advance notice.

Please refer to [www.atpinc.com](http://www.atpinc.com) for latest information

v1.0 012025

© Copyright 2025 ATP Electronics, Inc. All rights reserved.

### ATP TAIWAN (HQ)

TEL: +886-2-2659-6368  
sales-apac@atpinc.com

### ATP USA

TEL: +1-408-732-5000  
sales@atpinc.com

### ATP EUROPE

TEL: +49-89-374-9999-0  
sales-europe@atpinc.com

### ATP JAPAN

TEL: +81-3-6260-0797  
sales-japan@atpinc.com

### ATP CHINA

TEL: +86-21-5080-2220  
sales@cn.atpinc.com

### ATP INDIA

sales-india@atpinc.com

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ATP Electronics:](#)

[D516G0RD568DDMC](#)