

## Description

The AP7342 is a dual low-dropout regulator with high output voltage accuracy, low  $R_{DS(on)}$ , high PSRR, low output noise and low quiescent current. This regulator is based on a CMOS process.


Each regulator includes a voltage reference, error amplifier, current limit circuit and an enable input to turn on/off output. With the integrated resistor network, fixed output voltage versions can be delivered.

With its low power consumption and line and load transient response, the AP7342 is well suited for low power handheld communication equipment.

The AP7342 is packaged in X2-DFN1212-6 package and allows for smallest footprint and dense PCB layout.

## Pin Assignments

### Top View



**X2-DFN1212-6**

## Features


- Low  $V_{IN}$  and Wide  $V_{IN}$  Range: 1.7V to 5.25V
- Guarantee Output Current: 150mA
- $V_{OUT}$  Accuracy  $\pm 1\%$
- Ripple Rejection: 75dB at 1kHz
- Low Output Noise: 60 $\mu$ Vrms from 10Hz to 100kHz
- Quiescent Current as Low as 35 $\mu$ A
- $V_{OUT}$  Fixed 1.2V to 3.6V
- **Totally Lead-Free & and Fully RoHS Compliant (Notes 1 & 2)**
- **Halogen and Antimony Free, Green Device (Note 3)**
- **For automotive applications requiring specific change control (i.e. parts qualified to AEC-Q100/101/104/200, PPAP capable, and manufactured in IATF 16949 certified facilities), please [contact us](#) or your local Diodes representative. <https://www.diodes.com/quality/product-definitions/>**

## Applications

- Smart phones/Tablets
- RF supplies
- Cameras
- Portable videos
- Portable media players
- Wireless adapters
- Wireless communication

- Notes:
1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.
  2. See <https://www.diodes.com/quality/lead-free/> for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
  3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.


## Typical Applications Circuit




## Pin Descriptions

Pin Number	Pin Name	Function
1	VOUT1	Channel 1 Output Voltage Pin
2	VOUT2	Channel 2 Output Voltage Pin
3	GND	Ground
4	EN2	Channel 2 Enable Pin This pin should be driven either high or low and must not be floating. Driving this pin high enables channel 2 output, while pulling it low puts Channel 2 regulator into shutdown mode.
5	VIN	Power Input Pin
6	EN1	Channel 1 Enable Pin This pin should be driven either high or low and must not be floating. Driving this pin high enables channel 1 output, while pulling it low puts Channel 1 regulator into shutdown mode.
—	Thermal Pad	In PCB layout, it is preferred to use large copper area to cover this pad for better thermal dissipation, then connect this area to GND or leave it open. However, do not use it as GND electrode function alone.

## Functional Block Diagram



AP7342 (No Discharge)



AP7342 (With Discharge)

## Absolute Maximum Ratings (@T<sub>A</sub> = +25°C, unless otherwise specified.) (Note 4)

Symbol	Parameter	Rating	Unit
V <sub>IN</sub>	Input Voltage	6.0	V
V <sub>EN</sub>	Input Voltage at EN Pins	6.0	V
V <sub>OUT</sub>	Output Voltage	-0.3 to V <sub>IN</sub> +0.3	V
I <sub>OUT</sub>	Output Current	180	mA
P <sub>D</sub>	Power Dissipation	600	mW
T <sub>A</sub>	Operating Ambient Temperature	-40 to +85	°C
T <sub>STG</sub>	Storage Temperature	-55 to +125	°C

Note: 4. Stresses greater than those listed under *Absolute Maximum Ratings* can cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under *Recommended Operating Conditions* is not implied. Exposure to *Absolute Maximum Ratings* for extended periods can affect device reliability.

## Recommended Operating Conditions (@T<sub>A</sub> = +25°C, unless otherwise specified.)

Symbol	Parameter	Min	Max	Unit
V <sub>IN</sub>	Input Voltage	1.7	5.25	V
I <sub>OUT</sub>	Output Current	0	150	mA
T <sub>A</sub>	Operating Ambient Temperature	-40	+85	°C







## Electrical Characteristics

(@T<sub>A</sub> = +25°C, V<sub>IN</sub> = V<sub>OUT</sub>+1V (V<sub>OUT</sub> > 1.5V), V<sub>IN</sub> = 2.5V (V<sub>OUT</sub> ≤ 1.5V), I<sub>OUT</sub> = 1mA, C<sub>IN</sub> = C<sub>OUT</sub> = 1.0μF, unless otherwise specified.)







Parameter	Conditions		Min	Typ	Max	Unit
Input Voltage	T <sub>A</sub> = -40°C to +85°C		1.7	—	5.25	V
Output Voltage Accuracy (Note 5)	V <sub>IN</sub> = (V <sub>OUT-Nom</sub> +1.0V) to 5.25V I <sub>OUT</sub> = 1mA to 150mA	T <sub>A</sub> = +25°C	-1	—	1	%
		T <sub>A</sub> = -40°C to +85°C	-1.5	—	1.5	
Line Regulation (ΔV <sub>OUT</sub> /ΔV <sub>IN</sub> /V <sub>OUT</sub> )	V <sub>IN</sub> = (V <sub>OUT-Nom</sub> +1.0V) to 5.25V, I <sub>OUT</sub> = 1.0mA		—	0.02	0.1	%/V
Load Regulation (ΔV <sub>OUT</sub> /ΔI <sub>OUT</sub> )	V <sub>IN</sub> = V <sub>OUT-Nom</sub> +1.0V, I <sub>OUT</sub> = 1mA to 150mA		—	15	30	mV
Quiescent Current (Note 6)	Set EN1 high, set EN2 low, or set EN2 high, set EN1 low, No load		—	35	50	μA
	Set EN1/EN2 high, No load		—	70	100	μA
I <sub>STANDBY</sub>	Set EN1/EN2 low, No load		—	0.1	1.0	μA
Output Current	—		300	—	—	mA
Foldback Short Current (Note 7)	V <sub>OUT</sub> short to ground		—	55	—	mA
PSRR (Note 8)	V <sub>IN</sub> = (V <sub>OUT</sub> +1V) V <sub>DC</sub> + 0.2Vp-pAC V <sub>OUT</sub> ≥ 1.8V, I <sub>OUT</sub> = 30mA	f = 1kHz	—	75	—	dB
Output Noise Voltage (Notes 8 & 9)	BW = 10Hz to 100kHz, I <sub>OUT</sub> = 30mA		—	60	—	μVrms
Dropout Voltage (Note 10)	I <sub>OUT</sub> = 150mA	V <sub>OUT</sub> ≤ 1.2V	—	0.48	0.59	V
		1.2V < V <sub>OUT</sub> ≤ 1.4V	—	0.39	0.50	
		1.4V < V <sub>OUT</sub> ≤ 1.7V	—	0.35	0.44	
		1.7V < V <sub>OUT</sub> ≤ 2.1V	—	0.30	0.39	
		2.1V < V <sub>OUT</sub> ≤ 2.5V	—	0.26	0.34	
		2.5V < V <sub>OUT</sub> ≤ 3.0V	—	0.25	0.30	
		3.0V < V <sub>OUT</sub> ≤ 3.6V	—	0.22	0.29	
Output Voltage Temperature Coefficient	I <sub>OUT</sub> = 30mA, T <sub>A</sub> = -40°C to +85°C		—	±30	—	ppm/°C
EN Input Low Voltage	—		0	—	0.5	V
EN Input High Voltage	—		1.3	—	5.25	V
EN Input Leakage	V <sub>EN</sub> = 0V, V <sub>IN</sub> = 5.0V or V <sub>EN</sub> = 5.0V, V <sub>IN</sub> = 0V		-1.0	—	1.0	μA
On Resistance of N-Channel for Auto-Discharge (Note 11)	V <sub>IN</sub> = 4.0V, V <sub>EN</sub> = 0V (Disabled)	D Version, Chanel 1 & 2	—	50	—	Ω

- Notes:
- Potential multiple grades based on following output voltage accuracy.
  - Quiescent current defined here is the difference in current between the input and the output.
  - Short-circuit current is measured with V<sub>OUT</sub> pulled to GND.
  - This specification is guaranteed by design.
  - To make sure lowest environment noise minimizes the influence on noise measurement.
  - Dropout voltage is the voltage difference between the input and the output at which the output voltage drops 2% below its nominal value.
  - AP7342 has 2 options for output, built-in discharge and non-discharge.



## Typical Characteristics




## Typical Characteristics (continued)



## Typical Characteristic (continued)




Load Transient Response Waveforms ( $V_{IN}=V_{OUT}+1V$ ,  $C_{IN}=C_{OUT1}=C_{OUT2}=0.47\mu F$ ,  $T_A=+25^{\circ}C$ )



**Typical Characteristics** (continued)


Load Transient Response Waveforms ( $V_{IN} = V_{OUT} + 1V$ ,  $C_{IN} = C_{OUT1} = C_{OUT2} = 0.47\mu F$ ,  $T_A = +25^\circ C$ )






## Typical Characteristics (continued)

Turn On Waveform of Output Discharge Versions ( $V_{IN} = V_{OUT} + 1V$ ,  $C_{IN} = C_{OUT1} = C_{OUT2} = 0.47\mu F$ ,  $T_A = +25^\circ C$ )



Turn Off Waveform of Output Discharge Versions ( $V_{IN} = V_{OUT} + 1V$ ,  $C_{IN} = C_{OUT1} = C_{OUT2} = 0.47\mu F$ ,  $T_A = +25^\circ C$ )



## Application Information

### Output Capacitor

An output capacitor ( $C_{OUT}$ ) is needed to improve transient response and maintain stability. The AP7342 is stable with very small ceramic output capacitors. The ESR (Equivalent Series Resistance) and capacitance drives the selection. If the application has large load variations, it is recommended to utilize low-ESR bulk capacitors. It is recommended to place ceramic capacitors as close as possible to the load and the GND pin and care should be taken to reduce the impedance in the layout.

### Input Capacitor

To prevent the input voltage from dropping during load steps, it is recommended to utilize an input capacitor ( $C_{IN}$ ). A minimum  $0.47\mu\text{F}$  ceramic capacitor is recommended between  $V_{IN}$  and GND pin to decouple input power supply glitch. This input capacitor must be located as close as possible to the device to ensure input stability and reduce noise. For PCB layout, a wide copper trace is required for both  $V_{IN}$  and GND pin.

### Enable Control

The AP7342 is turned on by setting the EN pins high, and is turned off by pulling it low. If this feature is not used, the EN pins should be tied to  $V_{IN}$  pin to keep the regulator output on at all time. To ensure proper operation, the signal source used to drive the EN pins must be able to swing above and below the specified turn-on/off voltage thresholds listed in the *Electrical Characteristics* section.

### Short-Circuit Protection

When  $V_{OUT}$  pins are short-circuit to GND, short-circuit protection will be triggered and clamp the output current to approximately 60mA. This feature protects the regulator from overcurrent and damage due to overheating.



### Layout Considerations

For good ground loop and stability, the input and output capacitors should be located close to the input, output, and GND pin of the device. The regulator GND pin should be connected to the external circuit ground to reduce voltage drop caused by trace impedance. Ground plane is generally used to reduce trace impedance. Wide trace should be used for large current paths from  $V_{IN}$  to  $V_{OUT}$  and load circuit.


## ESR vs. Output Current

Ceramic type output capacitor is recommended for this series; however, the other output capacitors with low ESR can also be used. The relations between  $I_{OUT}$  (Output Current) and ESR of an output capacitor are shown below. The stable region is marked as the hatched area in the graph.

Measurement Conditions: Frequency Band: 10Hz to 2MHz, Temperature:  $-40^{\circ}\text{C}$  to  $+85^{\circ}\text{C}$ .



## Ordering Information




Part Number	Part Number Suffix	Package Code	Package	Packing	
				Qty.	Carrier
AP7342-XXXXFS6-7	-7	FS6	X2-DFN1212-6	5,000	7" Tape and Reel
AP7342D-XXXXFS6-7	-7	FS6	X2-DFN1212-6	5,000	7" Tape and Reel

## Marking Information

(1) X2-DFN1212-6

(Top View)



XXX : Identification Code

Y : Year : 0 to 9

W : Week : A to Z : week 1 to 26;  
a to z : week 27 to 52; z represents  
week 52 and 53


X : Internal Code

Part Number	V <sub>OUT1</sub> /V <sub>OUT2</sub>	Package	Identification Code
AP7342-3028FS6-7	3.0V/2.8V	X2-DFN1212-6	CAA
AP7342-3328FS6-7	3.3V/2.8V	X2-DFN1212-6	CAB
AP7342D-1218FS6-7	1.2V/1.8V	X2-DFN1212-6	CAC
AP7342D-1528FS6-7	1.5V/2.8V	X2-DFN1212-6	CAD
AP7342D-1815FS6-7	1.8V/1.5V	X2-DFN1212-6	CAE
AP7342D-1818FS6-7	1.8V/1.8V	X2-DFN1212-6	CAF
AP7342D-1828FS6-7	1.8V/2.8V	X2-DFN1212-6	CAG
AP7342D-1833FS6-7	1.8V/3.3V	X2-DFN1212-6	CAH
AP7342D-2518FS6-7	2.5V/1.8V	X2-DFN1212-6	CAJ
AP7342D-2812FS6-7	2.8V/1.2V	X2-DFN1212-6	CAK
AP7342D-2818FS6-7	2.8V/1.8V	X2-DFN1212-6	CAM
AP7342D-2825FS6-7	2.8V/2.5V	X2-DFN1212-6	CAN
AP7342D-2833FS6-7	2.8V/3.3V	X2-DFN1212-6	CAP
AP7342D-3018FS6-7	3.0V/1.8V	X2-DFN1212-6	CAR
AP7342D-3028FS6-7	3.0V/2.8V	X2-DFN1212-6	CAS
AP7342D-3030FS6-7	3.0V/3.0V	X2-DFN1212-6	CAT
AP7342D-3318FS6-7	3.3V/1.8V	X2-DFN1212-6	CAU
AP7342D-3328FS6-7	3.3V/2.8V	X2-DFN1212-6	CAV
AP7342D-3330FS6-7	3.3V/3.0V	X2-DFN1212-6	CAW
AP7342D-3333FS6-7	3.3V/3.3V	X2-DFN1212-6	CAX
AP7342D-3612FS6-7	3.6V/1.2V	X2-DFN1212-6	CAY

## Package Outline Dimensions

Please see <http://www.diodes.com/package-outlines.html> for the latest version.

X2-DFN1212-6




X2-DFN1212-6			
Dim	Min	Max	Typ
A	-	0.40	0.39
A1	0.00	0.05	0.020
A3	-	-	0.13
b	0.13	0.23	0.18
D	1.15	1.25	1.20
D2	0.89	0.99	0.94
E	1.15	1.25	1.20
E2	0.25	0.35	0.30
e	-	-	0.40
k	0.15	0.25	0.20
L	0.15	0.25	0.20
z	-	-	0.11
z1	-	-	0.05
All Dimensions in mm			

## Suggested Pad Layout



Please see <http://www.diodes.com/package-outlines.html> for the latest version.

X2-DFN1212-6



Dimensions	Value (in mm)
C	0.400
G	0.150
X	0.250
X1	0.940
X2	1.050
Y	0.400
Y1	0.300
Y2	1.400

## Tape Orientation



Note: 12. The taping orientation of the other package type can be found on our website at <https://www.diodes.com/assets/Packaging-Support-Docs/ap02007.pdf>.

**IMPORTANT NOTICE**

1. DIODES INCORPORATED (Diodes) AND ITS SUBSIDIARIES MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).
2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes' products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes' products. Diodes' products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of Diodes' products for their intended applications, (c) ensuring their applications, which incorporate Diodes' products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.
3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.
4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.
5. Diodes' products are provided subject to Diodes' Standard Terms and Conditions of Sale (<https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/>) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.
6. Diodes' products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes' products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.
7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.
8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.
9. This Notice may be periodically updated with the most recent version available at <https://www.diodes.com/about/company/terms-and-conditions/important-notice>

The Diodes logo is a registered trademark of Diodes Incorporated in the United States and other countries.  
All other trademarks are the property of their respective owners.  
© 2023 Diodes Incorporated. All Rights Reserved.

[www.diodes.com](http://www.diodes.com)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Diodes Incorporated:](#)

[AP7342D-3333FS6-7](#) [AP7342D-3030FS6-7](#) [AP7342D-2812FS6-7](#) [AP7342D-1828FS6-7](#) [AP7342D-2518FS6-7](#)  
[AP7342-3028FS6-7](#) [AP7342D-2833FS6-7](#) [AP7342D-1528FS6-7](#) [AP7342D-2818FS6-7](#) [AP7342D-3328FS6-7](#)  
[AP7342D-1218FS6-7](#) [AP7342D-3028FS6-7](#) [AP7342D-2825FS6-7](#) [AP7342D-3018FS6-7](#) [AP7342D-1833FS6-7](#)  
[AP7342D-3612FS6-7](#) [AP7342D-3318FS6-7](#) [AP7342D-1815FS6-7](#) [AP7342-3328FS6-7](#) [AP7342D-1818FS6-7](#)  
[AP7342D-3330FS6-7](#)